


TRIA C10M-AL

Intel® Atom™ E3900 Series / Pentium® / Celeron® SOC



84 x 55

7 / 14W

-40+85

COM 
Express



Highlights

- Intel Atom X7-E3950 quad-core 1.6/2.0GHz, 12W
- Intel Atom X5-E3940 quad-core 1.6/1.8GHz, 9.5W
- Intel Atom X5-E3930 dual-core 1.3/1.8GHz, 6.5W
- Intel Pentium N4200 quad-core 1.1/2.5GHz, 6W
- Intel Celeron N3350 dual-core 1.1/2.4GHz, 6W
- Integrated Intel Gen. 9 HD graphics
- Up to 8GB DDR3L SDRAM (ECC option)
- Two SATA 6Gb/s mass storage interfaces
- eMMC option
- DisplayPort/HDMI/DVI interface
- LVDS/Embedded DisplayPort interface
- Two independent displays supported
- DirectX 12, OpenGL 4.3, OpenCL 2.0
- Two USB 3.0/2.0 and six USB 2.0 interfaces
- Two high-speed UARTs
- Up to four PCI Express™ x1 lanes
- UEFI Firmware
- Trusted Platform Module (option)
- Extended temperature variants

COM Express Type 10



Technical Data

Technology	x86
Formfactor	COM Express Mini
CPU	Intel Atom X7-E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 12W Intel Atom X5-E3940 quad-core 1.6/1.8GHz, 12 EU GFX, 9.5W Intel Atom X5-E3930 dual-core 1.3/1.8GHz, 12 EU GFX, 6.5W Intel Pentium N4200 quad-core 1.1/2.5GHz, 18 EU GFX, 6W Intel Celeron N3350 dual-core 1.1/2.4GHz, 12 EU GFX, 6W
Chipset	SOC
RAM	up to 8GB DDR3L@1.35V SDRAM soldered on board, ECC optional
Flash	eMMC option
Storage Interfaces	2x SATA 6Gb/s
USB	2x USB 3.0, 6 x USB 2.0, 1 x USB 2.0/3.0 client
Serial Interfaces	2x HS UART
Bus Interfaces	4x PCI Express x1 Gen 2, LPC bus (Low Pin Count bus)
Display Controller	Integrated Intel HD graphics Gen. 9 Up to 18 execution units (EU) DirectX 12.0, OpenGL 4.3, OpenCL 2.0 Full Profile; MPEG2, H.264 (L5.2), VC-1, WMV9, VP8, JPEG/MJPEG, H.265 (HEVC), VP9, MVC
Display Interfaces	Two independent displays supported: 1x Digital Display Interface (DP 1.2a (4096 x 2160 @ 60Hz), HDMI 1.4b (3840 x 2160 @ 30Hz) 1x Embedded DisplayPort 1.3 (on variants without LVDS only); 4096 x 2160 @ 60Hz, LVDS 24bit, single-channel, 1366 x 768 @ 60Hz (shared with Embedded DisplayPort)
Network Interface	10/100/1000Base-TX (Intel i210)
Audio Interface	High Definition Audio
Security Device	TPM 2.0 (option)
Miscellaneous	Watchdog Timer: Initiates system reset, programmable RTC battery: external System Monitoring: voltage, temperature, CPU fan, system fan
Feature Highlights	Type 10 pin-out
Firmware	AMI Aptio UEFI
OS Support	Windows 10 (embedded) BSP for Linux on request EAPI (HW Programming Interface)
Power Requirement	Wide range input +5 ... +20V, 5V Stby optional, 7 W (typ.) up to 14 W (typ.)

COM Express Type 10



Environment	Ambient Temperature; 0° ... 60°C (operating, commercial), -40° ... 85°C (operating, industrial), -40° ... 85°C (storage) Humidity: 5 ... 95% (operating, non-condensing), 5 ... 95% (storage, non-condensing)
Dimensions	84mm x 55mm

Technical Data for TRIA C10M-AL

COM Express Type 10



Order Reference

Order No.	Description	Reference	Status*
70334	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom X5-E3950 quad-core 1.6/2.0GHz, 2MB L2, 12W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and LVDS interfaces; Ethernet: Intel i210 Gbit; 8GB DDR3L ECC SDRAM; 16GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; -40 ... +85°C	MSC C10M-AL-E3950-3412011 PCBFTX	PV
70260	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom X5-E3940 quad-core 1.6/1.8GHz, 2MB L2, 9.5W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and eDP interfaces; Ethernet: Intel i210 Gbit; 4GB DDR3L SDRAM; 16GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; -40 ... +85°C	MSC C10M-AL-E3940-2401011 PCBFTX	PV
70332	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom X5-E3940 quad-core 1.6/1.8GHz, 2MB L2, 9.5W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and LVDS interfaces; Ethernet: Intel i210 Gbit; 4GB DDR3L SDRAM; 16GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; -40 ... +85°C	MSC C10M-AL-E3940-2402011 PCBFTX	PV
70258	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom X5-E3930 dual-core 1.3/1.8GHz, 2MB L2, 6.5W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and LVDS interfaces; Ethernet: Intel i210 Gbit; 4GB DDR3L SDRAM; 16GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; -40 ... +85°C	MSC C10M-AL-E3930-2402011 PCBFTX	PV
70340	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Pentium N4200 quad-core 1.1/2.5GHz, 1MB L2, 6W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and eDP interfaces; Ethernet: Intel i210 Gbit; 8GB DDR3L SDRAM; 16GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; 0 ... +60°C;	MSC C10M-AL-N4200E-340101C PCBFTX	OR
70344	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Pentium N4200 quad-core 1.1/2.5GHz, 1MB L2, 6W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and LVDS interfaces; Ethernet: Intel i210 Gbit; 8GB DDR3L SDRAM; 32GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; 0 ... +60°C;	MSC C10M-AL-N4200E-350201C PCBFTX	OR
70342	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Celeron N3350 dual-core 1.1/2.4GHz, 2MB L2, 6W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and eDP interfaces; Ethernet: Intel i210 Gbit; 8GB DDR3L SDRAM; 32GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; 0 ... +60°C;	MSC C10M-AL-N3350E-350101C PCBFTX	OR
70338	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Celeron N3350 dual-core 1.1/2.4GHz, 2MB L2, 6W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and LVDS interfaces; Ethernet: Intel i210 Gbit; 8GB DDR3L SDRAM; 16GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; 0 ... +60°C;	MSC C10M-AL-N3350E-340201C PCBFTX	OR
70336	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom X5-E3950 quad-core 1.6/2.0GHz, 2MB L2, 12W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and eDP interfaces; Ethernet: Intel i210 Gbit; 8GB DDR3L ECC SDRAM; 32GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; -40 ... +85°C	MSC C10M-AL-E3950-3511011 PCBFTX	OR
70346	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom X5-E3930 dual-core 1.3/1.8GHz, 2MB L2, 6.5W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and LVDS interfaces; Ethernet: Intel i210 Gbit; 2GB DDR3L SDRAM; no eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; -40 ... +85°C	MSC C10M-AL-E3930-1N02011 PCBFTX	OR
70348	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom X5-E3930 dual-core 1.3/1.8GHz, 2MB L2, 6.5W TDP; Graphics: integrated Intel HD Gen 9; DP/HDMI and eDP interfaces; Ethernet: Intel i210 Gbit; 4GB DDR3L SDRAM; 16GB eMMC; HD audio; TPM; 2x SATA, 2x USB3/2, 6x USB2, 2x HS UART; 4x PCIe x1; -40 ... +85°C	MSC C10M-AL-E3930-2401011 PCBFTX	OR

Ordering Information for TRIA C10M-AL

*PV = Preferred variant; OR = on Request (in OEM quantities only)

Accessories

Cooling Solutions

Order No.	Description	Reference
1137520	Heatspreader for C10M-AL (Pentium/Celeron versions only). Single-piece aluminum profile, standoffs with M2.5 thread and thermopad for the thermal contact to SOC.	MSC C10M-AL-04 HSP-001
1137519	Heatspreader for C10M-AL (Pentium/Celeron versions only). Single-piece aluminum profile, standoffs without thread (2.7mm inner diameter) and thermopad for the thermal contact to SOC.	MSC C10M-AL-03 HSP-001
1137517	Heatspreader for C10M-AL (Atom versions only). Single-piece aluminum profile, standoffs with M2.5 thread and thermopad for the thermal contact to SOC.	MSC C10M-AL-02 HSP-001
1137518	Passive Heatsink for C10M-AL (Pentium/Celeron versions only), consisting of a single-piece aluminum pin cooler, standoffs without thread (2.7mm inner diameter) and thermopad for the thermal contact to SOC. With threaded mounting holes for an optional fan.	MSC C10M-AL-02 HSI-001
1137516	Heatspreader for C10M-AL (Atom versions only). Single-piece aluminum profile, standoffs without thread (2.7mm inner diameter) and thermopad for the thermal contact to SOC.	MSC C10M-AL-01 HSP-001
1137515	Passive Heatsink for C10M-AL (Atom versions only), consisting of a single-piece aluminum pin cooler, standoffs without thread (2.7mm inner diameter) and thermopad for the thermal contact to SOC. With threaded mounting holes for an optional fan.	MSC C10M-AL-01 HSI-001

Cooling Devices for TRIA C10M-AL

Starter Kits

Order No.	Description	Reference
70810	COM Express Type 10 Starterkit for C10M-AL modules with Intel Apollo Lake processors; uses the C10-MB-EV Mini-ITX platform for Type 10 modules; includes suitable Heatsinks for C10M-AL modules, 12V Power Supply and cable kit. Please order separately the COM Express C10M-AL module of your choice.	MSC C10-SK-AL-EV-KIT001

Starter Kits for TRIA C10M-AL

Tria Technologies GmbH
Industriestr. 16
76297 Stutensee
info@tria-technologies.com
tria-technologies.com

Copyright © 2024 Tria Technologies GmbH. All data is for information purposes only and is subject to change without notice. No guarantee for legal purposes is implied. Information in this document has been carefully checked, however, no responsibility for inaccuracies has to be assumed. All brand or product names may be trademarks and property of their respective owners.