

## TRIA C10M-ASL

Intel® Atom processors x7000RE/C Series



84 x 55

8 / 14 W

-45 - +85°C

**COM**   
**Express**



## Highlights

- Up to eight processing cores
- Power efficient processors, TDP 6 to 14W
- Integrated Intel UHD Gen.12 graphics, max. 32 executing units
- SKUs without GPU (headless) available
- Up to 16GB LPDDR5 SDRAM with IBECC
- Up to 256GB eMMC 5.1 Flash (optional)
- 2x SATA-III interface (6Gbps)
- DisplayPort/HDMI/DVI interface
- LVDS/Embedded DisplayPort interface
- Dual Independent Display support
- MIPI-CSI Camera Interface
- 4x PCI Express x1 Gen. 3
- Two USB 3.2 Gen 2 (10Gb/s) and eight USB 2.0 interfaces
- One Gb Ethernet port (Intel® i226)
- TSN, TCC support
- UART, SPI, I2C, SMBus
- High Definition Audio (HD-A)
- UEFI Firmware
- Trusted Platform Module TPM 2.0

# COM Express Type 10



## Technical Data

<b>Technology</b>	x86
<b>Formfactor</b>	COM Express Mini
<b>CPU</b>	Intel Atom® x7835RE, octa-core, 1.3GHz, 32EU, TCC, 12W, IUC, ET Intel Atom® x7433RE, quad-core, 1.5GHz, 32EU, TCC, 9W, IUC, ET Intel Atom® x7213RE, dual-core, 2.0GHz, 16EU, TCC, 9W, IUC, ET Intel Atom® x7211RE, dual-core, 1.0GHz, 16EU, TCC, 6W, IUC, ET Intel Atom® x7405C, quad-core, 2.2GHz, no GPU, TCC, 12W, EUC, CT Intel Atom® x7203C, dual-core, 2.0GHz, no GPU, TCC, 9W, EUC, CT Note: base frequency shown, other frequencies supported ET- Extended temperature CT- Commercial temperature EUC - Intel Embedded Use Conditions IUC - Intel Industrial Use Conditions
<b>Chipset</b>	SoC
<b>RAM</b>	Up to 16GB LPDDR5 SDRAM, up to 4800MT/s, IB ECC
<b>Flash</b>	On-board eMMC mass storage option, scalable capacity up to 256GB
<b>Storage Interfaces</b>	2x SATA 6Gb/s
<b>USB</b>	2x USB 3.2 Gen 2 (10Gb/s) 8 x USB 2.0
<b>Serial Interfaces</b>	Two UARTS
<b>Bus Interfaces</b>	4x PCI Express x1 Gen 3 (1x PCI Express x4 Gen 3 on request) LPC bus (Low Pin Count bus; no DMA support) (eSPI on request)
<b>Display Controller</b>	Integrated Intel UHD Graphics (Gen12) Up to 32 execution units (EU)  SKUs without GPU (headless) available
<b>Display Interfaces</b>	Two independent displays supported: 1x Digital Display Interface (DP, HDMI) 1x Embedded DisplayPort (on variants without LVDS only) LVDS 24bit, single-channel (not on all variants); max. 1920 x 1200 @ 60Hz
<b>Network Interface</b>	10/100/1000Base-TX, 2.5G <sup>2</sup> based on Intel i226 <sup>2</sup> Available bandwidths depending on carrier design
<b>Audio Interface</b>	High Definition Audio
<b>Security Device</b>	TPM 2.0
<b>Miscellaneous</b>	Watchdog Timer: Initiates system reset RTC battery: external System Monitoring: voltage, temperature, system fan GPIO, GSPIC (COM.0 Rev. 3.1)
<b>Feature Highlights</b>	Type 10 pin-out
<b>Firmware</b>	AMI Aptio UEFI
<b>OS Support</b>	Windows 10 IoT Enterprise 2021 LTSC Yocto Project (LTS kernel 2021)
<b>Power Requirement</b>	Voltage: +5V to +20V, +5V Stby optional  Power Consumption: 8W to 14 W (typ., variant dependent)

# COM Express Type 10



<b>Environment</b>	Ambient Temperature: -40° ... 85°C (operating) -25° ... 85°C (storage)  Humidity: 5 ... 95% (operating, non-condensing), 5 ... 95% (storage, non-condensing)
<b>Dimensions</b>	84 x 55mm
<b>Certificates</b>	UL / CE
<b>Cooling</b>	Passive heat sink Heat spreader with threaded or non-threaded standoffs
<b>Carrier</b>	Small carrier board (Mini-ITX) as part of a starter kit

Technical Data for TRIA C10M-ASL

# COM Express Type 10



## Order Reference

Order No.	Description	Reference	Status*
114730	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7835RE octal-core 1.3GHz, 12W TDP; Graphics: Intel UHD; DP/HDMI and LVDS interfaces; 32EU; Ethernet: 1Gbit; 16GB LPDDR5 SDRAM, in-band ECC; 32GB eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; -40 ... +85°C (recommended for 24/7 operation)	MSC C10M-ASL-x7835RE-45201I PCBFTX	PV
114762	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7835RE octal-core 1.3GHz, 12W TDP; Graphics: Intel UHD; DP/HDMI and eDP interfaces; 32EU; Ethernet: 1Gbit; 8GB LPDDR5 SDRAM, in-band ECC; 16GB eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; -40 ... +85°C (recommended for 24/7 operation)	MSC C10M-ASL-x7835RE-34101I PCBFTX	PV
114764	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7433RE quad-core 1.5GHz, 9W TDP; Graphics: Intel UHD; DP/HDMI and LVDS interfaces; 32EU; Ethernet: 1Gbit; 8GB LPDDR5 SDRAM, in-band ECC; 16GB eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; -40 ... +85°C (recommended for 24/7 operation)	MSC C10M-ASL-x7433RE-34201I PCBFTX	OR
114766	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7433RE quad-core 1.5GHz, 9W TDP; Graphics: Intel UHD; DP/HDMI and eDP interfaces; 32EU; Ethernet: 1Gbit; 8GB LPDDR5 SDRAM, in-band ECC; 16GB eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; -40 ... +85°C (recommended for 24/7 operation)	MSC C10M-ASL-x7433RE-34101I PCBFTX	PV
114768	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7213RE dual-core 2.0GHz, 9W TDP; Graphics: Intel UHD; DP/HDMI and LVDS interfaces; EU; Ethernet: 1Gbit; 8GB LPDDR5 SDRAM, in-band ECC; 16GB eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; -40 ... +85°C (recommended for 24/7 operation)	MSC C10M-ASL-x7213RE-34201I PCBFTX	PV
114770	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7213RE dual-core 2.0GHz, 9W TDP; Graphics: Intel UHD; DP/HDMI and eDP interfaces; EU; Ethernet: 1Gbit; 4GB LPDDR5 SDRAM, in-band ECC; 16GB eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; -40 ... +85°C (recommended for 24/7 operation)	MSC C10M-ASL-x7213RE-24101I PCBFTX	OR
114772	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7211RE dual-core 1.0GHz, 6W TDP; Graphics: Intel UHD; DP/HDMI and LVDS interfaces; EU; Ethernet: 1Gbit; 4GB LPDDR5 SDRAM, in-band ECC; 16GB eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; -40 ... +85°C (recommended for 24/7 operation)	MSC C10M-ASL-x7211RE-24201I PCBFTX	PV
114726	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7211RE dual-core 1.0GHz, 6W TDP; Graphics: Intel UHD; DP/HDMI and eDP interfaces; EU; Ethernet: 1Gbit; 4GB LPDDR5 SDRAM, in-band ECC; no eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; -40 ... +85°C (recommended for 24/7 operation)	MSC C10M-ASL-x7211RE-2N101I PCBFTX	PV

# COM Express Type 10



Order No.	Description	Reference	Status*
114728	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7203C dual-core 2.0GHz, 9W TDP; Graphics: Intel UHD; DP/HDMI and no interfaces; noEU; Ethernet: 1Gbit; 4GB LPDDR5 SDRAM, in-band ECC; 16GB eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; 0 ... +60°C	MSC C10M-ASL-x7203C-24N01C PCBFTX	OR
115012	COM Express Type 10 Mini module (84mm x 55mm); CPU: Intel Atom x7405C quad-core 2.2GHz, 12W TDP; Graphics: Intel UHD; DP/HDMI and no interfaces; noEU; Ethernet: 1Gbit; 8GB LPDDR5 SDRAM, in-band ECC; 16GB eMMC; HD audio; TPM 2.0; 2x SATA, 2x USB3/2, 6x USB2, 2x UART; 4x PCIe x1; 0 ... +60°C	MSC C10M-ASL-x7405C-34N01C PCBFTX	OR

Ordering Information for TRIA C10M-ASL \*PV = Preferred variant; OR = on Request (in OEM quantities only)

## Accessories

### Cooling Solutions

Order No.	Description	Reference
110195	Passive Heatsink for C10M-ALN and C10M-ASL (all versions), consisting of a single-piece aluminum pin cooler, standoffs without thread (2.7mm inner diameter) and thermopad for the thermal contact to SOC. With threaded mounting holes for an optional fan.	MSC C10M-ALN-01 HSI-001
110196	Heatspreader for C10M-ALN and C10M-ASL (all versions). Single-piece aluminum profile, standoffs without thread (2.7mm inner diameter) and thermopad for the thermal contact to SOC.	MSC C10M-ALN-01 HSP-001
110197	Heatspreader for C10M-ALN and C10M-ASL (all versions). Single-piece aluminum profile, standoffs with M2.5 thread and thermopad for the thermal contact to SOC.	MSC C10M-ALN-02 HSP-001

Cooling Devices for TRIA C10M-ASL/ALN

### Carrier Board

Order No.	Description	Reference
67293	COM Express Type 10 Evaluation Carrier Board with PCI Express x4 slot, USB 3.0/2.0, GbE, SATA, DisplayPort, eDP/LVDS and HD audio interfaces; Mini PCI Express socket, SD card slot, ATX power connector and single 12V power jack. Dimensions: 170mm x 170mm (Mini-ITX form factor)	MSC C10-MB-EV-001 PCBFTX

Carrier Options TRIA C10M-ASL/ALN

### Starter Kits

Order No.	Description	Reference
115022	COM Express Type 10 Starterkit for all C10M-ALN and C10M-ASL modules; contains the C10-MB-EV platform for Type 10 modules (Mini-ITX format); includes suitable Heatspreader for C10M-ALN/-ASL modules, 12V power supply and cable kit	MSC C10-SK-ALN-ASL-EV-KIT001 BRDFTX

Starter Kits for TRIA C10M-ALN/ASL

# COM Express Type 10



Tria Technologies GmbH  
Industriestr. 16  
76297 Stutensee  
info@tria-technologies.com  
tria-technologies.com

Copyright © 2024 Tria Technologies GmbH. All data is for information purposes only and is subject to change without notice. No guarantee for legal purposes is implied. Information in this document has been carefully checked, however, no responsibility for inaccuracies has to be assumed. All brand or product names may be trademarks and property of their respective owners.