

AVNET[®]
EMBEDDED

SIMPLE PLUS OPEN FRAME

GEO-070R1B1000C500-I-MBVM-PG018-G65

avnet.com/embedded

GEO-070R1B1000C500-I-MBVM-PG018-G65

1 YEAR WARRANTY

7" OPEN FRAME

CERTIFICATIONS : CE , FCC

DESCRIPTION

Avnet Embedded Open Frame provides the answer, handling the entirety of the display design for you and building optimized solutions based on modular combinations of standard displays and TFT multi-touch assemblies. Delivered as a pre-assembled unit that incorporates the power supply, touch controller and other components, an Open Frame is built into a no-bezel metal housing for simple integration into your solution. All-in-one computers are a variation on this approach that add the processor, memory and other components to create a full system. Both allow for flexible mounting options to support an open-ended variety of implementations.



Advantages

Six capabilities of Avnet integrated Open Frames and AIO that mean successful solution development

Compatibility and Ease of Integration



- Integrate with multiple generations and standards of equipment
- Implement in environments with space, thermal and other constraints
- Customize easily for individual solution requirements

Optimized Human-Machine Interaction



- Tailor display to size, aspect ratio and resolution needed
- Control input without external devices such as keyboard or mouse
- Support use by operators with gloved hands

Rugged Durability and Longevity



- Offer dependability of low failure rate and long lifespan
- Operate in extremes of dust, heat, moisture, shock and vibration
- Protect displays against glare, scratches, fingerprints and vibration

Flexible Mounting and Customizability



- Specify options such as processor, video card and interfaces
- Mount in enclosure, on equipment, on panel or using VESA
- Meet constraints with fanless install and solid state storage

Long-Term Cost-Effectiveness



- Eliminate one-time-engineering costs to develop custom display
- Simplify ongoing maintenance with Avnet-engineered solution
- Scale system performance with upgradeability when needed

Low Power Consumption and Noise



- Tailor power/performance balance with broad choice of components
- Reduce operating noise by eliminating exhaust fans
- Avoid pulling in dust and contaminants with passive cooling designs

Technical Data

GEO-070R1B1000C500-I-MBVM-PG018-G65

Panel Data	
Panel Size	7"
Display Ratio	16:10
Resolution	800(H) x 480 (V)
Panel type	a-Si TFT, Transmissive, Normally white, TN
Color	16.7M
Brightness (nits)	1000cd/m ²
Contrast	500:1
View Angle	70/70/ 70/ 60/ (L/R/T/B) CR \geq 10
Backlight	WLED
Life (hrs)	50000hours
Touch Screen	
Type	Capacitive touch screen
Touch points	5points
Touch Screen Structure	Glass+Glass(G+G); anti UV between cover glass and sensor
Cover glass	1.8mm;black
Input Method	Finger or Cap. Stylus
Bonding with TFT	Air bonding
Hardness	6H


SIMPLE PLUS OPEN FRAME

Technical Data

GEO-070R1B1000C500-I-MBVM-PG018-G65

Specification	
Material	Metal material(black)
Installation	Wall Mounted
Speaker	NONE
Interface	1*HDMI;1*USB(TOUCH);1*VGA;1*DC-IN;1*DP
Menu Language	Multilingual
Signal input	HDMI/DP/VGA
KEY FUNCTION	POWER,MENU,LEFT,RIGHT,EXIT
Power Supply	DC12V~DC24V
Operating condition:	Temperature:-20-70 degrees Celsius ; Humidity:20-80%
Storage condition:	Temperature: -30 to +80 degrees Celsius; Humidity: 20%-80%
Waterproof grade	IP65 on front
Certificate	CE,FCC,ROHS


SIMPLE PLUS OPEN FRAME



Avnet Embedded
MSC Technologies GmbH
Industriestr. 16
76297 Stutensee

embedded.avnet.com

SIMPLE PLUS OPEN FRAME



Avnet Embedded
MSC Technologies GmbH
Industriestr. 16
76297 Stutensee

embedded.avnet.com