


TRIA C6C-AL

Intel® Atom™ E3900 Series / Pentium® / Celeron® SOC



95 x 95

7 / 14W

-40-+85

COM 
Express



Highlights

- Intel Atom E3950 quad-core 1.6/2.0GHz, 12W
- Intel Atom E3940 quad-core 1.6/1.8GHz, 9.5W
- Intel Atom E3930 dual-core 1.3/1.8GHz, 6.5W
- Intel Pentium N4200 quad-core 1.1/2.5GHz, 6W
- Intel Celeron N3350 dual-core 1.1/2.4GHz, 6W
- Integrated Intel Gen. 9 HD graphics
- Up to 8GB DDR3L SDRAM, dual-channel
- Two SATA 6Gb/s mass storage interfaces
- MicroSD card socket, eMMC option
- DisplayPort/HDMI/DVI interface
- LVDS/Embedded DisplayPort interface
- Three independent displays supported
- DirectX 12, OpenGL 4.3, OpenCL 2.0
- Dual MIPI-CSI (option)
- Four USB 3.0/2.0 and four USB 2.0 interfaces
- Two high-speed UARTs
- Up to five PCI Express™ x1 lanes
- UEFI Firmware
- Trusted Platform Module
- Extended temperature variants

COM Express Type 6



Technical Data

Technology	x86
Formfactor	COM Express Compact
CPU	Intel Atom E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 12W Intel Atom E3940 quad-core 1.6/1.8GHz, 12 EU GFX, 9.5W Intel Atom E3930 dual-core 1.3/1.8GHz, 12 EU GFX, 6.5W Intel Pentium N4200 quad-core 1.1/2.5GHz, 18 EU GFX, 6W Intel Celeron N3350 dual-core 1.1/2.4GHz, 12 EU GFX, 6W
Chipset	SOC
RAM	2x 204-pin SO-DIMM socket for up to 2x 4 GB (dual channel operation) or 1x 8 GB (single channel operation); DDR3L-1866
Flash	MicroSD card socket eMMC option
Storage Interfaces	Up to 2x SATA 6Gb/s
USB	4x USB 3.0/2.0, 4x USB 2.0
Bus Interfaces	Up to 5x PCI Express x1, LPC bus (Low Pin Count bus; no DMA support)
Display Controller	Integrated Intel HD graphics Gen. 9 Up to 18 execution units (EU) DirectX 12.0, OpenGL 4.3, OpenCL 2.0 Full Profile; MPEG2, H.264 (L5.2), VC-1, WMV9, VP8, JPEG/MJPEG, H.265 (HEVC), VP9, MVC
Display Interfaces	Three independent displays supported: 2x Digital Display Interface (DP 1.2a (4096 x 2160 @ 60Hz), HDMI 1.4b (3840 x 2160 @ 30Hz) 1x Embedded DisplayPort 1.3 (on variants without LVDS only); 4096 x 2160 @ 60Hz, LVDS 24bit, dual-channel (not on all variants); 1920 x 1200 @ 60Hz
Network Interface	10/100/1000Base-T (Intel i210) or 10/100/1000Base-T (Intel i225) Note: see product descriptions for supported network controller
Audio Interface	High Definition Audio
Security Device	TPM 2.0
Miscellaneous	Watchdog Timer: Initiates system reset, programmable Fan Supply: 4-pin header for CPU fan, PWM speed controlled and PWM speed control for system fan supported RTC battery: external System Monitoring: voltage, temperature, CPU fan, system fan Dual MIPI-CSI (on feature connector, optional)
Feature Highlights	Type 6 pin-out
Firmware	AMI Aptio UEFI
OS Support	Windows 10 (embedded) BSP for Linux on request EAPI (HW Programming Interface)
Power Requirement	Wide range input +5 ... +20V, 5V Stby optional, 7 W to 14 W (typ.)

COM Express Type 6



Environment	Ambient Temperature; 0° ... 60°C (operating), -25° ... 85°C (storage) Extended temp. variants: -40 ... +85°C (operating) Humidity: 5 ... 95% (operating, non-condensing), 5 ... 95% (storage, non-condensing)
Dimensions	95mm x 95mm
Certificates	UL / CE
Cooling	Passive heat sink Active heat sink with fan Heat spreader with threaded or non-threaded standoffs
Carrier	Small carrier board (Mini-ITX) as part of a starter kit; Evaluation board in ATX form factor

Technical Data for TRIA C6C-AL

COM Express Type 6



Order Reference

Order No.	Description	Reference	Status*
69668	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3930 dual-core 1.3/1.8GHz, 12 EU GFX, 6W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C (recommended for 24/7 use cases)	MSC C6C-AL-E3930- NN2611 PCBFTX	OR
69670	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3940 quad-core 1.6/1.8GHz, 12 EU GFX, 9W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C (recommended for 24/7 use cases)	MSC C6C-AL-E3940- NN2611 PCBFTX	OR
85980	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3940 quad-core 1.6/1.8GHz, 12 EU GFX, 9W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 3x PCIe x1; TPM; no microSD, no MIPI-CSI; 2x socket for DDR3L SO-DIMM. -40...+85°C (recommended for 24/7 use cases)	MSC C6C-AL-E3940- NN2011 PCBFTX	OR
69672	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 12W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C (recommended for 24/7 use cases)	MSC C6C-AL-E3950- NN2611 PCBFTX	OR
86022	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 13W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 3x PCIe x1; TPM; no microSD, no MIPI-CSI; 2x socket for DDR3L SO-DIMM. -40...+85°C (recommended for 24/7 use cases)	MSC C6C-AL-E3950- NN2011 PCBFTX	OR

COM Express Type 6



Order No.	Description	Reference	Status*
69640	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Celeron N3350 dual-core 1.1/2.3GHz, 12 EU GFX, 6W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM.	MSC C6C-AL-N3350E- NN261C PCBFTX	OR
69662	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Pentium N4200 quad-core 1.1/2.5GHz, 18 EU GFX, 6W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM.	MSC C6C-AL-N4200E- NN261C PCBFTX	OR
69674	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3930 dual-core 1.3/1.8GHz, 12 EU GFX, 6W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; eDP; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C (recommended for 24/7 use cases)	MSC C6C-AL-E3930- NN161I PCBFTX	OR
69676	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3940 quad-core 1.6/1.8GHz, 12 EU GFX, 9W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; eDP; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C (recommended for 24/7 use cases)	MSC C6C-AL-E3940- NN161I PCBFTX	OR
69678	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 12W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; eDP; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C (recommended for 24/7 use cases)	MSC C6C-AL-E3950- NN161I PCBFTX	OR
69664	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Celeron N3350 dual-core 1.1/2.3GHz Burst, 12 EU GFX, 6W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; eDP; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM.	MSC C6C-AL-N3350E- NN161C PCBFTX	OR
69666	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Pentium N4200 quad-core 1.1/2.5GHz, 18 EU GFX, 6W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; eDP; Ethernet: Intel i210 Gbit; HD audio; 2x SATA, 4x USB3, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM.	MSC C6C-AL-N4200E- NN161C PCBFTX	OR

COM Express Type 6



Order No.	Description	Reference	Status*
91850	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3930 dual-core 1.3/1.8GHz, 12 EU GFX, 5.5W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; no +5V STDBY; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C	MSC C6C-AL-E3930- NN2E11 PCBFTX	OR
91862	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3940 quad-core 1.6/1.8GHz, 12 EU GFX, 9W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; no +5V STDBY; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C	MSC C6C-AL-E3940- NN2E11 PCBFTX	OR
91868	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 13W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; no +5V STDBY; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C	MSC C6C-AL-E3950- NN2E11 PCBFTX	OR
91864	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 13W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; eDP; Ethernet: Intel i210 Gbit; no +5V STDBY; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C	MSC C6C-AL-E3950- NN1E11 PCBFTX	OR
91866	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 13W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i210 Gbit; no +5V STDBY; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 3x PCIe x1; TPM; no microSD, no MIPI-CSI; 2x socket for DDR3L SO-DIMM. -40...+85°C	MSC C6C-AL-E3950- NN2811 PCBFTX	OR
95841	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3930 dual-core 1.3/1.8GHz, 12 EU GFX, 5.5W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i225 Gbit; no +5V STDBY; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C	MSC C6C-AL-E3930- NN2V11 PCBFTX	OR

COM Express Type 6



Order No.	Description	Reference	Status*
96003	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3940 quad-core 1.6/1.8GHz, 12 EU GFX, 9W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i225 Gbit; no +5V STDBY; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C	MSC C6C-AL-E3940- NN2V11 PCBFTX	OR
96007	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 13W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i225 Gbit; no +5V STDBY; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 5x PCIe x1; TPM; 2x socket for DDR3L SO-DIMM. -40...+85°C	MSC C6C-AL-E3950- NN2V11 PCBFTX	OR
96005	COM Express Type 6 Compact module (95mm x 95mm); CPU: Intel Atom E3950 quad-core 1.6/2.0GHz, 18 EU GFX, 13W Graphics: integrated Intel HD Gen 9; 2x DP/HDMI; LVDS; Ethernet: Intel i225 Gbit; no +5V STDBY; HD audio; 2x SATA, 4x USB3/2, 4x USB2, 3x PCIe x1; TPM; no microSD, no MIPI-CSI; 2x socket for DDR3L SO-DIMM. -40...+85°C	MSC C6C-AL-E3950- NN2P11 PCBFTX	OR

Ordering Information for TRIA C6C-AL

*PV = Preferred variant; OR = on Request (in OEM quantities only)

Accessories

Carrier Options

Order No.	Description	Reference
67295	COM Express Type 6 Evaluation Carrier Board with PCI Express x4/x16 slot, USB 3.0/2.0, GbE, SATA, DisplayPort, eDP/LVDS, VGA and HD audio interfaces; Mini PCI Express socket, SD card slot, ATX power connector and single 12V power jack. Dimensions: 170mm x 170mm (Mini-ITX form factor)	MSC C6-MB-EV-001 PCBFTX
41857	COM Express Type 6 Evaluation Carrier Board with various PCI Express x1, x4 and x16 slots, USB 3.0/2.0, GbE, SATA, DisplayPort, HDMI, LVDS, eDP, VGA, HD audio interfaces; mSATA and Mini PCI Express sockets, POST code display, ATX power connector. Dimensions: 305 x 244 mm (ATX form factor)	MSC C6-MB-EVA PCBFTX

Carrier Board TRIA C6B-KLH/CFLR/CFLH/TRIA C6C-TLU/WLU/KLU/EL/AL/BT

Cooling Solutions

Order No.	Description	Reference
1135097	Active Heatsink for C6C-AL (Atom variants only), consisting of a single-piece aluminum profile with fins, standoffs without thread (2.7mm inner diameter), screws and thermopads for the thermal contact to SOC. PWM fan 80x80x15mm.	MSC C6C-AL-01 HSF-001
1135098	Passive Heatsink for C6C-AL (Atom versions only), consisting of a single-piece aluminum profile with fins, standoffs without thread (2.7mm inner diameter), screws and thermopad for the thermal contact to SOC.	MSC C6C-AL-01 HSI-001
1135099	Heatspreader for C6C-AL (Atom versions only). Single-piece aluminum profile with standoffs without thread (2.7mm inner diameter), screws and thermopad for the thermal contact to SOC.	MSC C6C-AL-01 HSP-001
1135205	Active Heatsink for C6C-AL (Pentium/Celeron variants only), consisting of a single-piece aluminum profile with fins, standoffs without thread (2.7mm inner diameter), screws and thermopads for the thermal contact to SOC. PWM fan 80x80x15mm.	MSC C6C-AL-02 HSF-001
1135206	Passive Heatsink for C6C-AL (Pentium/Celeron versions only), consisting of a single-piece aluminum profile with fins, standoffs without thread (2.7mm inner diameter), screws and thermopad for the thermal contact to SOC.	MSC C6C-AL-02 HSI-001
1135100	Heatspreader for C6C-AL (Atom versions only). Single-piece aluminum profile with threaded standoffs (M2.5), screws and thermopad for the thermal contact to SOC.	MSC C6C-AL-02 HSP-001
1135207	Heatspreader for C6C-AL (Pentium/Celeron versions only). Single-piece aluminum profile with standoffs without thread (2.7mm inner diameter), screws and thermopad for the thermal contact to SOC.	MSC C6C-AL-03 HSP-001
1135208	Heatspreader for C6C-AL (Pentium/Celeron versions only). Single-piece aluminum profile with threaded standoffs (M2.5), screws and thermopad for the thermal contact to SOC.	MSC C6C-AL-04 HSP-001

Cooling Devices for TRIA C6C-AL

Memory Options

Order No.	Description	Reference
79964	4GB SoDimm, DDR3L-1866, 512Mx8 based, wide Temp.	MOD SODIMM DDR3 4GB PC3-14900 CL13 1B
79965	8GB SoDimm, DDR3L-1866, 512Mx8 based, wide Temp.	MOD SODIMM DDR3 8GB PC3-14900 CL13 2B

Memory Options for TRIA C6C-AL. Please contact your Tria Technologies representative for information on supported memory options.

Starter Kits

Order No.	Description	Reference
70503	COM Express Type 6 Starter kit for all C6C-AL modules; uses the C6-MB-EV platform for Type 6 modules in Mini-ITX format; includes 2x DDR3L memory modules, suitable Heatsinks for C6C-AL modules and 12V Power Supply with power cable. Please order separately the COM Express C6C-AL module of your choice.	MSC C6-SK-AL-EV-KIT001

Starter Kits for TRIA C6C-AL

Tria Technologies GmbH
Industriestr. 16
76297 Stutensee
info@tria-technologies.com
tria-technologies.com

Copyright © 2024 Tria Technologies GmbH. All data is for information purposes only and is subject to change without notice. No guarantee for legal purposes is implied. Information in this document has been carefully checked, however, no responsibility for inaccuracies has to be assumed. All brand or product names may be trademarks and property of their respective owners.