



AVNET<sup>®</sup>  
EMBEDDED

## SIMPLE PLUS OPEN FRAME

GEO-215R9B250C3000-I-PBVM-PG018-G

[avnet.com/embedded](http://avnet.com/embedded)

**GEO-215R9B250C3000-I-PBVM-PG018-G**

*1 YEAR WARRANTY*

21.5" OPEN FRAME

*CERTIFICATIONS : CE , FCC*

## DESCRIPTION

Avnet Embedded Open Frame provides the answer, handling the entirety of the display design for you and building optimized solutions based on modular combinations of standard displays and TFT multi-touch assemblies. Delivered as a pre-assembled unit that incorporates the power supply, touch controller and other components, an Open Frame is built into a no-bezel metal housing for simple integration into your solution. All-in-one computers are a variation on this approach that add the processor, memory and other components to create a full system. Both allow for flexible mounting options to support an open-ended variety of implementations.



## Advantages

Six capabilities of Avnet integrated Open Frames and AIO that mean successful solution development

**Compatibility and Ease of Integration**



- Integrate with multiple generations and standards of equipment
- Implement in environments with space, thermal and other constraints
- Customize easily for individual solution requirements

**Optimized Human-Machine Interaction**



- Tailor display to size, aspect ratio and resolution needed
- Control input without external devices such as keyboard or mouse
- Support use by operators with gloved hands

**Rugged Durability and Longevity**



- Offer dependability of low failure rate and long lifespan
- Operate in extremes of dust, heat, moisture, shock and vibration
- Protect displays against glare, scratches, fingerprints and vibration

**Flexible Mounting and Customizability**



- Specify options such as processor, video card and interfaces
- Mount in enclosure, on equipment, on panel or using VESA
- Meet constraints with fanless install and solid state storage

**Long-Term Cost-Effectiveness**



- Eliminate one-time-engineering costs to develop custom display
- Simplify ongoing maintenance with Avnet-engineered solution
- Scale system performance with upgradeability when needed

**Low Power Consumption and Noise**



- Tailor power/performance balance with broad choice of components
- Reduce operating noise by eliminating exhaust fans
- Avoid pulling in dust and contaminants with passive cooling designs

## Technical Data

### GEO-215R9B250C3000-I-PBVM-PG018-G


Panel Data	
Panel Size	21.5"
Display Ratio	16:9
Resolution	1920(H) x 1080 (V)/60 Hz
Color	16.7 Million colors
Brightness (nits)	250cd/m <sup>2</sup>
Contrast	3000:1
View Angle	89/ 89 / 89 / 89 degree
Response Time	14(ms)
Backlight	LED
Life (hrs)	50000hours
Touch Screen	
Type	Capacitive touch screen
Touch points	10 points
Touch Screen Structure	Glass+Glass(G+G);
Cover glass	1.8mm;black
Input Method	Finger or Cap. Stylus
Bonding	SCA
Surface Hardness	7H

## Technical Data

### GEO-215R9B250C3000-I-PBVM-PG018-G

Specification	
Material	Plastic material (back)
Installation	Desktop, VESA(100MM*100MM)
HDMI Input	Support 1080i HDMI
VGA Input	Standard VGA (15 pin D-SUB RGB) input(Optional)
OSD	POWER/ENTER/UP/DOWN/LEFT/RIGHT/EXIT
Earphone Input	Support
Speaker	1W*2
Language	English, Germany, French, Spanish, Russian and Others
I/O Interface	1*HDMI;1*VGA(Optional);1*DC INPUT USB 2.0 TYPE B*1 USB 2.0 TYPE A*3
Power Supply	DC 12V 5A
Line frequency	30-80KHZ
field frequency	56-75HZ
Operating condition:	temperature:0-40 degrees Celsius ; Humidity:10-90%
Storage condition:	temperature: -20 to +50 degrees Celsius; Humidity: 10%-90%

# SIZE



**Avnet Embedded**  
MSC Technologies GmbH  
Industriestr. 16  
76297 Stutensee

[embedded.avnet.com](http://embedded.avnet.com)