


MSC SM2S-IMX8MLC

NXP[®] i.MX 8M Mini
Arm[®] Cortex[®]-A53



82 x 50 mm

2-5 W

-40 +85



Description

The flexible MSC SM2S-IMX8MLC SMARC 2.1 module family is highly scalable and equipped with i.MX 8M Mini Application Processors, manufactured by NXP using 14nm FinFET process technology. The module integrates single-, dual- and quad-core Arm Cortex-A53 processors with up to 1.8 GHz, an Arm Cortex-M4 real-time processor and an efficient multimedia 2D/3D graphics processing unit (GPU). The thermal design power (TDP) ranges from 2 W to 5 W.

MSC SM2S-IMX8MLC offers cost-effective DDR4 memory technology, combined with up to 64GB eMMC Flash memory. Various interfaces for embedded applications such as Gigabit Ethernet, PCI Express, USB 2.0, dual-channel LVDS or MIPI-DSI and MIPI CSI-2 for connecting a camera are available.

The design deliberately omits features such as SD card socket, second Gigabit Ethernet port, CAN interfaces or on-board WiFi/Bluetooth module to allow single-sided assembly of the board.

The module is compliant with the new SMARC 2.1 standard, allowing easy integration with SMARC baseboards. For evaluation and design-in of the SM2S-IMX8MLC module, MSC provides a development platform and a starter kit. Support for Linux is available (Android support on request).

Highlights

- Single, Dual or Quad core Arm Cortex-A53 Applications Processor up to 1.8GHz
- Arm Cortex-M4 Real Time Processor up to 400MHz
- Vivante multimedia 2D/3D Graphics Processor
- Up to 1080p60 H.265 decode / H.264 encode
- Up to 4GB DDR4 SDRAM at 2400 MT/s
- Up to 64GB eMMC Flash
- Dual-channel LVDS / MIPI-DSI x4 (optional)
- MIPI CSI-2 Camera Interface
- PCI Express x1 Gen. 2
- Up to 4x USB 2.0 Host interface
- 1x USB 2.0 Host/Device interface
- 1x Gigabit Ethernet
- 1x MMC/SD/SDIO interface
- 2x I2S Audio Interface
- 14x GPIO
- UART, SPI, I2C
- SMARC 2.1 Compliant

Technical Data - MSC SM2S-IMX8MLC

Technology	Arm
Formfactor	SMARC Short Size
CPU	<p>NXP i.MX 8M Mini Arm Cortex-A53 Applications Processor</p> <ul style="list-style-type: none"> - i.MX 8M Mini Solo, single-core, 1.6 - 1.8GHz - i.MX 8M Mini Dual, dual-core, 1.6 - 1.8GHz - i.MX 8M Mini Quad, quad-core, 1.6 - 1.8GHz - i.MX 8M Mini SoloLite, single-core, 1.6 - 1.8GHz - i.MX 8M Mini DualLite, dual-core, 1.6 - 1.8GHz - i.MX 8M Mini QuadLite, quad-core, 1.6 - 1.8GHz <p>Arm Cortex-M4 Real Time Processor at 400MHz</p>
Chipset	SOC
RAM	Up to 4GB 2400MT/s DDR4 SDRAM, soldered, no ECC
Flash	Up to 64GB eMMC Flash QSPI NOR Flash (optional)
Storage Interfaces	1x MMC/SD/SDIO
USB	1x USB 2.0 Host/Client, 4x USB 2.0 Host or 1x USB 2.0 Host/Client, 1x USB 2.0 Host (optional)
Serial Interfaces	2x UART with 2-wire hand shake 2x UART w/o hand shake
Bus Interfaces	1x PCI Express x1 Gen.2 lanes 4x I2C up to 400 Kbit/s 2x SPI (with two chip selects)
Display Controller	<p>Vivante GC NanoUltra 3D Graphics Processing Unit (GPU) 3D Graphics Acceleration, 1 shader, 6.4 GFLOPS OpenGL ES 1.0, 2.0</p> <p>Video Processing Unit with hardware support for 1080p60 HEVC H.265, VP9, H.264, VP8 decode 1080p60 H.264, VP8 encode only available on i.MX 8M Mini Solo/Dual/Quad</p>
Display Interfaces	<p>Dual-channel LVDS interface, 18 or 24 bit (up to 1920x1080); also usable as one single-channel LVDS interface (up to 1366x768) or</p> <p>MIPI-DSI Display Interface, 4 lanes, up to 1920x1080 @ 60fps (optional)</p>
Network Interface	1x 10/100/1000BASE-T Ethernet
Audio Interface	2x I2S Audio
Security Device	<p>Advanced Security, Safety, and Reliability integrated in the SOC</p> <p>Trusted Platform Module (TPM) 2.0 (optional)</p>

Miscellaneous	Watchdog Timer for system reset (programmable, 1s ... 600s) High accuracy RTC 14x GPIO, configurable as input or output 64kbit ID EEPROM on I2C bus MIPI CSI-2 camera interface (CSI0, 2 lane) or MIPI CSI-2 camera interface (CSI1, 4-lane)
Feature Highlights	SMARC 2.1 compatible
OS Support	Linux Board Support Package Android Board Support Package (on request)
Power Requirement	Power Supply +5V +/-5%, 5V Standby Power Consumption 2-5 W typ. (depending on CPU and optional features)
Environment	Temperature Range: 0°C ... +70°C operating commercial -40°C ... +85°C operating extended -40°C ... +85°C storage Humidity: 5 ... 95% (operating, non condensing) 5 ... 95% (storage, non-condensing)
Dimensions	82 x 50 mm
Certificates	UL / CE
Cooling	Heatspreader
Carrier	MSC SM2-MB-EP1 MSC SM2-MB-EP5

Order Reference - MSC SM2S-IMX8MLC

Order Number	Description	Reference	Cat*
92474	SMARC module based on NXP i.MX 8M Mini Quad, Quad-Core Cortex-A53 processor at 1.6GHz, 2GB DDR4, 16GB eMMC Flash, GbE LAN, PCIe, 4x USB2.0 Host, 1x USB2.0 Host/Device, LVDS, MIPI CSI-2 Camera input (CSI1); industrial temperature -40...+85°C	MSC SM2S-IMX8MLC-QC-14N0200I PCBFTX	PV
115240	SMARC module based on NXP i.MX 8M Mini Quad, Quad-Core Cortex-A53 processor at 1.6GHz, 4GB DDR4, 16GB eMMC Flash, 1x GbE LAN, 1x PCIe, 1x USB2.0 Host, 1x USB2.0 Host/Device, LVDS, MIPI CSI-2 Camera input (CSI0); extended temperature -25...+85°C	MSC SM2S-IMX8MLC-QC-24N0230E PCBFTX	PV

*COM products are divided in two categories, „PV“ (preferred variant) and „OR“ (on request).

Accessories

Order Number	Description	Reference
Carrier Options		
68488	SMARC 2.0 Embedded Platform with PCI Express x4 slot, GbE, SATA, USB 3.0, USB 2.0, USB 2.0 OTG, RS232, CAN, SPI, eSPI, SMBus, I2C and GPIO interface, LVDS/eDP, DisplayPort and HDMI display interface, regulated backlight supply, HD/I2S audio interface, MIPI CSI-2 camera interface, mini PCI Express card slot, SD card slot, fan connector, CMOS battery, Mini-ITX form factor (170 x 170 mm), ATX power connector and single 12V/24V power jack, commercial temperature range 0..+70°C	MSC SM2-MB-EP1-001 PCBFTX
83977	SMARC 2.x compatible embedded platform (146 x 80mm), 10-36V input voltage, 3x RS232, 2x CAN, dual RJ45 LAN with LED (1 x LAN i210) , 1x M.2 2280 Key M slot, mPCIe slot, 1x USB 3.0 Type A, 1x USB 2.0 Type A, 1x USB 2.0 internal, 1x USB 2.0 Host/Device, 2x SPI, I ² C, 8 GPIO on FC, 1x HDMI, LVDS/eDP/DSI on JILI30 connector, SD Card Slot, regulated backlight supply, I2S Audio, 1W Mono, camera connector, RTC battery. Industrial temperature range -40..+85°C, ARM full version	MSC SM2S-MB-EP5-002 PCBFTX
83981	SMARC 2.x compatible embedded platform (146 x 80mm), 10-36V input voltage, 2x UART, 1x RS232, 2x CAN, 1x RJ45 LAN with LED, 1x USB 2.0 Type A, 1x USB3.0 Type A, 1x USB 2.0 internal, 1x USB 2.0 Host/Device, 2x SPI, 12 GPIO on FC, 1x HDMI , SD Card Slot, LVDS/eDP/DSI on JILI30 connector, regulated backlight supply, RTC battery. Industrial temperature range -40..+85°C, ARM slim version	MSC SM2S-MB-EP5-004 PCBFTX
Cooling Options		
1151823	Heatspreader for SM2S-IMX8MINI module, consisting of a single-piece aluminum plane and thermal pad for contact to the processor, with 2.7mm through-hole standoffs	MSC SM2S-IMX8MINI-01 HSP-001
Other Accessories		
82479	Debug Console (UART) Adapter for i.MX6-based Qseven and nanoRISC modules, with 8-pin FFC cable to connect COM module to 9-pin D-Sub connector	MSC Debug Console Adapter
68948	Debug Adapter for i.MX6-based Qseven, SMARC and nanoRISC modules, with 10-pin FFC cable to connect to COM module, adapter provides headers for JTAG connection to Lauterbach and/or Goepel debuggers	MSC JTAG Adapter FFC 10-pin
Starter Kits		
74008	Starter Kit for MSC SMARC i.MX 8 Series modules. Includes MSC SM2-MB-EP1 Baseboard, Heatspreader/Heatsink, SD Card with USB Card Reader, Power Supply and suitable cable kit. The StarterKit does not include the MSC SM2S-IMX8 / 8M / 8MINI / 8NANO / 8PLUS module. Please order your choice of module separately.	MSC SM2-SK-IMX8-EP1-KIT001 SETPAC

Avnet Embedded GmbH
 Industriestr. 16
 76297 Stutensee

AvnetEmbedded@avnet.com
avnet.com/embedded

Copyright © 2024 Avnet. All data is for information purposes only and is subject to change without notice. No guarantee for legal purposes is implied. Information in this document has been carefully checked, however, no responsibility for inaccuracies has to be assumed. All brand or product names may be trademarks and property of their respective owners.