


COM Express Type 6



TRIA C6C-RYZ8

AMD Ryzen™ Embedded 8000 Series Processor



95 x 95

tbd

0 - +60°C



Highlights

- COM Express Type 6, Compact module
- AMD Ryzen™ Embedded 8000 Series Processor
- Up to eight cores/sixteen threads
- Integrated AI accelerator (XDNA Neural Processing Unit)
- Up to 96GB DDR5-5600 SDRAM, dual channel, ECC
- Up to six RDNA3 work group processors (WGP)
- Four independent display streams
- Selectable display outputs from up to three DisplayPort/HDMI, LVDS, eDP
- Up to twenty PCI Express® Gen 4/3 lanes
- Two USB 3.2 Gen1/2 and eight USB 2.0 ports
- Two UARTs
- Optional on-board NVMe SSD, up to 256GB
- Up to two SATA 6Gb/s mass storage interfaces
- 1 / 2.5 Gb Ethernet port (Intel® i226)
- Trusted Platform Module TPM 2.0
- Long-term product availability

COM Express Type 6



Technical Data

Technology	x86
Formfactor / Interface	COM Express Compact Type 6
CPU	AMD Ryzen™ 7 Pro 8845HS, eight core, 3.8/5.1GHz, 8MB L2 / 16MB L3, 6 WGP, 45W (35-54W) TDP, DDR5-5600; AMD Ryzen™ 5 Pro 8645HS, six core, 4.3/5.0GHz, 6MB L2 / 16MB L3, 4 WGP, 45W (35-54W) TDP, DDR5-5600; AMD Ryzen™ 7 Pro 8840U, eight core, 3.3/5.1GHz, 8MB L2 / 16MB L3, 6 WGP, 28W (15-30W) TDP, DDR5-5600; AMD Ryzen™ 5 Pro 8640U, six core, 3.5/4.9GHz, 6MB L2 / 16MB L3, 4 WGP, 28W (15-30W) TDP, DDR5-5600;
Chipset	Integrated into System-on-Chip
RAM	2x 262-pin SO-DIMM socket for up to 2x 48 GB DDR5 SDRAM (DDR5-5600); ECC option; dual channel operation Note: maximum DDR5 bandwidth depending on assembled memory module type
Storage Interfaces	Up to 2x SATA 6Gb/s Optional on-board NVMe, 128GB, 256GB
USB	2x USB 3.2 Gen 2 / USB 2.0 6x USB 2.0
Serial Interfaces	2x serial ports
Bus Interfaces	PCIe Gen 4 1x8 or 2x4 on COME PEG[0:7] PCIe Gen 4 1x4 on COME PEG[8:11], optional, mutually exclusive with on-board NVMe PCIe Gen 4 1x4 on COME PCIE[0:3], flexible bifurcation options PCIe Gen 3 4x1 on COME PCIE[4:7], depending on assembly variant LPC bus (Low Pin Count bus)
Display Controller	RDNA3, up to six work group processors Four independent displays supported
Display Interfaces	Display Port and HDMI/DVI: Up to 3x Digital Display Interface, usable as DisplayPort 2.1 (up to 10Gbps) ¹ , also usable as HDMI 2.1 (up to 10Gbps) ¹ or DVI (up to 1920 x 1200 @ 60Hz) ¹ Re-timer required for operation above 3Gb/s 1x Embedded DisplayPort 1.5 (on variants without LVDS only); LCD: LVDS 24bit, dual-channel (not on all variants); 1920 x 1200 @ 60Hz
Network Interface	10/100/1000Base-TX, 2.5G ² based on Intel i226-LM ² Available bandwidths depending on carrier design
Audio Interface	High Definition Audio
Security Device	TPM 2.0
Miscellaneous	Watchdog Timer: Initiates system reset, programmable Fan Supply: 4-pin header for CPU fan, PWM speed controlled and PWM speed control for system fan supported RTC battery: external System Monitoring: voltage, temperature, CPU fan, system fan

COM Express Type 6



Firmware	UEFI Firmware: AMI Aptio® V Security: TPM 2.0 support, TCG compliant Power Management: ACPI Active fan control USB: USB legacy support (keyboard, mouse, storage) Monitoring: System Monitoring Health Monitoring Tria Adv. Boot Device Selection: Boot device priority setting based on physical interfaces
OS Support	Windows 11 BSP for Linux (Yocto)
Power Requirement	Voltage: +8.5V to +20V, +5V Stby optional, +3V RTC voltage Power Consumption: tbd W to tbd W (typ.)
Environment	Ambient Temperature: 0° ... 60°C (operating) -25° ... 85°C (storage) Humidity: 5 ... 95% (operating, non-condensing), 5 ... 95% (storage, non-condensing)
Dimensions	95mm x 95mm
Certificates	UL / CE

Technical Data for TRIA C6C-RYZ8

COM Express Type 6



Order Reference

Order No.	Description	Reference	
tdb	COM Express Type 6 Compact module (95mm x 95mm); CPU: AMD Ryzen 7 Pro 8845HS, eight-core, 3.8/5.1GHz, 35-54W TDP, 6 WGP; 3x DP/HDMI/DVI, LVDS (24 Bit, dual channel); 1x 1GbE; 2x SATA; 2x USB3, 8x USB2; 4x PCIe Gen 4, 4x PCIe Gen 3, PEG 3x4 Gen 4; TPM 2.0; 2x socket for DDR5 or DDR5ECC SO-DIMM; DDR5-5600; 0° ... 60°C	MSC C6C-RYZ8-8845HS- NN221C PCBFTX	PV
tdb	COM Express Type 6 Compact module (95mm x 95mm); CPU: AMD Ryzen 7 Pro 8840U, eight-core, 3.3/5.1GHz, 15-30W TDP, 6 WGP; 3x DP/HDMI/DVI, LVDS (24 Bit, dual channel); 1x 1GbE; 2x SATA; 2x USB3, 8x USB2; 4x PCIe Gen 4, 4x PCIe Gen 3, PEG 3x4 Gen 4; TPM 2.0; 2x socket for DDR5 or DDR5ECC SO-DIMM; DDR5-5600; 0° ... 60°C	MSC C6C-RYZ8-8840U- NN221C PCBFTX	PV
tdb	COM Express Type 6 Compact module (95mm x 95mm); CPU: AMD Ryzen 5 Pro 8645HS, six-core, 4.3/5.0GHz, 35-54W TDP, 4 WGP; 3x DP/HDMI/DVI, LVDS (24 Bit, dual channel); 1x 1GbE; 2x SATA; 2x USB3, 8x USB2; 4x PCIe Gen 4, 4x PCIe Gen 3, PEG 3x4 Gen 4; TPM 2.0; 2x socket for DDR5 or DDR5ECC SO-DIMM; DDR5-5600; 0° ... 60°C	MSC C6C-RYZ8-8645HS- NN221C PCBFTX	PV
tdb	COM Express Type 6 Compact module (95mm x 95mm); CPU: AMD Ryzen 5 Pro 8640U, six-core, 3.5/4.9GHz, 15-30W TDP, 4 WGP; 3x DP/HDMI/DVI, eDP; 1x 1GbE; 2x SATA; 2x USB3, 8x USB2; 4x PCIe Gen 4, PEG 3x4 Gen 4; TPM 2.0; 2x socket for DDR5 or DDR5ECC SO-DIMM; DDR5-5600; 0° ... 60°C	MSC C6C-RYZ8-8640U- NN101C PCBFTX	PV

Ordering Information for TRIA C6C-RYZ8 *PV = Preferred variant; OR = on Request (in OEM quantities only)

Accessories

Carrier Boards

Order No.	Description	Reference
111650	COM Express Type 6 Evaluation Carrier Board with various PCI Express x1, x4 and x16 slots, USB 3.0/2.0, GbE, M.2, SD card socket, SATA, DisplayPort, LVDS, eDP, VGA, HD audio interfaces; ATX power connector. Dimensions: 305 x 244 mm (ATX form factor)	MSC C6-MB-EV4 PCBFTX

Carrier Boards for TRIA C6B-xxx/C6C-xxx Products

Cooling Solutions

Order No.	Description	Reference
tbd	Passive Heatsink for C6C-RYZ8 consisting of a single-piece aluminum profile with fins, standoffs without thread (2.7mm inner diameter), screws and thermopads for the thermal contact to CPU, chipset, NVMe.	MSC C6C-RYZ8-01 HSI-001
tbd	Passive Heatsink / heat pipe for C6C-RYZ8 consisting of a single-piece aluminum profile with fins and embedded heatpipe, standoffs without thread (2.7mm inner diameter), screws and thermopads for the thermal contact to CPU, chipset, NVMe.	MSC C6C-RYZ8-01 HSI-HP-001
tbd	Heatspreader for C6C-RYZ8. Single-piece aluminum profile, standoffs without thread (2.7mm inner diameter), screws and thermopads for the thermal contact to CPU, chipset, NVMe.	MSC C6C-RYZ8-01 HSP-001
tbd	Heatspreader / heat pipe for C6C-RYZ8. Single-piece aluminum profile with embedded heat pipe, standoffs without thread (2.7mm inner diameter), screws and thermopad for the thermal contact to CPU, chipset, NVMe.	MSC C6C-RYZ8-01 HSP-HP-001
tbd	Heatspreader for C6C-RYZ8. Single-piece aluminum profile, standoffs with M2.5 thread, screws and thermopads for the thermal contact to CPU, chipset, NVMe.	MSC C6C-RYZ8-02 HSP-001

Cooling Devices for TRIA C6C-RYZ8

Order No.	Description	Reference
79809	Fan kit for Heatsink TRIA HCA-ALP/RLP-0x HSI-xxx, TRIA C6B-ALP/ RLP-0x HSI-xxx, TRIA C6B-TLH-0x HSI-xxx, TRIA C6C-ALP/RLP-0x HSI-xxx, TRIA C6C-TLU-0x HSI-xxx, TRIA C6C-WLU-0x HSI-xxx, TRIA C6C-ALN/ASL-0x HSI-xxx, TRIA C6C-EL-0x HSI-xxx, TRIA C6C-RYZx-0x HSI-xxx, PWM fan 80x80x15mm.	MSC C6C-FANKIT-01-HSF-001

Fan Kit for COM Express Heatsinks

COM Express Type 6



Tria Technologies GmbH
Industriestr. 16
76297 Stutensee
info@tria-technologies.com
tria-technologies.com

Copyright © 2024 Tria Technologies GmbH. All data is for information purposes only and is subject to change without notice. No guarantee for legal purposes is implied. Information in this document has been carefully checked, however, no responsibility for inaccuracies has to be assumed. All brand or product names may be trademarks and property of their respective owners.