



晶采光電科技股份有限公司
AMPIRE CO., LTD.

SPECIFICATIONS FOR LCD MODULE

CUSTOMER	
CUSTOMER PART NO.	
AMPIRE PART NO.	AM-1024768Z2TZQW-00H-A
APPROVED BY	
DATE	

☐ Preliminary Specification

☐ Approved Specification

AMPIRE CO., LTD.

**Building A., 4F., No.116, Sec. 1, Sintai 5th Rd., Xizhi Dist,
New Taipei City 221, Taiwan (R.O.C.)**

新北市汐止區新台五路一段 116 號 4 樓(東方科學園區 A 棟)

TEL:886-2-26967269 , FAX:886-2-26967196 or 26967270

APPROVED BY	CHECKED BY	ORGANIZED BY
<i>Patrick</i>	<i>Kokai</i>	<i>Mark</i>

This Specification is subject to change without notice

RECORD OF REVISION

Revision Date	Page	Contents	Editor
2022/12/26	-	New Release	Mark

1. Features

12.1 TFT Liquid Crystal Display module is a color active matrix thin film transistor (TFT) liquid crystal display (LCD) that uses amorphous silicon TFT as a switching device. It is composed of a TFT LCD panel, a driving circuit and a back light system. This TFT LCD has a 12.1 inch diagonally measured active display area with HD (1024 horizontal by 768 vertical pixel) resolution.

2. PHYSICAL SPECIFICATIONS

Item	Specifications	Remark
LCD size	12.1 inch(Diagonal)	
Driver element	a-Si TFT active matrix	
Display resolution	1024 (W) × 3(RGB) x768(H) dots	
Display mode	Normally Black	
Dot pitch	0.240 (W) x0.240 (H) mm	
Active area	245.76 (W) x 184.32 (H) mm	
Color arrangement	RGB Vertical Stripe	
Surface treatment	Antiglare, Hard-Coating (3H)	
Weight	480	

3. ABSOLUTE MAXIMUM RATINGS

ITEM	SYMBOL	VALUES		UNIT	REMARK
		MIN	MAX		
Power Voltage	V_{DD}	-0.3	5.0	V	
	V_{LED}	-0.3	28	V	
Operation Temperature	T_{op}	-30	85	°C	
Storage Temperature	T_{st}	-40	90	°C	


Note 1: The absolute maximum rating values of this product are not allowed to be exceeded at any times.

Should a module be used with any of the absolute maximum ratings exceeded, the characteristics of the module may not be recovered, or in an extreme case, the module may be permanently destroyed.


4. ELECTRICAL SPECIFICATIONS

4.1 TFT LCD Module

Item	Symbol	Min.	Typ.	Max.	Unit	Note
Supply Voltage	V_{DD}	3.0	3.3	3.6	V	
Current of power supply	I_{DD}	—	0.242	0.364	A	$V_{DD} = 3.3V$ 、white pattern (L255)
VDD Power	P_{DD}	—	--	6.6	W	$V_{DD} = 3.3V$ 、white pattern (L255)
Inrush current	I_{RUSH}	—	—	2.0	A	Note*



Test circuit




Rising time

4.2 Switching Characteristics for LVDS Receiver


Item	Symbol	Min.	Typ.	Max.	Unit	Conditions
Differential Input High Threshold	V_{TH}	100		300	mV	
Differential Input Low Threshold	V_{TL}	-300		100	mV	
Differential input common mode voltage	V_{CM}	1.0	1.2	-	V	
Input Current	I_{IN}	-10		10	μA	$RX+/-$, $RXC+/-$
Differential input Voltage	V_{ID}	200		600	mV	

4.3 Bit LVDS input

4.3.1 6bit LVDS input



4.3.2 8Bit LVDS input




4.4 Interface Timing (DE mode)


Item	Symbol	Min.	Typ.	Max.	Unit
Frame Rate	--	55	60	65	Hz
Vertical Total Time	T_v	783	798	813	line
Vertical Display Time	T_{vD}	768			
Vertical Blanking Time	T_{vB}	15	30	45	line
Horizontal Total Time	T_H	1104	1124	1144	clock
Horizontal Display Time	T_{HD}	1024			
Horizontal Blanking Time	T_{HB}	80	100	120	clock
Clock Rate	$1/T_{Clock}$	51.2	53.8	56.2	MHz

Timing Diagram of Interface Signal (DE mode)


1. Vertical



2. Horizontal



4.5 Power On / Off Sequence



Item	Min.	Typ.	Max.	Unit
TP1	0.5	--	10	msec
TP2	0	--	50	msec
TP3	200	--	--	msec
TP4	0.5	--	10	msec
TP5	10	--	--	msec
TP6	10	--	--	msec
TP7	0	--	10	msec
TP8	200	--	--	msec
TP9	0	--	50	msec
TP10	1	--	10	msec
TP11	1000	--	--	msec

4.6 Backlight Unit


Parameter	Symbol	Min	Typ	Max	Units	Condition
Input Current	I_i	--	850	1200	mA	$T_a=25^{\circ}\text{C}$
Input Voltage	V_i	10	12	16	Volt	$T_a=25^{\circ}\text{C}$
LED Life-Time	N/A	30,000	--	--	Hour	$T_a=25^{\circ}\text{C}$ $I_F=52.5\text{mA}$ A Note

Parameter	Symbol	Min	Typ	Max	Units	Note
Backlight Power Supply	V_i	10	12	16	Volt.	
LED_EN High Threshold	V_{ENH}	1.4	3.3	5.0	Volt.	
LED_EN Low Threshold	V_{ENL}	0	--	0.8	Volt.	
PWM High Threshold	V_{PWMH}	2.0	3.3	6.0	Volt.	
PWM Low Threshold	V_{PWML}	0	--	0.8	Volt.	
PWM Frequency	F_{PWM}	100	--	30K	Hz	Note (4)
PWM Duty Cycle	T_D	10	--	100	%	

Note (1) LED life time (Hr) can be defined as the time in which it continues to operate under the condition: $T_a=25\pm 3^{\circ}\text{C}$, typical I_L value indicated in the above table until the brightness becomes less than 50%.


Note (2) The "LED life time" is defined as the module brightness decrease to 50% original brightness at $T_a=25^{\circ}\text{C}$ and $I_i=850\text{mA}$, the LED lifetime could be decreased if operating I_L is larger than 850mA. The constant current driving method is suggested.

Note (3) LED Light Bar Circuit



BLU circuit : 11S-4P

Note (4) Dimming controller waveform



5. INTERFACE


5.1 Interface Connector (Input signal): STARCONN 076B20-0048RA-G4 or JAE FI-SEB20P-HFE (or equivalent)

Pin NO.	Symbol	Description	Note
1	RX3+	Differential Data Input, CH3 (Positive)	
2	RX3-	Differential Data Input, CH3 (Negative)	
3	BIST	Normal operation/BIST pattern select. BIST="0" : Normal operation. BIST="1" : BIST mode	Note*
4	SEL68	6bit/8bit mode select, SELB = "1" : LVDS input data is 8bits SELB = "0" : LVDS input data is 6bits	Note*
5	GND	Ground	
6	RXC+	Differential Clock Input (Positive)	
7	RXC-	Differential Clock Input (Negative)	
8	GND	Ground	
9	RX2+	Differential Data Input , CH2 (Positive)	
10	RX2-	Differential Data Input , CH2 (Negative)	
11	GND	Ground	
12	RX1+	Differential Data Input , CH1 (Positive)	
13	RX1-	Differential Data Input, CH1 (Negative)	
14	GND	Ground	
15	RX0+	Differential Data Input, CH0 (Positive)	
16	RX0-	Differential Data Input, CH0 (Negative)	
17	reLR	Left or right display control SHLR="1" : Right → Left SHLR="0" : Left → Right	Note*
18	reUD	Up / down display control UPDN="1" : Down → Up UPDN="0" : Up → Down	Note*
19	VDD	Power supply, 3.3V	
20	VDD	Power supply, 3.3V	

Note* : The high level voltage "1" is 3.3V, and the low level voltage "0" is GND.

Note 1 : UPDN and SHLR control function

reLR	reUD	Data shifting
1	0	Right→Left, Up→Down
0	0	Left→Right, Up→Down
1	1	Right→Left, Down→Up
0	1	Left→Right, Down→Up


**5.2 Backlight Pin Assignment (CN2) : ACES 1208-01001-H01 (or equivalent)**

Pin NO.	Symbol	Description	Note
1	Vi	Converter input voltage	12V
2	Vi	Converter input voltage	12V
3	Vi	Converter input voltage	12V
4	Vi	Converter input voltage	12V
5	VGND	Converter ground	Ground
6	VGND	Converter ground	Ground
7	VGND	Converter ground	Ground
8	VGND	Converter ground	Ground
9	EN	Enable pin	3.3V
10	ADJ	Backlight Adjust	PWM Dimming (100Hz-30KHz, Hi: 2.0~3.3V, Lo : 0~0.8V)

6. Optical Specifications

Item		Symbol	Condition	Min.	Typ.	Max.	Unit	Note
Contrast		CR	$\Theta=0$ Normal viewing angle	600	900	—		(1)(2)
Response time	Rising	TR+TF		—	30	40	msec	(1)(3)
	Falling							
White luminance (Center)		Y _L		400	600	—	cd/m ²	(1)(4) (I _L =850mA)
Color chromaticity (CIE1931)	White	W _x		0.260	0.300	0.340		(1)(4)
		W _y		0.280	0.320	0.360		
	Red	R _x		0.612	0.652	0.692		
		R _y		0.303	0.343	0.383		
	Green	G _x		0.263	0.303	0.343		
		G _y		0.578	0.618	0.658		
	Blue	B _x		0.104	0.144	0.184		
		B _y		0.053	0.093	0.133		
Viewing angle	Hor.	Θ_L	CR>10	80	85	—		
		Θ_R		80	85	—		
	Ver.	Θ_U		80	85	—		
		Θ_D		80	85	—		
Brightness uniformity		B _{UNI}	$\Theta=0$	70	80	—	%	(5)
Optima View Direction		Free						(6)


Note (1) Definition of Viewing Angle:




Note (2) Definition of Contrast Ratio (CR) :
measured at the center point of panel

$$CR = \frac{\text{Luminance with all pixels white}}{\text{Luminance with all pixels black}}$$


Note (3) Definition of Response Time : Sum of T_R and T_F



Note (4) Definition of optical measurement setup



Note (5) Definition of brightness uniformity



$$\text{Luminance uniformity} = \frac{(\text{Min Luminance of 9 points})}{(\text{Max Luminance of 9 points})} \times 100\%$$

Note (6) : Rubbing Direction (The different Rubbing Direction will cause the different optima view direction.

7. ELIABILITY TEST CONDITIONS

Test Item	Test Conditions	Note
High Temperature Operation	85±3°C ,Dry t=240 hrs	
Low Temperature Operation	-30±3°C, Dry t=240 hrs	
High Temperature Storage	90±3°C , Dry t=240 hrs	1,2
Low Temperature Storage	-40±3°C ,Dry t=240 hrs	1,2
Thermal Shock Test	-30°C ~ 25°C ~ 85°C 30 m in. 5 min. 30 min. (1 cycle) Total 100 cycle(Dry)	1,2
Storage Humidity Test	60 °C, Humidity 90%, 240 hrs	1,2
Vibration Test (Packing)	Sweep frequency : 10 ~ 55 ~ 10 Hz/1min Amplitude : 0.75mm Test direction : X.Y.Z/3 axis Duration : 30min/each axis	2

Note 1 : Condensation of water is not permitted on the module.

Note 2 : The module should be inspected after 1 hour storage in normal conditions (15-35°C , 45-65%RH).

Definitions of life end point :

- Current drain should be smaller than the specific value.
- Function of the module should be maintained.
- Appearance and display quality should not have degraded noticeably.
- Contrast ratio should be greater than 50% of the initial value.

8. GENERAL PRECAUTION

8.1 Use Restriction

This product is not authorized for use in life supporting systems, aircraft navigation control systems, military systems and any other application where performance failure could be life-threatening or otherwise catastrophic.

8.2 Disassembling or Modification

Do not disassemble or modify the module. It may damage sensitive parts inside LCD module, and may cause scratches or dust on the display. AMPIRE does not warrant the module, if customers disassemble or modify the module.

8.3 Breakage of LCD Panel

- (1) If LCD panel is broken and liquid crystal spills out, do not ingest or inhale liquid crystal, and do not contact liquid crystal with skin.
- (2) If liquid crystal contacts mouth or eyes, rinse out with water immediately.
- (3) If liquid crystal contacts skin or cloths, wash it off immediately with alcohol and rinse thoroughly with water.
- (4) Handle carefully with chips of glass that may cause injury, when the glass is broken.

8.4 Electric Shock

- (1) Disconnect power supply before handling LCD module.
- (2) Do not pull or fold the LED cable.
- (3) Do not touch the parts inside LCD modules and the fluorescent LED's connector or cables in order to prevent electric shock.

8.5 Absolute Maximum Ratings and Power Protection Circuit

- (1) Do not exceed the absolute maximum rating values, such as the supply voltage variation, input voltage variation, variation in parts' parameters, environmental temperature, etc., otherwise LCD module may be damaged.
- (2) Please do not leave LCD module in the environment of high humidity and high temperature for a long time.
- (3) It's recommended to employ protection circuit for power supply.

8.6 Operation

- (1) Do not touch, push or rub the polarizer with anything harder than HB pencil lead.
- (2) Use fingerstalls of soft gloves in order to keep clean display quality, when persons handle the LCD module for incoming inspection or assembly.
- (3) When the surface is dusty, please wipe gently with absorbent cotton or other soft material.
- (4) Wipe off saliva or water drops as soon as possible. If saliva or water drops contact with polarizer for a long time, they may cause deformation or color fading.
- (5) When cleaning the adhesives, please use absorbent cotton wetted with a little petroleum benzene or other adequate solvent.

8.7 Mechanism

Please mount LCD module by using mounting holes arranged in four corners tightly.

8.8 Static Electricity

- (1) Protection film must remove very slowly from the surface of LCD module to prevent from electrostatic occurrence.
- (2) Because LCD modules use CMOS-IC on circuit board and TFT-LCD panel, it is very weak to electrostatic discharge. Please be careful with electrostatic discharge. Persons who handle the module should be grounded through adequate methods.

8.9 Strong Light Exposure

The module shall not be exposed under strong light such as direct sunlight. Otherwise, display characteristics may be changed.


8.10 Disposal

When disposing LCD module, obey the local environmental regulations.


8.11 Others

Do not keep the LCD at the same display pattern continually. The residual image will happen and it will damage the LCD. Please use screen saver.

9. OUTLINE DIMENSION



REV	REVISION RECORD	DATE NAME
0	NEW RELEASE	05-26-17 YUPE



A Block

CN1

1	RX3+
2	RX3-
3	BIST
4	SEL68
5	GND
6	RXC+
7	RXC-
8	GND
9	RX2+
10	RX2-
11	GND
12	RX1+
13	RX1-
14	GND
15	RX0+
16	RX0-
17	reLR
18	reUD
19	VDD
20	VDD

CN2

1	VI
2	VI
3	VI
4	VI
5	VGND
6	VGND
7	VGND
8	VGND
9	EN
10	ADJ


Note:
1. Unless indicated, Tolerance "+0.5"

2. UV Glue For OLB Protection.

3. LCM Connector Recommend STARCONN 076B20-0048RA-G4 or JAE FI-SEB20P-HFE (or Equivalent).

4. Backlight Pin Assignment (CN2) : ACES 91208-01001-H01 (or Equivalent).

Back View



1	7	TOLERANCE GRADE(±)	A	B	DIM.	MM	DWN.	YUPEI	DATE	TITLE
2	8				IE NO.		CHK.		DATE	102476872
3	9				PARTS NO. LCM-1		APPD.		DATE	(12.1)
4	10				102476872					
5	11									
6	12									

AMP 晶采光電科技

DWG. NO. *1705136MA SHEET 1 OF 1

REV REVISION RECORD				DATE NAME	
0 NEW RELEASE				00-09-21 SNOW	

Note:

1. Bag = 1 PCS LCM
2. Big Box= 1x 10 = 10 PCS LCM

1	7	TOLERANCE GRADE(±)		A	B	DIM.	MM	DRAW.	SNOW	DATE	TITLE
2	8					IB NO.		CHK.		DATE	102476825
3	9										(12.1") IPS
4	10					PARTS NO. BOX		APPD.		DATE	
5	11					102476825					
6	12										

晶光电科技

DWG. NO.	SHEET
*2204175SA	1 OF 1