



AUO Display+

Product Specification

G101EAT02.601

☐ Preliminary Specification




☒ Final Specification

Module	10.1 Inch Color TFT-LCD with Touch
Model Name	G101EAT02.601

Company	Approved by	Date
	<u>LeaDer Feng</u>	<u>2024/09/18</u>
Checked & Approved by	Prepared by	
	<u>Danny Liao</u>	<u>2024/09/18</u>
	General Display Business Unit / AUO Display Plus Corporation	

Contents

1. Operating Precautions	5
2. General Description.....	6
2.1 Display Characteristics	6
2.2 Optical Characteristics	7
3. Functional Block Diagram.....	10
4. Absolute Maximum Ratings	11
4.1 Absolute Ratings of TFT LCD Module	11
4.2 Absolute Ratings of Environment	11
5. Electrical Characteristics	12
5.1 TFT LCD Module	12
5.2 Backlight Unit	15
5.3 Touch Sensor	16
5.3.1 Electrical Characteristics	16
5.3.2 Touch Driver Information	16
5.3.3 Touch Characteristics	16
6. Signal Characteristic	17
6.1 Pixel Format Image	17
6.2 Signal Description	18
6.3 Interface Timing.....	21
7. Reliability Test Criteria	23
8. Mechanical Characteristics.....	24
8.1 Outline Dimension (Front View)	24
8.2 Outline Dimension (Rear View)	25
9. Label and Packaging	26
9.1 Shipping Label (on the rear side of TFT-LCD display)	26
9.2 Carton/Pallet Package	26
10 Safety	27
10.1 Sharp Edge Requirements	27
10.2 Materials.....	27
10.3 Capacitors	27
10.4 National Test Lab Requirement.....	27

Version and Date	Page	Old description	New Description																																																																
0.0 2022/03/14	All	Draft specification																																																																	
0.1 2022/04/07	6		Update surface treatment																																																																
0.2 2022/04/25	24, 25		Update outline drawing																																																																
0.3 2022/05/30	26	9.2 Carton/Pallet Package TBD	9.2 Carton/Pallet Package  Max capacity: 20 pcs TFT-LCD module per carton Outside dimension of carton: 508(L) mm x 408 (W) mm x 279 (H) mm Pallet size: 1150 * 840 * 132mm Module by air: (2' * 2') * 5 layers + one pallet put 20 boxes, total 400 pcs module Module by sea: One pallet (2' * 2') * 5 layers + One pallet (2' * 2') * 1 layers, total 480 pcs module Module by sea_HQ: One pallet (2' * 2') * 5 layers + One pallet (2' * 2') * 2 layers, Total 560 pcs module																																																																
1.0 2022/07/27	6	Weight (Max.) [Grams] TBD	Weight (Max.) [Grams] 500 Update weight																																																																
	7	Color / Chromaticity Coordinates (CIE 1931) <table><tr><td>Red x</td><td>TBD</td><td>TBD</td><td>TBD</td></tr><tr><td>Red y</td><td>TBD</td><td>TBD</td><td>TBD</td></tr><tr><td>Green x</td><td>TBD</td><td>TBD</td><td>TBD</td></tr><tr><td>Green y</td><td>TBD</td><td>TBD</td><td>TBD</td></tr><tr><td>Blue x</td><td>TBD</td><td>TBD</td><td>TBD</td></tr><tr><td>Blue y</td><td>TBD</td><td>TBD</td><td>TBD</td></tr><tr><td>White x</td><td>TBD</td><td>TBD</td><td>TBD</td></tr><tr><td>White y</td><td>TBD</td><td>TBD</td><td>TBD</td></tr></table>	Red x	TBD	TBD	TBD	Red y	TBD	TBD	TBD	Green x	TBD	TBD	TBD	Green y	TBD	TBD	TBD	Blue x	TBD	TBD	TBD	Blue y	TBD	TBD	TBD	White x	TBD	TBD	TBD	White y	TBD	TBD	TBD	Color / Chromaticity Coordinates (CIE 1931) <table><tr><td>Red x</td><td>0.552</td><td>0.602</td><td>0.652</td></tr><tr><td>Red y</td><td>0.295</td><td>0.345</td><td>0.395</td></tr><tr><td>Green x</td><td>0.278</td><td>0.328</td><td>0.378</td></tr><tr><td>Green y</td><td>0.518</td><td>0.568</td><td>0.618</td></tr><tr><td>Blue x</td><td>0.101</td><td>0.151</td><td>0.201</td></tr><tr><td>Blue y</td><td>0.096</td><td>0.146</td><td>0.196</td></tr><tr><td>White x</td><td>0.263</td><td>0.313</td><td>0.363</td></tr><tr><td>White y</td><td>0.279</td><td>0.329</td><td>0.379</td></tr></table> Update Color	Red x	0.552	0.602	0.652	Red y	0.295	0.345	0.395	Green x	0.278	0.328	0.378	Green y	0.518	0.568	0.618	Blue x	0.101	0.151	0.201	Blue y	0.096	0.146	0.196	White x	0.263	0.313	0.363	White y	0.279	0.329	0.379
Red x	TBD	TBD	TBD																																																																
Red y	TBD	TBD	TBD																																																																
Green x	TBD	TBD	TBD																																																																
Green y	TBD	TBD	TBD																																																																
Blue x	TBD	TBD	TBD																																																																
Blue y	TBD	TBD	TBD																																																																
White x	TBD	TBD	TBD																																																																
White y	TBD	TBD	TBD																																																																
Red x	0.552	0.602	0.652																																																																
Red y	0.295	0.345	0.395																																																																
Green x	0.278	0.328	0.378																																																																
Green y	0.518	0.568	0.618																																																																
Blue x	0.101	0.151	0.201																																																																
Blue y	0.096	0.146	0.196																																																																
White x	0.263	0.313	0.363																																																																
White y	0.279	0.329	0.379																																																																
	16	5.3.1 Electrical Characteristics <table><tr><th>Item</th><th>Min.</th><th>Typ.</th><th>Max.</th><th>Unit</th><th>Remark</th></tr><tr><td>Power Supply</td><td></td><td>TBD</td><td></td><td>Voltage</td><td></td></tr><tr><td>Power Supply</td><td>Normal Operation Mode</td><td></td><td>TBD</td><td>mA</td><td></td></tr><tr><td>Current</td><td>Idle Mode</td><td></td><td>TBD</td><td>mA</td><td></td></tr></table>	Item	Min.	Typ.	Max.	Unit	Remark	Power Supply		TBD		Voltage		Power Supply	Normal Operation Mode		TBD	mA		Current	Idle Mode		TBD	mA		5.3.1 Electrical Characteristics <table><tr><th>Item</th><th>Min.</th><th>Typ.</th><th>Max.</th><th>Unit</th><th>Remark</th></tr><tr><td>Power Supply</td><td></td><td>5</td><td></td><td>V</td><td></td></tr><tr><td>Normal mode Current consumption @ Report rate 100Hz</td><td></td><td>55</td><td></td><td>mA</td><td></td></tr></table> Update touch sensor electrical characteristics.	Item	Min.	Typ.	Max.	Unit	Remark	Power Supply		5		V		Normal mode Current consumption @ Report rate 100Hz		55		mA																							
Item	Min.	Typ.	Max.	Unit	Remark																																																														
Power Supply		TBD		Voltage																																																															
Power Supply	Normal Operation Mode		TBD	mA																																																															
Current	Idle Mode		TBD	mA																																																															
Item	Min.	Typ.	Max.	Unit	Remark																																																														
Power Supply		5		V																																																															
Normal mode Current consumption @ Report rate 100Hz		55		mA																																																															
1.1 2022/10/05	2	Module 10.1 Inch Color TFT-LCD Model Name G101EAT02.6 (97D10G32.600)	Module 10.1 Inch Color TFT-LCD with Touch Model Name G101EAT02.6 TP FW version 00_T3 (20220928) Revise model name																																																																
1.2 2022/11/23	25		 Update drawing																																																																
1.3 2023/06/02	1	Module 10.1 Inch Color TFT-LCD with Touch Model Name G101EAT02.6 TP FW version 00_T3 (20220928)	Module 10.1 Inch Color TFT-LCD with Touch Model Name G101EAT02.6 Remove TP FW																																																																

Version and Date	Page	Old description	New Description														
1.4 2024/08/22	16	5.3.2 Touch Driver Information^(*) <table><tr><th>Driver Name / Designation^(*)</th><th>Specifications^(*)</th></tr><tr><td>Manufacturer^(*)</td><td>EETI^(*)</td></tr><tr><td>Type / Part Number^(*)</td><td>EXC81W32^(*)</td></tr></table>	Driver Name / Designation ^(*)	Specifications ^(*)	Manufacturer ^(*)	EETI ^(*)	Type / Part Number ^(*)	EXC81W32 ^(*)	5.3.2 Touch Driver Information^(*) <table><tr><th>Driver Name / Designation^(*)</th><th>Specifications^(*)</th></tr><tr><td>Manufacturer^(*)</td><td>EETI^(*)</td></tr><tr><td>Type / Part Number^(*)</td><td>EXC81W32^(*)</td></tr><tr><td>Firmware version^(*)</td><td>A11J_v00_T1_00_C002^(*)</td></tr></table> Add TP FW version	Driver Name / Designation ^(*)	Specifications ^(*)	Manufacturer ^(*)	EETI ^(*)	Type / Part Number ^(*)	EXC81W32 ^(*)	Firmware version ^(*)	A11J_v00_T1_00_C002 ^(*)
Driver Name / Designation ^(*)	Specifications ^(*)																
Manufacturer ^(*)	EETI ^(*)																
Type / Part Number ^(*)	EXC81W32 ^(*)																
Driver Name / Designation ^(*)	Specifications ^(*)																
Manufacturer ^(*)	EETI ^(*)																
Type / Part Number ^(*)	EXC81W32 ^(*)																
Firmware version ^(*)	A11J_v00_T1_00_C002 ^(*)																
	26	9.1 Shipping Label (on the rear side of TFT-LCD display)^(*)  30mm 12mm	9.1 Shipping Label (on the rear side of TFT-LCD display)^(*)  30mm 12mm Update shipping label drawing														
1.5 2024/09/18	-	-	Final spec.														

1. Operating Precautions

- 1) Since front polarizer is easily damaged, please be cautious and not to scratch it.
- 2) Be sure to turn off power supply when inserting or disconnecting from input connector.
- 3) Wipe off water drop immediately. Long contact with water may cause discoloration or spots.
- 4) When the panel surface is soiled, wipe it with absorbent cotton or soft cloth.
- 5) Since the panel is made of glass, it may be broken or cracked if dropped or bumped on hard surface.
- 6) To avoid ESD (Electro Static Discharge) damage, be sure to ground yourself before handling TFT-LCD Module.
- 7) Do not open nor modify the module assembly.
- 8) Do not press the reflector sheet at the back of the module to any direction.
- 9) In case if a module has to be put back into the packing container slot after it was taken out from the container, do not press the center of the LED light bar edge. Instead, press at the far ends of the LED light bar edge softly. Otherwise the TFT Module may be damaged.
- 10) At the insertion or removal of the Signal Interface Connector, be sure not to rotate nor tilt the Interface Connector of the TFT Module.
- 11) TFT-LCD Module is not allowed to be twisted & bent even force is added on module in a very short time. Please design your display product well to avoid external force applying to module by end-user directly.
- 12) Small amount of materials having no flammability grade is used in the LCD module. The LCD module should be supplied by power complied with requirements of Limited Power Source (IEC60950 or UL1950), or be applied exemption.
- 13) Severe temperature condition may result in different luminance, response time and lamp ignition voltage.
- 14) Continuous operating TFT-LCD display under low temperature environment may accelerate lamp exhaustion and reduce luminance dramatically.
- 15) The data on this specification sheet is applicable when LCD module is placed in landscape position.
- 16) Continuous displaying fixed pattern may induce image sticking. It's recommended to use screen saver or shuffle content periodically if fixed pattern is displayed on the screen.

2. General Description

G101EAT02.6 is a Color Active Matrix Liquid Crystal Display composed of a TFT LCD panel and LED backlight system. The screen format is intended to support the 16:10 WXGA, 1280(H) x 800(V) screen and 16.7M colors with LED backlight driving circuit. All input signals are LVDS interface compatible.

2.1 Display Characteristics

The following items are characteristics summary under 25 °C condition:

Items	Unit	Specifications
Screen Diagonal	[inch]	10.1"
Active Area	[mm]	216.96(H) x 135.6(V)
Pixels H x V		1280(RGB)x 800
Pixel Pitch	[mm]	0.1695X 0.1695
Pixel Arrangement		R.G.B. Vertical Stripe
Display Mode		AHVA, Normally Black
Nominal Input Voltage VDD	[Volt]	3.3 (Typical)
Power Consumption	[Watt]	Logic Power : 1(Max)@White pattern 3.3V input LED power max 3.024 W
Weight (Max.)	[Grams]	500
Physical Size (typ.)	[mm]	249.66(H) x 168.30(V)x 11.03(T) (max.)
Electrical Interface		LVDS 1Port 8bit
Surface Treatment		AS Coating, 7H
Support Color		16.7M colors
Temperature Range Operating Storage (Non-Operating)	[°C] [°C]	-20 to +70 (Front and rear surface) -30 to +80
RoHS Compliance		RoHS Compliance

2.2 Optical Characteristics

The optical characteristics are measured under stable conditions at 25 °C (Room Temperature):

Item	Unit	Conditions	Min.	Typ.	Max.	Note
White Luminance	[cd/m2]	I _{LED} = 28mA (center)	320	400	---	
Uniformity	%	5 points	70%		---	
Contrast Ratio			600	800	---	
Response Time	[msec]	Rising + Falling	---	29	38	
Viewing Angle	[degree]	Horizontal (Right)	80	89	---	
	[degree]	CR = 10 (Left)	80	89	---	
	[degree]	Vertical (Upper)	80	89	---	
	[degree]	CR = 10 (Lower)	80	89	---	
Color / Chromaticity Coordinates (CIE 1931)		Red x	0.552	0.602	0.652	
		Red y	0.295	0.345	0.395	
		Green x	0.278	0.328	0.378	
		Green y	0.518	0.568	0.618	
		Blue x	0.101	0.151	0.201	
		Blue y	0.096	0.146	0.196	
		White x	0.263	0.313	0.363	
		White y	0.279	0.329	0.379	
Color Gamut	%		---	45	---	


Note 1: Measurement method

Equipment Pattern Generator, Power Supply, Digital Voltmeter, Luminance meter (SR_3 or equivalent)


Aperture Field angle 2° with 50cm measuring distance

Test Point Follow Note 2 position

Environment < 1 lux



Note 2: Definition of 5 points position



Note 3: The luminance uniformity of 5 points is defined by dividing the minimum luminance values by the maximum test point luminance


$$\delta_{w5} = \frac{\text{Minimum Brightness of five points}}{\text{Maximum Brightness of five points}}$$

Note 4: Definition of contrast ratio (CR):

$$\text{Contrast ratio (CR)} = \frac{\text{Brightness on the "White" state}}{\text{Brightness on the "Black" state}}$$

Note 5: Definition of response time:


The output signals of photo detector are measured when the input signals are changed from "White" to "Black" (falling time) and from "Black" to "White" (rising time), respectively. The response time interval is between 10% and 90% of amplitudes. Please refer to the figure as below.



AUO Display+

Note 6: Definition of viewing angle


Viewing angle is the measurement of contrast ratio ≥ 10 , at the screen center, over a 180° horizontal and 180° vertical range (off-normal viewing angles). The 180° viewing angle range is broken down as below: 90° (θ) horizontal left and right, and 90° (Φ) vertical high (up) and low (down). The measurement direction is typically perpendicular to the display surface with the screen rotated to its center to develop the desired measurement viewing angle.



AUO Display+

3. Functional Block Diagram

The following diagram shows the functional block of the 10.1 inch color TFT/LCD module:





AUO Display+

4. Absolute Maximum Ratings

4.1 Absolute Ratings of TFT LCD Module

Item	Symbol	Min	Max	Unit
Logic/LCD drive Voltage	VDD	-0.3	3.6	[Volt]
LCD Input Signal Voltage	V _{SIGNAL}	-0.3	3.6	[Volt]

4.2 Absolute Ratings of Environment

Item	Symbol	Min	Max	Unit
Operating Temperature	TOP	-20	+70	[°C]
Humidity	HOP	5	90	[%RH]
Storage Temperature	TST	-30	+80	[°C]
Storage Humidity	HST	5	90	[%RH]

Note 1: Permanent damage to the device may occur if exceed maximum values

Note 2: Maximum wet-bulb temperature is less than 39 oC and no condensation

Note 3: Operating temperature means “Front and rear surface” of panel

5. Electrical Characteristics

5.1 TFT LCD Module


5.1.1 Power Specification

The power specification are measured under 25°C and frame frequency under 59.99Hz

Symbol	Parameter	Min	Typ	Max	Units	Remark
VDD	Logic/LCD Drive Voltage	3.0	3.3	3.6	[Volt]	
IDD	VDD Current	-	278.7	303	[mA]	All White Pattern (VDD=3.3V, at 59.9Hz)
Irush	LCD Inrush Current	-	-	1500	[mA]	Note 1
PDD	VDD Power	-	0.92	1	[Watt]	All White Pattern (VDD=3.3V, at 59.9Hz)
VDDrp	Allowable Logic/LCD Drive Ripple Voltage	-	-	100	[mV] p-p	All White Pattern (VDD=3.3V, at 59.9Hz)

Note 1 : Maximum Measurement Condition : White Pattern at 3.3V driving voltage. ($P_{max}=V_{3.3} \times I_{white}$)

Note 2 : Measure Condition



AUO Display+

5.1.2 Signal Electrical Characteristics


Input signals shall be low or Hi-Z state when VDD is off.

Symbol	Item	Min.	Typ.	Max.	Unit	Remark
VTH	Differential Input High Threshold	-	-	100	[mV]	VCM=1.2V
VTL	Differential Input Low Threshold	-100	-	-	[mV]	VCM=1.2V
VID	Input Differential Voltage	100		600	[mV]	
VICM	Differential Input Common Mode Voltage	1.0	1.2	1.5	[V]	VTH/VTL=±100mV


Note: LVDS Signal Waveform.

VP-VN=|VID|>VTH="High"
VP-VN=-|VID|<VTL="Low"

Single-end Signal




Differential Signal



5.1.3 Power ON/OFF Sequence

VDD power and backlight on/off sequence is as below. Interface signals are also shown in the chart. Signals from any system shall be Hi-Z state or low level when VDD is off.



Power Sequence Timing

Parameter	Value			Unit
	Min.	Typ.	Max.	
T1	0.5	-	10	[ms]
T2	50	60	70	[ms]
T3	200	-	-	[ms]
T4	0.5	-	10	[ms]
T5	10	-	-	[ms]
T6	10	-	-	[ms]
T7	0	-	-	[ms]
T8	10	-	-	[ms]
T9	-	-	10	[ms]
T10	110	-	-	[ms]
T11	0	16	50	[ms]
T12	-	-	10	[ms]
T13	1000	-	-	[ms]

The above on/off sequence should be applied to avoid abnormal function in the display. Please make sure to turn off the power when you plug the cable into the input connector or pull the cable out of the connector.

5.2 Backlight Unit

5.2.1 Parameter guideline for LED

Following characteristics are measured under a stable condition using an inverter at 25°C(Room Temperature):

Symbol	Parameter	Min.	Typ.	Max.	Unit	Remark
VLED	Input Voltage	10.8	12	13.2	[Volt]	
I _{VLED}	Input Current	---	222	252	[mA]	100% Brightness (VLED = 12V)
P _{VLED}	Power Consumption	---	2.664	3.024	[Watt]	100% Brightness (VLED = 12V)
I _F	LED Forward Current	---	28	---	[mA]	Ta = 25°C
VEN	LED Enable Input High Level	2.3	-	5.5	[Volt]	
	LED Enable Input Low Level	-	-	0.3	[Volt]	
VPWM	PWM Logic Input High Level	2.3	-	5.5	[Volt]	
	PWM Logic Input Low Level	-	-	0.3	[Volt]	
PWM Input Frequency	FPWM	200	-	20K	Hz	
PWM Duty Ratio	Duty	5		100	%	
Operation Life	---	50,000	---	---	Hrs	(Ta=25°C), Note 2 I _F =28mA

Note 1: Ta means ambient temperature of TFT-LCD module.

Note 2: V_{LED}, I_{VLED}, P_{VLED} are defined for LED backlight.(100% duty of PWM dimming)

Note 3: If G101EAT02.6 module is driven by high current or at high ambient temperature & humidity condition. The operating life will be reduced.

Note 4: Operating life means brightness goes down to 50% initial brightness. Minimum operating life time is estimated data.

5.3 Touch Sensor

5.3.1 Electrical Characteristics

Item	Min.	Typ.	Max.	Unit	Remark
Power Supply	--	5	--	V	
Normal mode Current consumption @ Report rate 100Hz	--	55	--	mA	

5.3.2 Touch Driver Information


Driver Name / Designation	Specifications
Manufacturer	EETI
Type / Part Number	EXC81W32
Firmware version	A11J_v00_T1_00_C002

5.3.3 Touch Characteristics

Item	Specifications
Thickness	2.0mm±0.2mm (CL: 1.1mm±0.2mm / Sensor:0.9mm±0.2mm)
TP View Area	136.60mm*217.96mm
Substrate Material	SDL CS Glass
Single / Multi-touch Accuracy	+/- 1.5mm ~ +/- 2.5mm
Linearity	+/- 1.5mm ~ +/- 2.5mm
Surface Hardness	JIS-5600 7H
Mutiel touch	10 Point
Report Rate (points /sec)	100Hz
Transparency	>85%

6.2 Signal Description

The following figures show the image seen from the front view. The arrow indicates the direction of scan.



6.2.1 Pin Assignment

LVDS is a differential signal technology for LCD interface and high speed data transfer device.

PIN NO	Symbol	Function
1	GND	Ground
2	VDD	LCD Power Supply +3.3V
3	VDD	LCD Power Supply +3.3V
4	VDD	LCD Power Supply +3.3V
5	NC	AUO Self Test Pin
6	NC	AUO Self Test Pin
7	NC	AUO Self Test Pin
8	Rxin0-	-LVDS differential data input
9	Rxin0+	+LVDS differential data input
10	GND	Ground
11	Rxin1-	-LVDS differential data input
12	Rxin1+	+LVDS differential data input
13	GND	Ground
14	Rxin2-	-LVDS differential data input
15	Rxin2+	+LVDS differential data input
16	GND	Ground
17	ClkIN-	-LVDS differential clock input
18	ClkIN+	+LVDS differential clock input
19	GND	Ground
20	Rxin3-	-LVDS differential data input

21	Rxin3+	+LVDS differential data input
22	GND	Ground
23	NC	No connect
24	NC	No connect
25	GND	Ground
26	NC	No connect
27	NC	No connect
28	GND	Ground
29	NC	No connect
30	NC	No connect
31	BL_GND	Ground for backlight
32	BL_GND	Ground for backlight
33	BL_GND	Ground for backlight
34	NC	No connect
35	LED_PWM	PWM Dimming
36	LED_EN	LED ON/OFF
37	NC	No connect
38	VLED	LED Power Supply +12V
39	VLED	LED Power Supply +12V
40	VLED	LED Power Supply +12V

6.2.2 LVDS Connector


Physical interface is described as for the connector on module.

These connectors are capable of accommodating the following signals and will be following components.

Connector Name / Designation	Signal Connector
Manufacturer	IPEX or compatible
Connector Model Number	IPEX 20765-040E-11A or compatible
Adaptable Plug	IPEX 20453-040T-01 or compatible

6.2.3 Touch Pin Assignment

PIN NO	Symbol	Function
1	GND_EARTH	GROUND
2	VDD	VDD
3	GND	GND
4	D+	USB D+
5	D-	USB D-



6.2.4 Touch Connector

Connector Name / Designation	Signal Connector
Manufacturer	ACES
Connector Model Number	ACES 50224-00501-001


6.3 Interface Timing

6.3.1 Timing Characteristics

Signal		Symbol	Min.	Typ.	Max.	Unit
Clock Frequency		1/ TClock	68.9	71.1	74.5	MHz
Vertical Section	Period	TV	815	823	840	TLine
	Active	TVD	800			
	Blanking	TVB	15	23	40	
Horizontal Section	Period	TH	1410	1440	1480	TClock
	Active	THD	1280			
	Blanking	THB	130	160	200	
Frame Rate		F	---	59.99	---	Hz


Note : DE mode.

6.3.2 Input Timing Diagram



6.3.3 The Input Data Format

8 bits LVDS Input (VESA Format)



Signal Name	Description	
R7 R6 R5 R4 R3 R2 R1 R0	Red Data 7 (MSB) Red Data 6 Red Data 5 Red Data 4 Red Data 3 Red Data 2 Red Data 1 Red Data 0 (LSB)	Red-pixel Data For 8Bits LVDS input MSB: R7 ; LSB: R0
G7 G6 G5 G4 G3 G2 G1 G0	Green Data 7 (MSB) Green Data 6 Green Data 5 Green Data 4 Green Data 3 Green Data 2 Green Data 1 Green Data 0 (LSB)	Green-pixel Data For 8Bits LVDS input MSB: R7 ; LSB: R0
B7 B6 B5 B4 B3 B2 B1 B0	Blue Data 7 (MSB) Blue Data 6 Blue Data 5 Blue Data 4 Blue Data 3 Blue Data 2 Blue Data 1 Blue Data 0 (LSB)	Blue-pixel Data For 8Bits LVDS input MSB: R7 ; LSB: R0
RxCLKIN	Data Clock	The signal is used to strobe the pixel data and DE signals. All pixel data shall be valid at the falling edge when the DE signal is high.
DE	Display Timing	This signal is strobed at the falling edge of RxCLKIN. When the signal is high, the pixel data shall be valid to be displayed.

Note: Output signals from any system shall be low or High-impedance state when VDD is off.

7. Reliability Test Criteria

Items	Required Condition	Note
Temperature Humidity Bias	40 °C /90%,300Hr	
High Temperature Operation	70°C, 300Hr	LCD Surface Temp.
Low Temperature Operation	-20 °C, 300Hr	
Hot Storage	80 °C, 300Hr	
Cold Storage	-30 °C, 300Hr	
Thermal Shock Test	-30 °C /30 min , 70 °C /30 min , 20cycles	
Hot Start Test	70 °C /1 Hr min. power on/off per 5 minutes, 5 times	
Cold Start Test	-20 °C /1 Hr min. power on/off per 5 minutes, 5 times	
On/off test	On/10 sec, Off/10 sec, 30,000 cycles	
ESD	Contact : $\pm 8KV$ / operation, Class B Air : $\pm 15KV$ / operation, Class B	Note 1
Shock test	50G,20ms,Half-sine wave, ($\pm X$, $\pm Y$, $\pm Z$), non-operation	
Vibration test	1.5G, (10~200Hz, random), 30 mins / axis (X, Y, Z),non-operation	


Note1: According to EN61000-4-2 , ESD class B: Some performance degradation allowed. No data lost
Self-recoverable. No hardware failures.

Note2:


- Water condensation is not allowed for each test items.
- Each test is done by new TFT-LCD module. Don't use the same TFT-LCD module repeatedly for reliability test.
- The reliability test is performed only to examine the TFT-LCD module capability.
- To inspect TFT-LCD module after reliability test, please store it at room temperature and room humidity for 24 hours at least in advance.

8. Mechanical Characteristics

8.1 Outline Dimension (Front View)



8.2 Outline Dimension (Rear View)




AUO Display+

9. Label and Packaging

9.1 Shipping Label (on the rear side of TFT-LCD display)



9.2 Carton/Pallet Package



Max capacity: 20 pcs TFT-LCD module per carton

Outside dimension of carton: 508(L) mm x 408 (W) mm x 279 (H) mm

Pallet size: 1150 * 840 * 132mm

Module by air: (2 * 2) * 5 layers , one pallet put 20 boxes, total 400 pcs module

Module by sea: One pallet (2 * 2) * 5 layers + One pallet (2 * 2) * 1 layers, total 480 pcs module

Module by sea_ HQ: One pallet (2 * 2) * 5 layers + One pallet (2 * 2) * 2 layers, Total 560 pcs module



AUO Display+

Product Specification

G101EAT02.6

10 Safety

10.1 Sharp Edge Requirements

There will be no sharp edges or comers on the display assembly that could cause injury.

10.2 Materials

10.2.1 Toxicity

There will be no carcinogenic materials used anywhere in the display module. If toxic materials are used, they will be reviewed and approved by the responsible AUO toxicologist.

10.2.2 Flammability

All components including electrical components that do not meet the flammability grade UL94-V1 in the module will complete the flammability rating exception approval process.

The printed circuit board will be made from material rated 94-V1 or better. The actual UL flammability rating will be printed on the printed circuit board.

10.3 Capacitors

If any polarized capacitors are used in the display assembly, provisions will be made to keep them from being inserted backwards.

10.4 National Test Lab Requirement

The display module will satisfy all requirements for compliance to:

UL 60950-1 second edition

U.S.A. Information Technology Equipment