

# SPECIFICATION

## OF

## LIQUID CRYSTAL DISPLAY MODULE



CUSTOMER : URT-STD

Model No. : UMOH-9729FD-T

Model version : 0

Document Revision : 2

CUSTOMER APPROVED SIGNATURE			

This specification need to be signed by purchaser or customer as a specification of products production and delivery from URT. Without signature of this specification , any purchase order for this model no. will be treated and considered that this specification is automatically acknowledged and accepted by purchaser or customer.

 **UNITED RADIANT TECHNOLOGY CORPORATION**

<u>Joe Wu</u> APPROVED	<u>Ashin Chiu</u> CHECKED	<u>Ashin Chiu</u> PREPARED	<u>Jun-04-2025</u> Date
---------------------------	------------------------------	-------------------------------	----------------------------

COMPANY : No. 2,Fu-hsing Road,Taichung Tanzi Technology Industrial Park,Tantzu,Taichung,Taiwan,R.O.C.  
TEL: 886-4-25314277 FAX: 886-4-25313067

## Revision record

Document Revision	Model No. Version No.	Description	Revision by
0	UMOH-9729MD-T Version No. 0	7" TFT.	William Don Emir Lu 04-Jan-2024
1	UMOH-9729MD-T Version No. 1	Update LCD Type Description..	William Don Emir Lu 02-Jun-2025
2	UMOH-9729FD-T Version No. 0	1. Update LCD Type Description. 2. Modify module number from UMOH-9729MD-T to UMOH-9729FD-T.	William Don Emir Lu 04-Jun-2025
 <b>U.R.T.</b>	Revision 2 ; UMOH-9729FD-T Ver. 0 ; June-04-2025		<b>Page: 2</b>

## CONTENTS:

No.	Item	Page
1	<b>BASIC SPECIFICATION</b> 1.1 Mechanical Specification 1.2 Display Specification 1.3 Outline Dimension 1.4 Block Diagram 1.5 Interface Pin	4 4 5 6 7
2	<b>ELECTRICAL CHARACTERISTICS</b> 2.1 Absolute Maximum Ratings 2.2 DC Characteristics 2.3 Back-light only Specification 2.4 LVDS DC Characteristics 2.5 LVDS AC Characteristics 2.6 LVDS Data Format 2.7 Input timing 2.8 Power On/OFF sequence	8 9 10 11 12 13 14 15
3	<b>OPTICAL CHARACTERISTICS</b> 3.1 Condition 3.2 Temperature Characteristics 3.3 Definition of Optical Characteristics	16 16 17~18
4	<b>RELIABILITY</b>	19
5	<b>PRODUCT HANDING AND APPLICATION</b>	20
6	<b>DATECODE</b>	21
7	<b>LOT NO</b>	22
8	<b>INSPECTION STANDARD</b>	23~25

## 1. BASIC SPECIFICATION

### 1.1 Mechanical specifications


Items	Nominal Dimension	Unit
Active screen size	7.0" Diagonal	-
Dot Matrix	800 x RGB x 480	Pixel
Module Size (W x H x T)	169.8 x 109.7 x 6.08	mm.
Active Area ( W×H )	152.4 x 91.44	mm.
Pixel Size ( W×H )	0.1905 x 0.1905	mm.
Color depth	16.7M	color
Interface	LVDS(6 bit/8 bit)	-
Driving IC Package	COG	-
Module weight	170± 10%	g

### 1.2 Display specification

Display	Descriptions	Note
LCD Type	TFT transflective (Micro Reflective)	-
LCD Mode	Normally black	-
Pixel arrangement	RGB-stripe	-
Backlight Type	LED	-
Viewing Direction	All Viewing	-

## 1. Outline of the dimension


CONFIDENTIAL(B)



**NOTE :** 1. Angular deviation of LCD cell from the TFT-LCD monitor's reference axis shall be less than  $\pm 50^\circ$ .

2. Protective film is affixed on front surface of the screen  
Protective film is not protrude from the outline of the monitor.  
3. Don't stress to the solder area.
4. Recommended FPC connectors: IRIS/MSA-06998-30A-GPI (lower contact)
5. Burns direction of S case is outward. (Burns size is less than 0.33mm)
6. Don't touch any conductive material to conductive area.
7. S case C and FPC conduction resistance value cannot be guaranteed.
8. The gap generated at the corner of the tape from S case to not questioned.
9. The inclination of conductive TAPE and surface wrinkles are unquestioned.
10. The inclination of insulation TAPE and surface wrinkles are unquestioned.
11. Mounted parts may not be completely hidden by insulating tape.
12. Tolerance for not assigned:  $\pm 5\text{mm}$
13. LCD TYPE TFT transreflective (Micro Reflective)

#### 1.4 Block Diagram:



## 1.5 Interface Pin Connection :

Pin No.	Pin Symbol	I/O	Description	Remark
1	BLH	P	LED Drive power source . (Anode side )	
2	BLL2	P	LED Drive power source . (Cathode side 2)	
3	BLL1	P	LED Drive power source . (Cathode side 1)	
4	GND	I	Ground.	
5~6	VDD	P	Power supply input.	
7	TEST1	I	Test input (connect to VDD)	
8	TEST2	I	Test input (connect to GND)	
9	TEST3	I	Test input (connect to GND)	
10	NC	-		
11	UL/DR	I	Up & Left / Down & Right switching terminal.(Low : DR , High or NC :UL)	
12	IM	I	6 / 8 bit(based on VESA) switching terminal.(Low : 6 bit , High or NC : 8 bit)	
13	STBYB	I	Standby signal.(Low : standby operation ; High : normal operation.)	
14	GND	P	Ground.	
15~16	R0- / R0+	I	LVDS differential data input.	
17	GND	P	Ground.	
18~19	R1- / R1+	I	LVDS differential data input.	
20	GND	P	Ground.	
21~22	CLK- / CLK+	I	LVDS differential clock input.	
23	GND	P	Ground.	
24~25	R2- / R2+	I	LVDS differential data input.	
26	GND	P	Ground.	
27~28	R3- / R3+	I	LVDS differential data input.	
29	GND	P	Ground.	
30	NC	-	No connection.	

### I: input, O: output, P: Power

- Recommended connector : IRISO ELECTRONICS 9699 series [IMSA-9699S-30A-GFN1]
- Please be sure to check a consistency between pin assignment in "3.2 Outward Form" and your connector pin assignment when designing your circuit.  
Inconsistency in input signal assignment may cause a malfunction.
- Since FPC cable has gold plated terminals, gilt finish contact shoe connector is recommended.

## 2. ELECTRICAL CHARACTERISTICS

### 2.1 Absolute Maximum Ratings

Items	Symbol	Min.	Max.	Unit
Power supply voltage	VDD	-0.3	3.9	V
Input voltage for logic	Vi	-0.3	VDD+0.3	V
Forward current	IL1,IL2	-	40	mA
Operate temperature range	TOP	-30	85	°C
Storage temperature range	TST	-40	95	°C
Storage Humidity	HD	20	90	% H

## 2.2 DC Characteristics:

### Typical Operation Conditions

Items	Symbol	Min.	Typ.	Max.	Unit	Condition
Digital Supply voltage	VDD	3.0	3.3	3.6	V	
Input Voltage for logic	VI	0	-	VDD	V	

### Current Consumption

Items	Symbol	Min.	Typ.	Max.	Unit	Condition
High Level input voltage	VIH	0.7VDD	-	VDD		
Low Level input voltage	VIL	0		0.3VDD		
Pull up / down resistor	RI	200	350	850	KΩ	IM,STBYB
		100	175	425	KΩ	UL/DR
Current for Driver	I <sub>VDD</sub>	-	38	76	mA	VDD = 3.3V

## 2.3 Back-light only Specification :

PARAMETER	SYMBOL	MIN	TYP	MAX	Unit	Test Condition	Remark
Voltage for LED backlight	VF1	-	18.5	19.8	V	BLH,BLL1	
	VF2		18.5	19.8	V	BLH,BLL2	
Current for LED backlight	IL1	-	20	40	mA	BLH,BLL1	
	IL2					BLH,BLL2	

Note1: - Please control so that each current does not vary (IL1 = IL2).


Note2: - The lifetime of the LED is defined as a period till the brightness of the LED decreases to the half of its initial value.

- This figure is given as a reference purpose only, and not as a guarantee.
- This figure is estimated for an LED operating alone.

As the performance of an LED may differ when assembled as a monitor together with a TFT panel due to different environmental temperature.

- Estimated lifetime could vary on a different temperature and usually higher temperature could reduce the life significantly.

**LED Circuit**




\* It is recommended to control currents of BLL1 / BLL2 to equal current values (IL1 = IL2).

## 2.4 LVDS DC Characteristics


(Unless otherwise noted,  $T_a=25\text{ }^{\circ}\text{C}$ ,  $VDD=3.3\text{V}$ ,  $GND=0\text{V}$ )

Item	Symbol	Condition	Rating			Unit	Applicable terminal
			MIN	TYP	MAX		
Differential input high threshold voltage	$Rxvth$	$Rxvcm=1.2\text{V}$	-	-	0.1	$\text{V}$	CLK+, CLK- R0+, R0-, R1+, R1- R2+, R2-, R3+, R3-
Differential input low threshold voltage	$Rxvtl$		-0.1	-	-	$\text{V}$	
Differential input common Mode voltage	$Rxvcm$		1.0	1.2	$1.8- V_{ID} /2$	$\text{V}$	
Differential input voltage	$ V_{ID} $		0.2	-	0.6	$\text{V}$	
Differential input leakage current	$RV_{\text{leak}}$		-10	-	+10	$\mu\text{A}$	

### Single end signals





### Differential signals



## 2.5 LVDS AC Characteristics


(Unless otherwise noted,  $T_a=25\text{ }^{\circ}\text{C}$ ,  $V_{DD}=3.3\text{V}$ ,  $GND=0\text{V}$ )

Item	Symbol	Rating			Unit
		MIN	TYP	MAX	
CLK Frequency	$f_{clk}$	25.2	27.2	30.5	MHz
Clock period	$T_c$	32.8	36.8	39.7	ns
1 data bit time	UI	-	1/7	-	$T_c$
CLK High level Width	$T_{chw}$	2.9	4	4.1	UI
CLK Low level Width	$T_{clw}$	2.9	3	4.1	UI
Position 1	$T_{pos\_1}$	-0.2	0	0.2	UI
Position 0	$T_{pos\_0}$	0.8	1	1.2	UI
Position 6	$T_{pos\_6}$	1.8	2	2.2	UI
Position 5	$T_{pos\_5}$	2.8	3	3.2	UI
Position 4	$T_{pos\_4}$	3.8	4	4.2	UI
Position 3	$T_{pos\_3}$	4.8	5	5.2	UI
Position 2	$T_{pos\_2}$	5.8	6	6.2	UI
Reciever Strobe Position 7	TEYEW	0.6	-	-	UI
Reciever Strobe Position 8	TEX	-	-	0.2	UI




## 2.6 LVDS Data Format

VESA Format 8bit




VESA Format 6bit




## 2.7 Input timing

Item	Symbol	Rating			Unit	Signal ( * )
		MIN	TYP	MAX		
CLK frequency	fCLK	25.2	27.2	30.5	MHz	CLK
VD frequency	fVD	-	60	-	Hz	VD
1 vertical field	tv	490	528	552	H	
VD pulse width	tvp	1	2	66	H	
VD back porch	tvb	5	10	67	H	VD,HD,ENAB
VD front porch	tvf	5	38	67	H	
Vertical valid data	tvdp	480			H	
HD frequency	fHD	-	28.8	-	kHz	HD
1 horizontal field	th	856	860	920	CLK	
HD pulse width	thp	1	2	100	CLK	
HD back porch	thb	5	16	101	CLK	CLK,HD,ENAB
HD front porch	thf	19	44	115	CLK	
ENAB pulse width	tenp	800			CLK	
Horizontal valid data	thdp	800			CLK	R[7:0],G[7:0],B[7:0]

( \*) Input terminals are (R0+/-, R1+/-, R2+/-, R3+/-, CLK+/-).



## 2.8 Power On/OFF sequence



Note : ENAB , HD and VD are include in the R2+ / R2- terminals.


### 3. OPTICAL CHARACTERISTICS

#### 3.1 Characteristics

##### Electrical and Optical Characteristics

Measured temperature:  $T_a=25^\circ C$

No.	Item	symbol / temp.		Min.	Typ.	Max.	Unit	Note
1	Response Time	Tr+Tf	25 °C	-	50	100	ms	2
2	Viewing Angle	Hor. Ver.	$Cr \geq 10$	$\theta_{2+}$	$\Phi = 0^\circ$	80	-	-
				$\theta_{2-}$	$\Phi = 180^\circ$	80	-	-
				$\theta_{1+}$	$\Phi = 270^\circ$	80	-	-
				$\theta_{1-}$	$\Phi = 90^\circ$	80	-	-
3	Contrast Ratio	Cr	25 °C	350	700	-	-	4
4	White x-code	Wx	25 °C	White Chromaticity Range			-	5
	White y-code	Wy		240	400	-	cd/m <sup>2</sup>	
	Brightness	Y		70	-	-	%	
5	Brightness Uniformity		25 °C					6



[White Chromaticity Range ]


x	y
0.29	0.38
0.27	0.34
0.27	0.28
0.28	0.27
0.34	0.27
0.36	0.31
0.36	0.37
0.35	0.38

#### 3.2 Temperature Characteristics

Item	Symbol	Specification			Remark
		MIN	TYP	MAX	
Contrast ratio	CR	200	-	-	Ta=-30°C Backlight ON
		200	-	-	Ta=85°C Backlight ON
Response time Rise time + Fall time	TON + TOFF	-	980ms	1500ms	Ta=-30°C
		-	40ms	80ms	Ta=85°C
Display Quality		No noticeable display defect or ununiformity should be observed.			


### 3.3 Definition of optical characteristics

Measurement condition : Transmissive mode optical measurement system




LCD Evaluation System : DMS-803  
Light Source : Halogen Lamp.


#### [Note 1] Definition of LCD Driving Vop and Waveform :




#### [Note 2] Definition of Response Time




#### [Note 3] Definition of Viewing Angle :




#### [Note 4] Definition of Contrast Ratio :




**[Note 5] Definition of measurement of Color Chromaticity and Brightness**



**[Note 6] Definition of Brightness Uniformity**



#### 4. RELIABILITY :

Item No	Items	Condition	Note
1	High temperature operating	85 °C , 240 hours	1
2	Low temperature operating	-30 °C , 240 hours	1
3	High temperature storage	95 °C , 240 hours	1
4	Low temperature storage	-40 °C , 240 hours	1
5	High temperature & humidity storage	60°C, 90%RH, 240 hours	2
6	Thermal Shock storage	-40°C, 30min.<=> 95°C, 30min. 10 Cycles	
7	Vibration test	Total amplitude 1.5mm , f : 10~55Hz X , Y , Z directions for each 30mins.	
8	Electrostatic discharge test (Non operation)	C : 200pF , R : 0Ω , V : ±200V Each 3 times of discharge on and power supply and other terminals.	
9	Surface discharge test (Non operation)	C : 250pF , R : 100Ω , V : ±12KV Each 3 times of discharge on and power supply and other terminals.	
10	Packing drop test	Drop from 75cm high 1 time to each 6 surfaces , 3 edges , 1 corner.	
11	Image Sticking Test	$25 \pm 2^\circ\text{C}$ Operation with test pattern sustained for 2 hrs, then change to gray pattern immediately. After 5 mins, the mura must be disappeared completely <div style="display: flex; justify-content: space-around; align-items: center; margin-top: 10px;">  <span>Image Sticking - pattern</span>  <span>Mid-Grav pattern</span> </div>	

Note 2 : The product move into the room temperature for at least 24 hours with no condensation.

Note 3 : Please change the display picture (autorun) during operating mode. Avoid displaying static images to avoid image sticking , and the image sticking is accelerated by temperature.

Note 4: In case of malfunction defect caused by ESD damage, if it would be recovered to normal state after resetting, it would be judged as a good part.

- \* One single product test for only one item.
- \* Judgment after test : keep in room temperature for more than 2 hours.
  - Current consumption < 2 times of initial value
  - Function : work normally

## 5. PRODUCT HANDLING AND APPLICATION

### 5.1 PRECAUTION FOR HANDLING LCM

- The LCD module contains a C-MOS LSI. People who operate the LCM should wear ESD protection equipment to prevent ESD hurt on products.
- Do not input any signal before power is turned on.
- Do not take LCM from its packaging bag until it is assembled.
- Peel off the LCM protective film slowly since static electricity may be generated.
- Hand Soldering : Soldering temperature less than 260°C, within 5 sec, at 5 mm. Away from pin connection.
- Do not touch the display surface or connection terminals area with bare hands. Smudges on the display surface reduce the insulation between terminals.
- Do not twist or bend the modules and also avoid any inappropriate external force on display surface during assembly.
- Do not expose LCM to organic solvent. If clean the surface, wipe it gently with soft cloth dampened by alcohol.
- Do not attempt to wipe off the contact pads.
- Keep LCM panels away from direct sunlight or fluorescent light, also avoid them in high-temperature & high humidity environment for a long period.
- It is an indispensable condition to drive LCD's within the specified voltage limit since the higher voltage then the limit cause the shorter LCD life.
- Do not drive LCM by DC voltage & avoid displaying at certain pattern for a long time otherwise it might cause image sticking.
- Response time will be extremely delayed at lower temperature than the operating temperature range and on the other hand at higher temperature LCD's have dark color in them. However those phenomena do not mean malfunction or out of order with LCD's, which will come back in the specified operation temperature.
- If the display area is pushed hard during operation, some font will be abnormally displayed but it resumes normal condition after turning off once.
- Never use the LCD, LCM under 45 Hz, the liquid crystal will decompose and cause perfectly damage on display !!
- Liquid in LCM is hazardous substance. In case a contact with liquid crystal material is occurred, be sure to immediately wash such material away by soap and water.
- The polarizer is easily damaged and should be handled with special care. Don't press or rub it with hard objects.

### 5.2 PRECAUTION FOR STORING

- Store the module in a dark room where must keep at 25±10°C and 65%RH or less.
- Do not store the module in surroundings containing organic solvent or corrosive gas
- Store the module in an anti-electrostatic container or bag.

### 5.3 USING ON MEDICAL CARE , SAFETY OR HAZARDOUS APPLICATION OR SYSTEM

- For the application in medical care, safety and hazardous products or systems, an authorization from URT is required. URT will not be responsible for any damage or loss which caused by the products without any authorization given by URT.
- This product is not allowed to be designed and used for military application and/or purpose.
- The delivery of this product to the countries and/or regions where the embargoes are imposed by U.N. is prohibited.
- The application and delivery of this product must comply with Strategic High-Tech Commodities (SHTC) export control and the sales to the embargoed and/or sanctioned countries or regions are strictly prohibited.

## 6. DATE CODE OF PRODUCTS

- Date code will be shown on each product :

- **YY MM DD - XXXX**

Year Month Day - Production lots no.


- Example: 241108 - 0003 ==> Year 2024, November,8th ,  
Production lots no. 0003

Note : The lot no. attached on the packing box will be used for tracking once the part is too small to print the date code.


## 7. LOT NO

Instruction of lot number:

LOT NO. : 0 0 0 8 3 5 2 5 (ex)



Label of carton:



## **8. INSPECTION STANDARD**

### **8.1. QUALITY :**

THE QUALITY OF GOODS SUPPLIED TO PURCHASER SHALL COME UP TO THE FOLLOWING STANDARD.

#### **8.1.1. THE METHOD OF PRESERVING GOODS**

AFTER DELIVERY OF GOODS FROM U.R.T. TO PURCHASER. PURCHASER SHALL CONTROL THE LCM AT -10 °C ~40 °C ,AND IT MIGHT BE DESIRABLE TO KEEP AT THE NORMAL ROOM TEMPERATURE AND HUMIDITY UNTIL INCOMING INSPECTION OR THROWING INTO PROCESS LINE.

#### **8.1.2. INCOMING INSPECTION**

##### **(A) THE METHOD OF INSPECTION**

IF PURCHASER MAKE AN INCOMING INSPECTION , A SAMPLING PLAN SHALL BE APPLIED ON THE CONDITION THAT QUALITY OF ONE DELIVERY SHALL BE REGARDED AS ONE LOT.

##### **(B) THE STANDARD OF QUALITY**

ISO-2859-1 (SAME AS MIL-STD-105E ) , LEVEL II SINGLE PLAN.

##### **(C) MEASURE**

IF AS THE RESULT OF ABOVE RECEIVING INSPECTION , A LOT OUT IS DISCOVERED. PURCHASER SHALL BE INFORM SELLER OF IT WITHIN SEVEN DAYS. BUT FIRST SHIPMENT WITHIN FOURTEEN DAYS.

#### **8.1.3. WARRANTY POLICY**

U.R.T. WILL PROVIDE ONE-YEAR WARRANTY FOR THE PRODUCTS ONLY IF UNDER SPECIFICATION OPERATING CONDITIONS. U.R.T. WILL REPLACE GOOD PRODUCTS FOR THESE DEFECT PRODUCTS WHICH UNDER WARRANTY PERIOD AND BELONG TO THE RESPONSIBILITY OF U.R.T.

#### **8.1.4 Illustrate of The Inspection**

Samples are used to assist and verify compliance with specifications, not as inspection standards. If a physical sample is required as the inspection standard, both parties shall jointly determine and sign "Inspection sample or Limited sample (with upper limit and lower limit ) " .

## 8.2 Standard of Visual Inspection :


### 8.2.1 Defective Display and Screen Quality

Test Condition: Observed TFT-LCD monitor from front during operation with the following conditions

Driving Signal Raster Patter (RGB, white, black)

Observation distance 30 cm

Illuminance 200 to 350 lx



Defect item	Defect content		Criteria
Display Quality	Line defect	Black, white or color line, 3 or more neighboring defective dots	
	Dot defect	Uneven brightness on dot-by-dot base due to defective TFT or CF, or dust is counted as dot defect (brighter dot, darker dot) Dark dot: Appear dark through white display	
Screen Quality	Dirt	Uneven brightness (white stain, black stain etc)	
	Foreign particle	Point-like	$0.25\text{mm} < \varphi$ $0.20\text{mm} < \varphi \leq 0.25\text{mm}$ $\varphi \leq 0.20\text{mm}$
Screen Quality		Liner	$3.0\text{mm} < \text{length and } 0.08\text{mm} < \text{width}$ $\text{length} \leq 3.0\text{mm or width} \leq 0.08\text{mm}$
Others	Use boundary sample for judgment when necessary		

$\varphi(\text{mm})$ : Average diameter = (major axis + minor axis)/2  
Permissible number: N

Table 1

Judgment screen	black	gray	red	green	blue	Total
Bright dot	○	don't judge	○	○	○	0
Dark dot	don't judge	○	○	○	○	1 or less

Definition of bright dot and dark dot

List of screens	R	G	B
black	00h	00h	00h
gray	94h	94h	94h
red	94h	00h	00h
green	00h	94h	00h
blue	00h	00h	94h

### 8.2.2 Screen and Other Appearance

## Testing conditions

### Observation distance

30cm

## Illuminance

1200~2000 lx

Item		Criteria	Remark
Polarizer	Flaw Stain Bubble Dust Dent	Ignore invisible defect when the backlight is on.	Applicable area: Active area only (Refer to the section 1.3 3.2 "Outward form")
S-case		No functional defect occurs	
FPC cable		No functional defect occurs	