



AUO Display+

G057QTN01.4

() Preliminary Specifications

(V) Final Specifications

Module		5.7 Inch Color TFT-LCD
Model Name		G057QTN01.4

Customer	Date
_____	_____
Checked & Approved by	
_____	_____
Note: This Specification is subject to change without notice.	

Approved by	Date
LeadDer Feng	2021/7/13
Prepared by	
Carol Wong	2021/7/13
General Display Business Unit / AUO Display Plus Corporation	

Contents

1. Operating Precautions.....	10
2. General Description.....	11
2.1 Display Characteristics	11
2.2 Optical Characteristics	12
3. Functional Block Diagram	15
4. Absolute Maximum Ratings	16
4.1 Absolute Ratings of TFT LCD Module	16
4.2 Absolute Ratings of Environment	16
5. Electrical Characteristics	17
5.1 TFT LCD Module.....	17
5.2 Backlight Unit	18
6. Signal Characteristic	20
6.1 Pixel Format Image	20
6.2 Scanning Direction	21
The following figures show the image seen from the front view. The arrow indicates the direction of scan.	21
6.3 TFT- LCD Interface Signal Description	21
6.4 The Input Data Format.....	23
6.5 Interface Timing.....	24
6.7 Power ON/OFF Sequence.....	27
7. Connector & Pin Assignment.....	28
7.1 TFT- LCD Signal (CN1): LCD Connector.....	28
7.2 Backlight Power (CN2): LED Connector.....	28
8. Reliability Test Criteria	30
9. Mechanical Characteristics	31
10. Label and Packaging.....	32
10.1 Shipping Label (on the rear side of TFT-LCD display).....	32
10.2 Carton Package	32
.....	32
11 Safety.....	33
11.1 Sharp Edge Requirements	33
11.2 Materials	33
11.3 Capacitors	33
11.4 National Test Lab Requirement	33

Version and Date		Page	Old description	New Description			
0.0	2021/1/22	All	First Edition				
0.1	2021/2/26	7	Color / Chromaticity Coordinates (CIE 1931)	Color / Chromaticity Coordinates (CIE 1931)			
		12	Item Symbol Min Max Unit Remark	Item Symbol Min Max Unit Remark			
		13	5.1.1 Power Specification	5.1.1 Power Specification			
		14	5.2.1 Parameter guideline for LED	5.2.1 Parameter guideline for LED			
		19	DCLK (Positive Polarity) DE (Positive Polarity) DIN DCLK (Negative Polarity) DE (Positive Polarity) DIN	Data DEN			
		20	6.5.2 Input Timing Diagram	6.5.2 Input Timing Diagram			

	21	<table><tr><th>Pin #</th><th>Symbol</th><th>Pin Description</th></tr><tr><td>1</td><td>VLED</td><td>12V input</td></tr><tr><td>2</td><td>VLED</td><td>12V input</td></tr><tr><td>3</td><td>GND</td><td>Ground</td></tr><tr><td>4</td><td>GND</td><td>Ground</td></tr><tr><td>5</td><td>LED On/Off</td><td>0V-Off, 2~5V/NC-On</td></tr><tr><td>6</td><td>PWM DIM</td><td>1~100% PWM dimming</td></tr></table> <p>Note 1: "NC" stands for "No Connection"</p>	Pin #	Symbol	Pin Description	1	VLED	12V input	2	VLED	12V input	3	GND	Ground	4	GND	Ground	5	LED On/Off	0V-Off, 2~5V/NC-On	6	PWM DIM	1~100% PWM dimming	<table><tr><th>Pin #</th><th>Symbol</th><th>Pin Description</th></tr><tr><td>1</td><td>VLED</td><td>Backlight Power Supply Voltage</td></tr><tr><td>2</td><td>VLED</td><td>Backlight Power Supply Voltage</td></tr><tr><td>3</td><td>GND</td><td>Ground</td></tr><tr><td>4</td><td>GND</td><td>Ground</td></tr><tr><td>5</td><td>LED On/Off</td><td>Backlight ON-OFF(ON:2.5~5V,OFF:0~0.8V)</td></tr><tr><td>6</td><td>PWM DIM</td><td>Light Dimming Control(PWM)input(High active)</td></tr></table>	Pin #	Symbol	Pin Description	1	VLED	Backlight Power Supply Voltage	2	VLED	Backlight Power Supply Voltage	3	GND	Ground	4	GND	Ground	5	LED On/Off	Backlight ON-OFF(ON:2.5~5V,OFF:0~0.8V)	6	PWM DIM	Light Dimming Control(PWM)input(High active)																																																																						
Pin #	Symbol	Pin Description																																																																																																																	
1	VLED	12V input																																																																																																																	
2	VLED	12V input																																																																																																																	
3	GND	Ground																																																																																																																	
4	GND	Ground																																																																																																																	
5	LED On/Off	0V-Off, 2~5V/NC-On																																																																																																																	
6	PWM DIM	1~100% PWM dimming																																																																																																																	
Pin #	Symbol	Pin Description																																																																																																																	
1	VLED	Backlight Power Supply Voltage																																																																																																																	
2	VLED	Backlight Power Supply Voltage																																																																																																																	
3	GND	Ground																																																																																																																	
4	GND	Ground																																																																																																																	
5	LED On/Off	Backlight ON-OFF(ON:2.5~5V,OFF:0~0.8V)																																																																																																																	
6	PWM DIM	Light Dimming Control(PWM)input(High active)																																																																																																																	
	22	<table><tr><td>Manufacturer</td><td>STM or compatible</td></tr><tr><td>Connector Model Number</td><td>MSK24022P10 or compatible</td></tr></table>	Manufacturer	STM or compatible	Connector Model Number	MSK24022P10 or compatible	<table><tr><td>Manufacturer</td><td>JAE</td></tr><tr><td>Connector Model Number</td><td>FI-S6P-HFE, compatible with FI-S6S</td></tr></table>	Manufacturer	JAE	Connector Model Number	FI-S6P-HFE, compatible with FI-S6S																																																																																																								
Manufacturer	STM or compatible																																																																																																																		
Connector Model Number	MSK24022P10 or compatible																																																																																																																		
Manufacturer	JAE																																																																																																																		
Connector Model Number	FI-S6P-HFE, compatible with FI-S6S																																																																																																																		
	23																																																																																																																		
0.2 2021/3/26	14	<p>5.2.1 Parameter guideline for LED Following characteristics are measured under stable condition using a LED driving board at 25°C(Room Temperature).</p> <table><tr><th>Symbol</th><th>Parameter</th><th>Min</th><th>Typ</th><th>Max</th><th>Units</th><th>Remark</th></tr><tr><td>VLED</td><td>Input Voltage</td><td>4.5</td><td>5</td><td>5.5</td><td>Volt</td><td></td></tr><tr><td>ILED</td><td>Input Current</td><td>-</td><td>TBD</td><td>-</td><td>A</td><td>VLED=5V, D_{PWM}=100%</td></tr><tr><td>PWM</td><td>Backlight power control input voltage</td><td>2.5</td><td>-</td><td>VLED</td><td>V</td><td>ON</td></tr><tr><td></td><td></td><td>0</td><td>-</td><td>0.8</td><td>V</td><td>OFF</td></tr><tr><td>F_{PWM}</td><td>Dimming Frequency</td><td>TBD</td><td>200</td><td>600</td><td>Hz</td><td>Note 1,2</td></tr><tr><td>D_{PWM}</td><td>Dimming duty cycle</td><td>0.01</td><td></td><td>100</td><td>%</td><td></td></tr><tr><td>LT</td><td>Operating life</td><td></td><td>75000</td><td>100000</td><td>Hrs</td><td>Note 3,4</td></tr></table>	Symbol	Parameter	Min	Typ	Max	Units	Remark	VLED	Input Voltage	4.5	5	5.5	Volt		ILED	Input Current	-	TBD	-	A	VLED=5V, D _{PWM} =100%	PWM	Backlight power control input voltage	2.5	-	VLED	V	ON			0	-	0.8	V	OFF	F _{PWM}	Dimming Frequency	TBD	200	600	Hz	Note 1,2	D _{PWM}	Dimming duty cycle	0.01		100	%		LT	Operating life		75000	100000	Hrs	Note 3,4	<p>5.2.1 Parameter guideline for LED Following characteristics are measured under stable condition using a LED driving board at 25°C(Room Temperature).</p> <table><tr><th>Symbol</th><th>Parameter</th><th>Min</th><th>Typ</th><th>Max</th><th>Units</th><th>Remark</th></tr><tr><td>VLED</td><td>Input Voltage</td><td>4.5</td><td>5</td><td>5.5</td><td>Volt</td><td></td></tr><tr><td>ILED</td><td>Input Current</td><td>-</td><td>TBD</td><td>-</td><td>A</td><td>VLED=5V, D_{PWM}=100%</td></tr><tr><td>PWM</td><td>Backlight power control input voltage</td><td>2.5</td><td>-</td><td>VLED</td><td>V</td><td>ON</td></tr><tr><td></td><td></td><td>0</td><td>-</td><td>0.8</td><td>V</td><td>OFF</td></tr><tr><td>F_{PWM}</td><td>Dimming Frequency</td><td>TBD</td><td>200</td><td>600</td><td>Hz</td><td>Note 1,2</td></tr><tr><td>D_{PWM}</td><td>Dimming duty cycle</td><td>0.1</td><td></td><td>100</td><td>%</td><td></td></tr><tr><td>LT</td><td>Operating life</td><td></td><td>75000</td><td>100000</td><td>Hrs</td><td>Note 3,4</td></tr></table>	Symbol	Parameter	Min	Typ	Max	Units	Remark	VLED	Input Voltage	4.5	5	5.5	Volt		ILED	Input Current	-	TBD	-	A	VLED=5V, D _{PWM} =100%	PWM	Backlight power control input voltage	2.5	-	VLED	V	ON			0	-	0.8	V	OFF	F _{PWM}	Dimming Frequency	TBD	200	600	Hz	Note 1,2	D _{PWM}	Dimming duty cycle	0.1		100	%		LT	Operating life		75000	100000	Hrs	Note 3,4
Symbol	Parameter	Min	Typ	Max	Units	Remark																																																																																																													
VLED	Input Voltage	4.5	5	5.5	Volt																																																																																																														
ILED	Input Current	-	TBD	-	A	VLED=5V, D _{PWM} =100%																																																																																																													
PWM	Backlight power control input voltage	2.5	-	VLED	V	ON																																																																																																													
		0	-	0.8	V	OFF																																																																																																													
F _{PWM}	Dimming Frequency	TBD	200	600	Hz	Note 1,2																																																																																																													
D _{PWM}	Dimming duty cycle	0.01		100	%																																																																																																														
LT	Operating life		75000	100000	Hrs	Note 3,4																																																																																																													
Symbol	Parameter	Min	Typ	Max	Units	Remark																																																																																																													
VLED	Input Voltage	4.5	5	5.5	Volt																																																																																																														
ILED	Input Current	-	TBD	-	A	VLED=5V, D _{PWM} =100%																																																																																																													
PWM	Backlight power control input voltage	2.5	-	VLED	V	ON																																																																																																													
		0	-	0.8	V	OFF																																																																																																													
F _{PWM}	Dimming Frequency	TBD	200	600	Hz	Note 1,2																																																																																																													
D _{PWM}	Dimming duty cycle	0.1		100	%																																																																																																														
LT	Operating life		75000	100000	Hrs	Note 3,4																																																																																																													
	25	<p>9. Mechanical Characteristics</p>	<p>9. Mechanical Characteristics</p>																																																																																																																
0.3 2021/4/16	23																																																																																																																		
	25	<p>9. Mechanical Characteristics</p>	<p>9. Mechanical Characteristics</p>																																																																																																																


0.4 2021/5/5	15	<h3>4.1 Absolute Ratings of TFT LCD Module</h3> <table><thead><tr><th>Item</th><th>Symbol</th><th>Min</th><th>Max</th><th>Unit</th><th>Remark</th></tr></thead><tbody><tr><td>Logic/LCD Drive Voltage</td><td>VDD</td><td>0</td><td>+5</td><td>Volt</td><td>Ta= 25°C</td></tr><tr><td>LCD Input Signal Voltage</td><td>VIN</td><td>0</td><td>+5</td><td>Volt</td><td>Ta= 25°C</td></tr><tr><td>LED BLU Drive Voltage</td><td>VLED</td><td>0</td><td>23</td><td>Volt</td><td>Ta= 25°C</td></tr><tr><td>LED Dimming Input Voltage</td><td>VPWM</td><td>0</td><td>5.5</td><td>Volt</td><td>Ta= 25°C</td></tr><tr><td>LED On/Off Input Voltage</td><td>VLED-ON/OFF</td><td>0</td><td>5.5</td><td>Volt</td><td>Ta= 25°C</td></tr></tbody></table>	Item	Symbol	Min	Max	Unit	Remark	Logic/LCD Drive Voltage	VDD	0	+5	Volt	Ta= 25°C	LCD Input Signal Voltage	VIN	0	+5	Volt	Ta= 25°C	LED BLU Drive Voltage	VLED	0	23	Volt	Ta= 25°C	LED Dimming Input Voltage	VPWM	0	5.5	Volt	Ta= 25°C	LED On/Off Input Voltage	VLED-ON/OFF	0	5.5	Volt	Ta= 25°C	<h3>4.1 Absolute Ratings of TFT LCD Module</h3> <table><thead><tr><th>Item</th><th>Symbol</th><th>Min</th><th>Max</th><th>Unit</th><th>Remark</th></tr></thead><tbody><tr><td>Logic/LCD Drive Voltage</td><td>VDD</td><td>-0.3</td><td>+4.0</td><td>Volt</td><td>Ta= 25°C</td></tr><tr><td>LCD Input Signal Voltage</td><td>VIN</td><td>-0.3</td><td>+4.0</td><td>Volt</td><td>Ta= 25°C</td></tr><tr><td>LED BLU Drive Voltage</td><td>VLED</td><td>-0.3</td><td>42</td><td>Volt</td><td>Ta= 25°C</td></tr><tr><td>LED Dimming Input Voltage</td><td>VPWM</td><td>-0.3</td><td>+6</td><td>Volt</td><td>Ta= 25°C</td></tr><tr><td>LED On/Off Input Voltage</td><td>VLED-ON/OFF</td><td>-0.3</td><td>+6</td><td>Volt</td><td>Ta= 25°C</td></tr></tbody></table>	Item	Symbol	Min	Max	Unit	Remark	Logic/LCD Drive Voltage	VDD	-0.3	+4.0	Volt	Ta= 25°C	LCD Input Signal Voltage	VIN	-0.3	+4.0	Volt	Ta= 25°C	LED BLU Drive Voltage	VLED	-0.3	42	Volt	Ta= 25°C	LED Dimming Input Voltage	VPWM	-0.3	+6	Volt	Ta= 25°C	LED On/Off Input Voltage	VLED-ON/OFF	-0.3	+6	Volt	Ta= 25°C																																																																																																						
Item	Symbol	Min	Max	Unit	Remark																																																																																																																																																																												
Logic/LCD Drive Voltage	VDD	0	+5	Volt	Ta= 25°C																																																																																																																																																																												
LCD Input Signal Voltage	VIN	0	+5	Volt	Ta= 25°C																																																																																																																																																																												
LED BLU Drive Voltage	VLED	0	23	Volt	Ta= 25°C																																																																																																																																																																												
LED Dimming Input Voltage	VPWM	0	5.5	Volt	Ta= 25°C																																																																																																																																																																												
LED On/Off Input Voltage	VLED-ON/OFF	0	5.5	Volt	Ta= 25°C																																																																																																																																																																												
Item	Symbol	Min	Max	Unit	Remark																																																																																																																																																																												
Logic/LCD Drive Voltage	VDD	-0.3	+4.0	Volt	Ta= 25°C																																																																																																																																																																												
LCD Input Signal Voltage	VIN	-0.3	+4.0	Volt	Ta= 25°C																																																																																																																																																																												
LED BLU Drive Voltage	VLED	-0.3	42	Volt	Ta= 25°C																																																																																																																																																																												
LED Dimming Input Voltage	VPWM	-0.3	+6	Volt	Ta= 25°C																																																																																																																																																																												
LED On/Off Input Voltage	VLED-ON/OFF	-0.3	+6	Volt	Ta= 25°C																																																																																																																																																																												
	17	<h3>5.1.2 Signal Electrical Characteristics</h3> <p>Input signals shall be low or Hi-Z state when VDD is off.</p> <table><thead><tr><th>Parameter</th><th>Symbol</th><th>Min.</th><th>Typ.</th><th>Max.</th><th>Unit</th><th>Remarks</th></tr></thead><tbody><tr><td rowspan="2">Logic Input Voltage for Display Signals</td><td>High VIH</td><td>0.7VDD</td><td>-</td><td>VDD</td><td>Volt</td><td></td></tr><tr><td>Low VIL</td><td>0</td><td>-</td><td>0.3VDD</td><td>Volt</td><td></td></tr><tr><td rowspan="2">Input Voltage for RL/UD</td><td>High VIH</td><td>0.7VDD</td><td>-</td><td>VDD</td><td>Volt</td><td></td></tr><tr><td>Low VIL</td><td>0</td><td>-</td><td>0.2VDD</td><td>Volt</td><td></td></tr></tbody></table>	Parameter	Symbol	Min.	Typ.	Max.	Unit	Remarks	Logic Input Voltage for Display Signals	High VIH	0.7VDD	-	VDD	Volt		Low VIL	0	-	0.3VDD	Volt		Input Voltage for RL/UD	High VIH	0.7VDD	-	VDD	Volt		Low VIL	0	-	0.2VDD	Volt		<h3>5.1.2 Signal Electrical Characteristics</h3> <p>Input signals shall be low or Hi-Z state when VDD is off.</p> <table><thead><tr><th>Parameter</th><th>Symbol</th><th>Min.</th><th>Typ.</th><th>Max.</th><th>Unit</th><th>Remarks</th></tr></thead><tbody><tr><td rowspan="2">Logic Input Voltage for Display Signals</td><td>High VIH</td><td>0.7VDD</td><td>-</td><td>VDD</td><td>Volt</td><td></td></tr><tr><td>Low VIL</td><td>0</td><td>-</td><td>0.3VDD</td><td>Volt</td><td></td></tr><tr><td rowspan="2">Input Voltage for RL/UD</td><td>High VIH</td><td>VDD-0.4</td><td>-</td><td>VDD</td><td>Volt</td><td></td></tr><tr><td>Low VIL</td><td>0</td><td>-</td><td>GND+0.4</td><td>Volt</td><td></td></tr></tbody></table>	Parameter	Symbol	Min.	Typ.	Max.	Unit	Remarks	Logic Input Voltage for Display Signals	High VIH	0.7VDD	-	VDD	Volt		Low VIL	0	-	0.3VDD	Volt		Input Voltage for RL/UD	High VIH	VDD-0.4	-	VDD	Volt		Low VIL	0	-	GND+0.4	Volt																																																																																																													
Parameter	Symbol	Min.	Typ.	Max.	Unit	Remarks																																																																																																																																																																											
Logic Input Voltage for Display Signals	High VIH	0.7VDD	-	VDD	Volt																																																																																																																																																																												
	Low VIL	0	-	0.3VDD	Volt																																																																																																																																																																												
Input Voltage for RL/UD	High VIH	0.7VDD	-	VDD	Volt																																																																																																																																																																												
	Low VIL	0	-	0.2VDD	Volt																																																																																																																																																																												
Parameter	Symbol	Min.	Typ.	Max.	Unit	Remarks																																																																																																																																																																											
Logic Input Voltage for Display Signals	High VIH	0.7VDD	-	VDD	Volt																																																																																																																																																																												
	Low VIL	0	-	0.3VDD	Volt																																																																																																																																																																												
Input Voltage for RL/UD	High VIH	VDD-0.4	-	VDD	Volt																																																																																																																																																																												
	Low VIL	0	-	GND+0.4	Volt																																																																																																																																																																												
	17	<h3>5.2.1 Parameter guideline for LED</h3> <p>Following characteristics are measured under stable condition using a LED driving board at 25°C(Room Temperature).</p> <table><thead><tr><th>Symbol</th><th>Parameter</th><th>Min</th><th>Typ</th><th>Max</th><th>Units</th><th>Remark</th></tr></thead><tbody><tr><td>VLED</td><td>Input Voltage</td><td>4.5</td><td>5</td><td>5.5</td><td>Volt</td><td></td></tr><tr><td>ILED</td><td>Input Current</td><td>-</td><td>TBD</td><td>-</td><td>A</td><td>VLED =5V, DPM =100%</td></tr><tr><td>PLED</td><td>Power Consumption</td><td>-</td><td>TBD</td><td>-</td><td>W</td><td>VLED =5V, DPM =100%</td></tr><tr><td>InrushLED</td><td>Inrush Current</td><td>-</td><td>TBD</td><td>-</td><td>A</td><td>VLED =5V, DPM =100%</td></tr><tr><td rowspan="2">VPWM DIM</td><td rowspan="2">Backlight power control input voltage</td><td>1.2</td><td>-</td><td>5.5</td><td>V</td><td>ON</td></tr><tr><td>-</td><td>-</td><td>0.4</td><td>V</td><td>OFF</td></tr><tr><td>FPWM</td><td>Dimming Frequency</td><td>100</td><td>-</td><td>600</td><td>Hz</td><td></td></tr><tr><td>DPWM</td><td>Dimming duty cycle</td><td>0.1</td><td>-</td><td>100</td><td>%</td><td>Note 1,2</td></tr><tr><td>LT</td><td>Operating life</td><td>-</td><td>75000</td><td>100000</td><td>Hrs</td><td>Note 3,4</td></tr></tbody></table>	Symbol	Parameter	Min	Typ	Max	Units	Remark	VLED	Input Voltage	4.5	5	5.5	Volt		ILED	Input Current	-	TBD	-	A	VLED =5V, DPM =100%	PLED	Power Consumption	-	TBD	-	W	VLED =5V, DPM =100%	InrushLED	Inrush Current	-	TBD	-	A	VLED =5V, DPM =100%	VPWM DIM	Backlight power control input voltage	1.2	-	5.5	V	ON	-	-	0.4	V	OFF	FPWM	Dimming Frequency	100	-	600	Hz		DPWM	Dimming duty cycle	0.1	-	100	%	Note 1,2	LT	Operating life	-	75000	100000	Hrs	Note 3,4	<h3>5.2.1 Parameter guideline for LED</h3> <p>Following characteristics are measured under stable condition using a LED driving board at 25°C(Room Temperature).</p> <table><thead><tr><th>Symbol</th><th>Parameter</th><th>Min</th><th>Typ</th><th>Max</th><th>Units</th><th>Remark</th></tr></thead><tbody><tr><td>VLED</td><td>Input Voltage</td><td>4.5</td><td>5</td><td>5.5</td><td>Volt</td><td></td></tr><tr><td>ILED</td><td>Input Current</td><td>-</td><td>TBD</td><td>-</td><td>A</td><td>VLED =5V, DPM =100%</td></tr><tr><td>PLED</td><td>Power Consumption</td><td>-</td><td>TBD</td><td>-</td><td>W</td><td>VLED =5V, DPM =100%</td></tr><tr><td>InrushLED</td><td>Inrush Current</td><td>-</td><td>TBD</td><td>-</td><td>A</td><td>VLED =5V, DPM =100%</td></tr><tr><td rowspan="2">VPWM DIM</td><td rowspan="2">Backlight power control input voltage</td><td>1.2</td><td>-</td><td>5.5</td><td>V</td><td>ON</td></tr><tr><td>-</td><td>-</td><td>0.4</td><td>V</td><td>OFF</td></tr><tr><td>FPWM</td><td>Dimming Frequency</td><td>100</td><td>-</td><td>600</td><td>Hz</td><td></td></tr><tr><td>DPWM</td><td>Dimming duty cycle</td><td>0.1</td><td>-</td><td>100</td><td>%</td><td>Note 1,2</td></tr><tr><td rowspan="2">VLED On/Off</td><td>On Control Voltage</td><td>1.2</td><td>-</td><td>5.5</td><td>Volt</td><td>Note 3, 4</td></tr><tr><td>Off Control Voltage</td><td>-</td><td>-</td><td>0.4</td><td>Volt</td><td></td></tr><tr><td>LT</td><td>Operating life</td><td>-</td><td>75000</td><td>100000</td><td>Hrs</td><td>Note 3,4</td></tr></tbody></table>	Symbol	Parameter	Min	Typ	Max	Units	Remark	VLED	Input Voltage	4.5	5	5.5	Volt		ILED	Input Current	-	TBD	-	A	VLED =5V, DPM =100%	PLED	Power Consumption	-	TBD	-	W	VLED =5V, DPM =100%	InrushLED	Inrush Current	-	TBD	-	A	VLED =5V, DPM =100%	VPWM DIM	Backlight power control input voltage	1.2	-	5.5	V	ON	-	-	0.4	V	OFF	FPWM	Dimming Frequency	100	-	600	Hz		DPWM	Dimming duty cycle	0.1	-	100	%	Note 1,2	VLED On/Off	On Control Voltage	1.2	-	5.5	Volt	Note 3, 4	Off Control Voltage	-	-	0.4	Volt		LT	Operating life	-	75000	100000	Hrs	Note 3,4																									
Symbol	Parameter	Min	Typ	Max	Units	Remark																																																																																																																																																																											
VLED	Input Voltage	4.5	5	5.5	Volt																																																																																																																																																																												
ILED	Input Current	-	TBD	-	A	VLED =5V, DPM =100%																																																																																																																																																																											
PLED	Power Consumption	-	TBD	-	W	VLED =5V, DPM =100%																																																																																																																																																																											
InrushLED	Inrush Current	-	TBD	-	A	VLED =5V, DPM =100%																																																																																																																																																																											
VPWM DIM	Backlight power control input voltage	1.2	-	5.5	V	ON																																																																																																																																																																											
		-	-	0.4	V	OFF																																																																																																																																																																											
FPWM	Dimming Frequency	100	-	600	Hz																																																																																																																																																																												
DPWM	Dimming duty cycle	0.1	-	100	%	Note 1,2																																																																																																																																																																											
LT	Operating life	-	75000	100000	Hrs	Note 3,4																																																																																																																																																																											
Symbol	Parameter	Min	Typ	Max	Units	Remark																																																																																																																																																																											
VLED	Input Voltage	4.5	5	5.5	Volt																																																																																																																																																																												
ILED	Input Current	-	TBD	-	A	VLED =5V, DPM =100%																																																																																																																																																																											
PLED	Power Consumption	-	TBD	-	W	VLED =5V, DPM =100%																																																																																																																																																																											
InrushLED	Inrush Current	-	TBD	-	A	VLED =5V, DPM =100%																																																																																																																																																																											
VPWM DIM	Backlight power control input voltage	1.2	-	5.5	V	ON																																																																																																																																																																											
		-	-	0.4	V	OFF																																																																																																																																																																											
FPWM	Dimming Frequency	100	-	600	Hz																																																																																																																																																																												
DPWM	Dimming duty cycle	0.1	-	100	%	Note 1,2																																																																																																																																																																											
VLED On/Off	On Control Voltage	1.2	-	5.5	Volt	Note 3, 4																																																																																																																																																																											
	Off Control Voltage	-	-	0.4	Volt																																																																																																																																																																												
LT	Operating life	-	75000	100000	Hrs	Note 3,4																																																																																																																																																																											
	20	<h3>6.2 Scanning Direction</h3> <p>The following figures show the image seen from the front view. The arrow indicates the direction of scan.</p> <div></div>	<h3>6.2 Scanning Direction</h3> <p>The following figures show the image seen from the front view. The arrow indicates the direction of scan.</p> <div></div>																																																																																																																																																																														
	23	<h3>6.5 Interface Timing</h3> <h4>6.5.1 Timing Characteristics</h4> <table><thead><tr><th>Signal</th><th>Parameter</th><th>Symbol</th><th>Min.</th><th>Typ.</th><th>Max.</th><th>Unit</th></tr></thead><tbody><tr><td rowspan="2">Clock Timing</td><td>Clock Pulse Duty</td><td>Tsk</td><td>40</td><td>50</td><td>60</td><td>%</td></tr><tr><td>Setup Time</td><td>Tdsu</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td rowspan="2">Data</td><td>Hold Time</td><td>Tdhd</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td>Setup Time</td><td>Tdsu</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td rowspan="2">DE</td><td>Hold Time</td><td>Tdehd</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td>Setup Time</td><td>Tdesu</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td rowspan="3">Hsync Timing</td><td rowspan="3">Horizontal Section</td><td>Period</td><td>TH</td><td>TBD</td><td>375</td><td>TBD</td></tr><tr><td>Active</td><td>THD</td><td></td><td>320</td><td></td></tr><tr><td>Blanking</td><td>THB</td><td>TBD</td><td>55</td><td>TBD</td></tr><tr><td rowspan="3">Vsync Timing</td><td rowspan="4">Vertical Section</td><td>Period</td><td>TV</td><td>TBD</td><td>264</td><td>TBD</td></tr><tr><td>Active</td><td>TVH</td><td></td><td>240</td><td></td></tr><tr><td>Blanking</td><td>TVB</td><td>TBD</td><td>24</td><td>TBD</td></tr><tr><td colspan="2">Frame Rate</td><td>F</td><td>-</td><td>60</td><td>-</td><td>Hz</td></tr></tbody></table>	Signal	Parameter	Symbol	Min.	Typ.	Max.	Unit	Clock Timing	Clock Pulse Duty	Tsk	40	50	60	%	Setup Time	Tdsu	12			ns	Data	Hold Time	Tdhd	12			ns	Setup Time	Tdsu	12			ns	DE	Hold Time	Tdehd	12			ns	Setup Time	Tdesu	12			ns	Hsync Timing	Horizontal Section	Period	TH	TBD	375	TBD	Active	THD		320		Blanking	THB	TBD	55	TBD	Vsync Timing	Vertical Section	Period	TV	TBD	264	TBD	Active	TVH		240		Blanking	TVB	TBD	24	TBD	Frame Rate		F	-	60	-	Hz	<h3>6.5 Interface Timing</h3> <h4>6.5.1 Timing Characteristics</h4> <table><thead><tr><th>Signal</th><th>Parameter</th><th>Symbol</th><th>Min.</th><th>Typ.</th><th>Max.</th><th>Unit</th></tr></thead><tbody><tr><td rowspan="2">Clock Timing</td><td>Clock frequency</td><td>1/Tclock</td><td>TBD</td><td>6</td><td>TBD</td><td>MHz</td></tr><tr><td>Setup Time</td><td>Tdsu</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td rowspan="2">Data</td><td>Hold Time</td><td>Tdhd</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td>Setup Time</td><td>Tdsu</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td rowspan="2">DE</td><td>Hold Time</td><td>Tdehd</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td>Setup Time</td><td>Tdesu</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td rowspan="3">Hsync Timing</td><td rowspan="3">Horizontal Section</td><td>Period</td><td>TH</td><td>TBD</td><td>375</td><td>TBD</td></tr><tr><td>Active</td><td>THD</td><td></td><td>320</td><td></td></tr><tr><td>Blanking</td><td>THB</td><td>TBD</td><td>55</td><td>TBD</td></tr><tr><td rowspan="3">Vsync Timing</td><td rowspan="4">Vertical Section</td><td>Period</td><td>TV</td><td>TBD</td><td>264</td><td>TBD</td></tr><tr><td>Active</td><td>TVH</td><td></td><td>240</td><td></td></tr><tr><td>Blanking</td><td>TVB</td><td>TBD</td><td>24</td><td>TBD</td></tr><tr><td colspan="2">Frame Rate</td><td>F</td><td>-</td><td>60</td><td>-</td><td>Hz</td></tr></tbody></table>	Signal	Parameter	Symbol	Min.	Typ.	Max.	Unit	Clock Timing	Clock frequency	1/Tclock	TBD	6	TBD	MHz	Setup Time	Tdsu	12			ns	Data	Hold Time	Tdhd	12			ns	Setup Time	Tdsu	12			ns	DE	Hold Time	Tdehd	12			ns	Setup Time	Tdesu	12			ns	Hsync Timing	Horizontal Section	Period	TH	TBD	375	TBD	Active	THD		320		Blanking	THB	TBD	55	TBD	Vsync Timing	Vertical Section	Period	TV	TBD	264	TBD	Active	TVH		240		Blanking	TVB	TBD	24	TBD	Frame Rate		F	-	60	-	Hz
Signal	Parameter	Symbol	Min.	Typ.	Max.	Unit																																																																																																																																																																											
Clock Timing	Clock Pulse Duty	Tsk	40	50	60	%																																																																																																																																																																											
	Setup Time	Tdsu	12			ns																																																																																																																																																																											
Data	Hold Time	Tdhd	12			ns																																																																																																																																																																											
	Setup Time	Tdsu	12			ns																																																																																																																																																																											
DE	Hold Time	Tdehd	12			ns																																																																																																																																																																											
	Setup Time	Tdesu	12			ns																																																																																																																																																																											
Hsync Timing	Horizontal Section	Period	TH	TBD	375	TBD																																																																																																																																																																											
		Active	THD		320																																																																																																																																																																												
		Blanking	THB	TBD	55	TBD																																																																																																																																																																											
Vsync Timing	Vertical Section	Period	TV	TBD	264	TBD																																																																																																																																																																											
		Active	TVH		240																																																																																																																																																																												
		Blanking	TVB	TBD	24	TBD																																																																																																																																																																											
Frame Rate		F	-	60	-	Hz																																																																																																																																																																											
Signal	Parameter	Symbol	Min.	Typ.	Max.	Unit																																																																																																																																																																											
Clock Timing	Clock frequency	1/Tclock	TBD	6	TBD	MHz																																																																																																																																																																											
	Setup Time	Tdsu	12			ns																																																																																																																																																																											
Data	Hold Time	Tdhd	12			ns																																																																																																																																																																											
	Setup Time	Tdsu	12			ns																																																																																																																																																																											
DE	Hold Time	Tdehd	12			ns																																																																																																																																																																											
	Setup Time	Tdesu	12			ns																																																																																																																																																																											
Hsync Timing	Horizontal Section	Period	TH	TBD	375	TBD																																																																																																																																																																											
		Active	THD		320																																																																																																																																																																												
		Blanking	THB	TBD	55	TBD																																																																																																																																																																											
Vsync Timing	Vertical Section	Period	TV	TBD	264	TBD																																																																																																																																																																											
		Active	TVH		240																																																																																																																																																																												
		Blanking	TVB	TBD	24	TBD																																																																																																																																																																											
Frame Rate		F	-	60	-	Hz																																																																																																																																																																											
	26	<h3>6.6 LED Backlight Unit Interface Signal Description</h3> <table><thead><tr><th>Pin #</th><th>Symbol</th><th>Pin Description</th></tr></thead><tbody><tr><td>1</td><td>VLED</td><td>Backlight Power Supply Voltage</td></tr><tr><td>2</td><td>VLED</td><td>Backlight Power Supply Voltage</td></tr><tr><td>3</td><td>GND</td><td>Ground</td></tr><tr><td>4</td><td>GND</td><td>Ground</td></tr><tr><td>5</td><td>LED On/Off</td><td>Backlight ON-OFF(ON:2.5~5V,OFF:0~0.8V)</td></tr><tr><td>6</td><td>PWM DIM</td><td>Light Dimming Control(PWM)input(High active)</td></tr></tbody></table>	Pin #	Symbol	Pin Description	1	VLED	Backlight Power Supply Voltage	2	VLED	Backlight Power Supply Voltage	3	GND	Ground	4	GND	Ground	5	LED On/Off	Backlight ON-OFF(ON:2.5~5V,OFF:0~0.8V)	6	PWM DIM	Light Dimming Control(PWM)input(High active)	<h3>6.6 LED Backlight Unit Interface Signal Description</h3> <table><thead><tr><th>Pin #</th><th>Symbol</th><th>Pin Description</th></tr></thead><tbody><tr><td>1</td><td>VLED</td><td>Backlight Power Supply Voltage</td></tr><tr><td>2</td><td>VLED</td><td>Backlight Power Supply Voltage</td></tr><tr><td>3</td><td>GND</td><td>Ground</td></tr><tr><td>4</td><td>GND</td><td>Ground</td></tr><tr><td>5</td><td>VLED On/Off</td><td>Backlight ON-OFF(ON:1.2V,OFF:0~0.4V)</td></tr><tr><td>6</td><td>PWM DIM</td><td>Light Dimming Control(PWM)input(High active)</td></tr></tbody></table>	Pin #	Symbol	Pin Description	1	VLED	Backlight Power Supply Voltage	2	VLED	Backlight Power Supply Voltage	3	GND	Ground	4	GND	Ground	5	VLED On/Off	Backlight ON-OFF(ON:1.2V,OFF:0~0.4V)	6	PWM DIM	Light Dimming Control(PWM)input(High active)																																																																																																																																				
Pin #	Symbol	Pin Description																																																																																																																																																																															
1	VLED	Backlight Power Supply Voltage																																																																																																																																																																															
2	VLED	Backlight Power Supply Voltage																																																																																																																																																																															
3	GND	Ground																																																																																																																																																																															
4	GND	Ground																																																																																																																																																																															
5	LED On/Off	Backlight ON-OFF(ON:2.5~5V,OFF:0~0.8V)																																																																																																																																																																															
6	PWM DIM	Light Dimming Control(PWM)input(High active)																																																																																																																																																																															
Pin #	Symbol	Pin Description																																																																																																																																																																															
1	VLED	Backlight Power Supply Voltage																																																																																																																																																																															
2	VLED	Backlight Power Supply Voltage																																																																																																																																																																															
3	GND	Ground																																																																																																																																																																															
4	GND	Ground																																																																																																																																																																															
5	VLED On/Off	Backlight ON-OFF(ON:1.2V,OFF:0~0.4V)																																																																																																																																																																															
6	PWM DIM	Light Dimming Control(PWM)input(High active)																																																																																																																																																																															

26

6.7 Power ON/OFF Sequence

Power ON/OFF sequence time : TBD

6.7 Power ON/OFF Sequence



Power ON/OFF sequence timing

Parameter	Min.	Typ.	Max.	Units
T1	0.5	-	10	[ms]
T2	30	40	50	[ms]
T3	200	-	-	[ms]
T4	0.5	-	10	[ms]
T5	10	-	-	[ms]
T6	10	-	-	[ms]
T7	0	-	-	[ms]
T8	10	-	-	[ms]
T9	-	-	10	[ms]
T10	110	-	-	[ms]
T11	0	16	50	[ms]
T12	-	-	10	[ms]
T13	1000	-	-	[ms]

The above on/off sequence should be applied to avoid abnormal function in the display. Please make sure to turn off the power when you plug the cable into the input connector or pull the cable out of the connector.

27

7.2 Backlight Power (CN2): LED Connector

Manufacturer	JAE
Connector Model Number	FI-S6P-HFE, compatible with FI-S6S

7.2 Backlight Power (CN2): LED Connector

Manufacturer	JAE
Backlight-side Connector Model Number	FI-S6P-HFE
Mating Connector Model Number	FI-S6S

29

8. Reliability Test Criteria


Items	Required Condition	Note
Temperature Humidity Bias	40°C/90%~300 hours	Note 2
High Temperature Operation	85°C/300 hours	Note 2
Low Temperature Operation	-30°C/300 hours	Note 2
Hot Storage	85°C/300 hours	Note 2
Cold Storage	-30°C/300 hours	Note 2
Thermal Shock Test	-20°C/30 min, 60°C/30 min, 100cycles	Note 2
Hot Start Test	85°C/1 Hr (min.), power on/off per 5 minutes, repeat 5 times	Note 2
Cold Start Test	-30°C/1 Hr (min.), power on/off per 5 minutes, repeat 5 times	Note 2
Shock Test (Non-Operating)	50G, 20ms, Half-sine wave, (±X, ±Y, ±Z)	Note 2
Vibration Test (Non-Operating)	1.5G, (10~200Hz, P-P) 30 mins/axis (X, Y, Z)	Note 2
On/off test	On/10 sec, Off/10 sec, 30,000 cycles	Note 1,2
ESD	Contact Discharge: ±8KV, 150pF(330Ω)1sec, 8 points, 25 times/point Air Discharge: ±15KV, 150pF(330Ω)1sec, 8 points, 25 times/point	Note 2
Altitude Test	Operating: 14,000 ft, Ramp: 2000 ft/min, 8hrs Non-operating: 40,000 ft, Ramp: 2000 ft/min, 24hrs	Note 2

8. Reliability Test Criteria


Items	Required Condition	Note
Temperature Humidity Bias	40°C/90%~300 hours	Note 2
High Temperature Operation	85°C/300 hours	Note 2
Low Temperature Operation	-30°C/300 hours	Note 2
Hot Storage	85°C/300 hours	Note 2
Cold Storage	-30°C/300 hours	Note 2
Thermal Shock Test	-20°C/30 min, 60°C/30 min, 100cycles	Note 2
Hot Start Test	85°C/1 Hr (min.), power on/off per 5 minutes, repeat 5 times	Note 2
Cold Start Test	-30°C/1 Hr (min.), power on/off per 5 minutes, repeat 5 times	Note 2
Shock Test (Non-Operating)	50G, 20ms, Half-sine wave, (±X, ±Y, ±Z)	Note 2
Vibration Test (Non-Operating)	1.5G, (10~200Hz, P-P) 30 mins/axis (X, Y, Z)	Note 2
On/off test	On/10 sec, Off/10 sec, 30,000 cycles	Note 1,2
ESD	Contact Discharge: ±8KV, 150pF(330Ω)1sec, 8 points, 25 times/point Air Discharge: ±15KV, 150pF(330Ω)1sec, 8 points, 25 times/point	Note 2

30

9. Mechanical Characteristics




9. Mechanical Characteristics



10.2 Carton Package

Max. capacity: TBD
Max. weight: TBD
Outside dimension of carton: TBD

10.2 Carton Package



Typical Power Consumption		[Watt]	TBD		
Weight		[Grams]	TBD		
Color / Chromaticity Coordinates (CIE 1931)	White x		0.263	0.313	0.363
	White y		0.279	0.329	0.379
	Red x			TBD	
	Red y			TBD	
	Green x			TBD	
	Green y			TBD	
	Blue x			TBD	
	Blue y			TBD	

5.1.1 Power Specification

Symbol	Parameter	Min	Typ	Max	Units	Remark
VDD	Logic/LCD Drive Voltage	3.0	3.3	3.6	[V _{olt}]	
IDD	VDD Current	-	-	TBD	[nA]	All Black Pattern (VDD=3.3V, at 60Hz)
Irush	LCD Inrush Current	-	-	1.5	[A]	Note 1
PDD	VDD Power	-	TBD	TBD	[Watt]	All Black Pattern (VDD=3.3V, at 60Hz)
VDDrp	Allowable Logic/LCD Drive Ripple Voltage	-	-	100	mVp-p	All Black Pattern (VDD=3.3V, at 60Hz)

Symbol	Parameter	Min	Typ	Max	Units	Remark
V _{LED}	Input Voltage	4.5	5	5.5	Volt	
I _{LED}	Input Current	-	TBD	-	A	V _{LED} =5V, D _{PWM} =100%
P _{LED}	Power Consumption	-	TBD	-	W	V _{LED} =5V, D _{PWM} =100%
Inrush _{LED}	Inrush Current	-	TBD	-	A	V _{LED} =5V, D _{PWM} =100%
V _{FWM DIM}	Backlight power control input voltage	1.2	-	5.5	V	ON
F _{PWM}	Dimming Frequency	100	-	600	Hz	OFF
D _{PWM}	Dimming duty cycle	0.1	100	-	%	Note 1,2
V _{LED ON/OFF}	On Control Voltage	1.2	-	5.5	Volt	
	Off Control Voltage	-	-	0.4	Volt	Note 3,4
LT	Operation life	-	75000	100000	Hrs	Note 3,4

Typical Power Consumption		[Watt]	1.566 W (LCD: 0.066 W/LED BLU: 1.5 W) @ All black pattern, Full Load and VLED=5V		
Weight		[Grams]	150g (typ.), 165g (max.)		
Color / Chromaticity Coordinates (CIE 1931)		White x	0.263	0.313	0.361
		White y	0.279	0.329	0.379
		Red x	0.491	0.541	0.591
		Red y	0.253	0.303	0.353
		Green x	0.279	0.329	0.379
		Green y	0.559	0.609	0.659
		Blue x	0.111	0.161	0.211
	Blue y	0.064	0.114	0.164	

5.1.1 Power Specification


Symbol	Parameter	Min	Typ	Max	Units	Remark
VDD	Logic/LCD Drive Voltage	3.0	3.3	3.6	[Volt]	
IDD	VDD Current	-	20	24	[mA]	All Black Pattern (VDD=3.3V, at 60Hz)
Irush	LCD Inrush Current	-	-	0.26	[A]	Note 1
PDD	VDD Power	66	88		[mW]	All Black Pattern (VDD=3.3V, at 60Hz)
VDDrp	Allowable Logic/LCD Drive Ripple Voltage	-	-	100	mVp-p	All Black Pattern (VDD=3.3V, at 60Hz)

Symbol	Parameter	Min	Typ	Max	Units	Remark
V _{LED}	Input Voltage	4.5	5	5.5	Volt	
I _{LED}	Input Current	-	0.3	0.4	A	V _{LED} = 5V, D _{PRW} = 100%
P _{LED}	Power Consumption	-	1.5	2.2	W	V _{LED} = 5V, D _{PRW} = 100%
I _{rushLED}	Inrush Current	-	-	1.5	A	V _{LED} = 5V, D _{PRW} = 100%
V _{FWM DIM}	Backlight power control input voltage	1.2	-	5.5	V	ON OFF
		-	-	0.4	V	
F _{FWM}	Dimming Frequency	100	-	600	Hz	Note 1, 2
D _{PRW}	Dimming duty cycle	0.1	100	100	%	
V _{LED ON/OFF}	On Control Voltage	1.2	-	5.5	Volt	Note 3, 4
	Off Control Voltage	-	-	0.4	Volt	
LT	Operation life	-	75000	100000	Hrs	Note 3, 4

6.5.1 Timing Characteristics

Signal	Parameter	Symbol	Min.	Typ.	Max.	Unit
Clock Timing	Clock frequency	1/ <i>T_{clk}</i>	<i>TBD</i>			MHz
Data	Setup Time	<i>T_{dsu}</i>	12			ns
	Hold Time	<i>T_{dhd}</i>	12			ns
DE	Setup Time	<i>T_{dsu}</i>	12			ns
	Hold Time	<i>T_{dhd}</i>	12			ns
Hsync Timing	Horizontal Section	Period	<i>T_H</i>	<i>TBD</i>	375	<i>TBD</i>
		Active	<i>T_{HD}</i>		320	<i>T_{clock}</i>
		Blanking	<i>T_{HB}</i>	<i>TBD</i>	55	<i>TBD</i>
Vsync Timing	Vertical Section	Period	<i>T_V</i>	<i>TBD</i>	264	<i>TBD</i>
		Active	<i>T_{VD}</i>		240	<i>T_{line}</i>
		Blanking	<i>T_{VB}</i>	<i>TBD</i>	24	<i>TBD</i>
Frame Rate			<i>F</i>	-	60	Hz


6.5.2 Input Timing Diagram



6.5.1 Timing Characteristics


Parameter		Symbol	Min.	Typ.	Max.	Unit
Clock frequency		1/ T_{Clock}	5	6	8	MHz
Data	Setup Time	T_{dsu}	12			
	Hold Time	T_{dhd}	12			
DE	Setup Time	T_{esu}	12			
	Period Time	T_h	325	371	438	
HSYNC	Display Period	T_{hdisp}		320		
	Back Porch	T_{bse}	3	43	43	
	Front Porch	T_{fse}	2	8	75	
	Pulse Width	T_{pw}	2	4	43	
VSYNC	Period Time	T_v	244	260	289	
	Display Period	T_{vdisp}		240		
	Back Porch	T_{vbs}	2	12	12	
	Front Porch	T_{vfs}	2	8	37	
	Pulse Width	T_{vps}	2	4	12	
Frame Rate		F		60		Hz

6.5.2 Input Timing Diagram




31

9. Mechanical Characteristics



9. Mechanical Characteristics



Punch thickness 9.8mm is reference

10

Typical Power Consumption	[Watt]	1.566 W (LCD: 0.066 WILED BLU: 1.5 W) @ All black pattern, Full Load and VLED=5V
---------------------------	--------	---

Typical Power Consumption	[Watt]	1.818 W (LCD: 0.066 WILED BLU: 1.75 W) @ All black pattern, Full Load and VLED=5V
---------------------------	--------	--

11

Note 1: Measurement method
Equipment Pattern Generator, Power Supply, Digital Voltmeter, Luminance meter (SR_3 or equivalent)
Aperture 1" with 50cm viewing distance

Note 1: Measurement method
Equipment Pattern Generator, Power Supply, Digital Voltmeter, Luminance meter (SR_3 or equivalent)
Aperture 1" with 50cm viewing distance

13

Note 7: Definition of viewing angle
Viewing angle is the measurement of contrast ratio ≥ 10 , at the screen center, over a 180° horizontal and 180° vertical range (off-normal viewing angles). The 180° viewing angle range is broken down as below: 90° (θ) horizontal left and right, and 90° (φ) vertical high (up) and low (down). The measurement direction is typically perpendicular to the display surface with the screen rotated to its center to develop the desired measurement viewing angle.

Note 7: Definition of viewing angle
Viewing angle is the measurement of contrast ratio ≥ 10 , at the screen center, over a 180° horizontal and 180° vertical range (off-normal viewing angles). The 180° viewing angle range is broken down as below: 90° (θ) horizontal left and right, and 90° (φ) vertical high (up) and low (down). The measurement direction is typically perpendicular to the display surface with the screen rotated to its center to develop the desired measurement viewing angle.

13

Note 8: Definition of Gamma Value

Remove this note.

17

5.1.1 Power Specification						
Symbol	Parameter	Min	Typ	Max	Units	Remark
VDD	Logic/LCD Drive Voltage	3.0	3.3	3.6	[Volt]	
IDD	VDD Current	-	20	24	[mA]	All Black Pattern (VDD=3.3V, at 60Hz)
Irush	LCD Inrush Current	-	-	0.28	[A]	Note 1
PDD	VDD Power	-	66	88	[Watt]	All Black Pattern (VDD=3.3V, at 60Hz)
VDDrp	Allowable Logic/LCD Drive Ripple Voltage	-	-	100	mVp-p	All Black Pattern (VDD=3.3V, at 60Hz)

5.1.1 Power Specification						
Symbol	Parameter	Min	Typ	Max	Units	Remark
VDD	Logic/LCD Drive Voltage	3.0	3.3	3.6	[Volt]	
IDD	VDD Current	-	20	24	[mA]	All Black Pattern (VDD=3.3V, at 60Hz)
Irush	LCD Inrush Current	-	-	280	[mA]	Note 1
PDD	VDD Power	-	66	88	[mW]	All Black Pattern (VDD=3.3V, at 60Hz)
VDDrp	Allowable Logic/LCD Drive Ripple Voltage	-	-	100	mVp-p	All Black Pattern (VDD=3.3V, at 60Hz)

18

5.1.2 Signal Electrical Characteristics						
Input signals shall be low or Hi-Z state when VDD is off.						
Parameter	Symbol	Min.	Typ.	Max.	Unit	Remarks
Logic Input Voltage for Display Signals	High	VIH	0.7VDD	-	VDD	Volt
	Low	VIL	0	-	0.3VDD	Volt
Input Voltage for RL/UD	High	VIH	VDD-0.4	-	VDD	Volt
	Low	VIL	0	-	GND+0.4	Volt

5.1.2 Signal Electrical Characteristics						
Input signals shall be low or Hi-Z state when VDD is off.						
Parameter	Symbol	Min.	Typ.	Max.	Unit	Remarks
Logic Input Voltage for Display Signals	High	VIH	0.7VDD	-	VDD	Volt
	Low	VIL	0	-	0.3VDD	Volt
Input Voltage for RL/UD	High	VIH	0.7VDD	-	VDD	Volt
	Low	VIL	0	-	0.3VDD	Volt

18

Symbol	Parameter	Min	Typ	Max	Units	Remark
VLED	Input Voltage	4.5	5	5.5	Volt	
ILED	Input Current	-	0.3	0.4	A	VLED=5V, DPMW=100%
PLED	Power Consumption	-	1.5	2.2	W	VLED=5V, DPMW=100%
IrushLED	Inrush Current	-	-	1.5	A	VLED=5V, DPMW=100%
VPWM DIM	Backlight power control input voltage	1.2	-	5.5	V	ON
		-	-	0.4	V	OFF
FPWM	Dimming Frequency	100	-	600	Hz	Note 1, 2
DPMW	Dimming duty cycle	0.1	-	100	%	
VLED on/off	On Control Voltage	1.2	-	5.5	Volt	Note 3, 4
	Off Control Voltage	-	-	0.4	Volt	
LT	Operating life	75000	100000	-	Hrs	Note 3, 4

Symbol	Parameter	Min	Typ	Max	Units	Remark
VLED	Input Voltage	4.5	5	5.5	Volt	
ILED	Input Current	-	0.35	0.4	A	VLED=5V, DPMW=100%
PLED	Power Consumption	-	1.5	2.2	W	VLED=5V, DPMW=100%
IrushLED	Inrush Current	-	-	1.5	A	VLED=5V, DPMW=100%
VPWM DIM	Backlight power control input voltage	1.2	-	5.5	V	ON
		-	-	0.4	V	OFF
FPWM	Dimming Frequency	100	-	600	Hz	Note 1, 2
DPMW	Dimming duty cycle	0.1	-	100	%	
VLED on/off	On Control Voltage	1.2	-	5.5	Volt	Note 3, 4
	Off Control Voltage	-	-	0.4	Volt	
LT	Operating life	75000	100000	-	Hrs	Note 3, 4

24

6.5.1 Timing Characteristics						
Parameter	Symbol	Min.	Typ.	Max.	Unit	
Clock frequency						
Data	Setup Time	Tdsu	12		ns	
	Hold Time	Tdhd	12		ns	
DE	Setup Time	Tdsu	12		ns	
	Period Time	Th	325	371	438	
HSYNC	Display Period	Tdisp		320		
	Back Porch	Tb	3	43	43	
	Front Porch	Tf	2	8	75	
	Pulse Width	Tpw	2	4	43	
	Period Time	Tx	244	260	289	
VSYNC	Display Period	Tdisp		240		
	Back Porch	Tb	2	12	12	
	Front Porch	Tf	2	8	37	
	Pulse Width	Tpw	2	4	12	
Frame Rate		F		60		Hz

6.5.1 Timing Characteristics						
Parameter	Symbol	Min.	Typ.	Max.	Unit	
Clock frequency						
Data	Setup Time	Tdsu	12		ns	
	Hold Time	Tdhd	12		ns	
DE	Setup Time	Tdsu	12		ns	
	Period Time	Th	325	371	438	
HSYNC	Display Period	Tdisp		320		
	Back Porch	Tb	3	43	43	
	Front Porch	Tf	2	8	75	
	Pulse Width	Tpw	2	4	43	
	Period Time	Tx	244	260	289	
VSYNC	Display Period	Tdisp		240		
	Back Porch	Tb	2	12	12	
	Front Porch	Tf	2	8	37	
	Pulse Width	Tpw	2	4	12	
Frame Rate		F		60		Hz

		<div>Note 8: Definition of Gamma Value</div> <div>Generally, Gamma Value is defined as the slope of a Gray Level – Luminance curve in log-log space, that is</div> <div>$\gamma = d \log(\text{Luminance}) / d \log(\text{Gray Level})$</div> <div>The Gamma Value defined in this spec is Linear Regression ($\gamma_1, \gamma_2, \gamma_3 \dots, \gamma_{16}$). γ_1 to γ_{16} are the section gamma of the following 17 sampling points, GL(0), GL(16), GL(32), GL(48), GL(64), GL(80), GL(96), GL(112), GL(128), GL(144), GL(160), GL(176), GL(192), GL(208), GL(224), GL(240) and GL(255), in 8 bits input.</div>		<div>Remove Note 8</div>																																																																																																																																																																																																					
				<div>Add Note 5</div> <div>5.2.1 Parameter guideline for LED</div> <div>Following characteristics are measured under stable condition using a LED driving board at 25°C(Room Temperature).</div> <table><tr><th>Symbol</th><th>Parameter</th><th>Min</th><th>Typ</th><th>Max</th><th>Units</th><th>Remark</th></tr><tr><td>V_{LED}</td><td>Input Voltage</td><td>4.5</td><td>5</td><td>5.5</td><td>Volt</td><td></td></tr><tr><td>I_{LED}</td><td>Input Current</td><td>-</td><td>0.35</td><td>0.4</td><td>A</td><td>$V_{LED} = 5V, D_{PWM} = 100\%$</td></tr><tr><td>$P_{LED}$</td><td>Power Consumption</td><td>-</td><td>1.5</td><td>2.2</td><td>W</td><td>$V_{LED} = 5V, D_{PWM} = 100\%$</td></tr><tr><td>$I_{rushLED}$</td><td>Inrush Current</td><td>-</td><td>-</td><td>1.5</td><td>A</td><td>$V_{LED} = 5V, D_{PWM} = 100\%$ Note 5</td></tr><tr><td>$V_{PWM \text{ DIM}}$</td><td>Backlight power control input voltage</td><td>1.2</td><td>-</td><td>5.5</td><td>V</td><td>ON</td></tr><tr><td></td><td></td><td>-</td><td>-</td><td>0.4</td><td>V</td><td>OFF</td></tr><tr><td>F_{PWM}</td><td>Dimming Frequency</td><td>100</td><td>-</td><td>600</td><td>Hz</td><td>Note 1, 2</td></tr><tr><td>D_{PWM}</td><td>Dimming duty cycle</td><td>0.1</td><td>-</td><td>100</td><td>%</td><td></td></tr><tr><td>$V_{LED \text{ On/Off}}$</td><td>On Control Voltage</td><td>1.2</td><td>-</td><td>5.5</td><td>Volt</td><td>Note 3, 4</td></tr><tr><td></td><td>Off Control Voltage</td><td>-</td><td>-</td><td>0.4</td><td>Volt</td><td></td></tr><tr><td>LT</td><td>Operating life</td><td>75000</td><td>100000</td><td>-</td><td>Hrs</td><td>Note 3, 4</td></tr></table> <div>Note 5: Measurement condition:</div> <div>V_{LED} rising time</div>	Symbol	Parameter	Min	Typ	Max	Units	Remark	V_{LED}	Input Voltage	4.5	5	5.5	Volt		I_{LED}	Input Current	-	0.35	0.4	A	$V_{LED} = 5V, D_{PWM} = 100\%$	P_{LED}	Power Consumption	-	1.5	2.2	W	$V_{LED} = 5V, D_{PWM} = 100\%$	$I_{rushLED}$	Inrush Current	-	-	1.5	A	$V_{LED} = 5V, D_{PWM} = 100\%$ Note 5	$V_{PWM \text{ DIM}}$	Backlight power control input voltage	1.2	-	5.5	V	ON			-	-	0.4	V	OFF	F_{PWM}	Dimming Frequency	100	-	600	Hz	Note 1, 2	D_{PWM}	Dimming duty cycle	0.1	-	100	%		$V_{LED \text{ On/Off}}$	On Control Voltage	1.2	-	5.5	Volt	Note 3, 4		Off Control Voltage	-	-	0.4	Volt		LT	Operating life	75000	100000	-	Hrs	Note 3, 4																																																																																																																	
Symbol	Parameter	Min	Typ	Max	Units	Remark																																																																																																																																																																																																			
V_{LED}	Input Voltage	4.5	5	5.5	Volt																																																																																																																																																																																																				
I_{LED}	Input Current	-	0.35	0.4	A	$V_{LED} = 5V, D_{PWM} = 100\%$																																																																																																																																																																																																			
P_{LED}	Power Consumption	-	1.5	2.2	W	$V_{LED} = 5V, D_{PWM} = 100\%$																																																																																																																																																																																																			
$I_{rushLED}$	Inrush Current	-	-	1.5	A	$V_{LED} = 5V, D_{PWM} = 100\%$ Note 5																																																																																																																																																																																																			
$V_{PWM \text{ DIM}}$	Backlight power control input voltage	1.2	-	5.5	V	ON																																																																																																																																																																																																			
		-	-	0.4	V	OFF																																																																																																																																																																																																			
F_{PWM}	Dimming Frequency	100	-	600	Hz	Note 1, 2																																																																																																																																																																																																			
D_{PWM}	Dimming duty cycle	0.1	-	100	%																																																																																																																																																																																																				
$V_{LED \text{ On/Off}}$	On Control Voltage	1.2	-	5.5	Volt	Note 3, 4																																																																																																																																																																																																			
	Off Control Voltage	-	-	0.4	Volt																																																																																																																																																																																																				
LT	Operating life	75000	100000	-	Hrs	Note 3, 4																																																																																																																																																																																																			
1.2 2021/7/9	19																																																																																																																																																																																																								
		<div>6.5.1 Timing Characteristics</div> <table><tr><th>Parameter</th><th>Symbol</th><th>Min.</th><th>Typ.</th><th>Max.</th><th>Unit</th></tr><tr><td>Clock frequency</td><td>$1/T_{Clock}$</td><td>5</td><td>6</td><td>8</td><td>MHz</td></tr><tr><td>Data</td><td>Setup Time T_{dsu}</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td></td><td>Hold Time T_{dhd}</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td>DE</td><td>Setup Time T_{esu}</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td></td><td>Period Time T_h</td><td>325</td><td>371</td><td>438</td><td></td></tr><tr><td>HSYNC</td><td>Display Period T_{hdsp}</td><td></td><td>320</td><td></td><td></td></tr><tr><td></td><td>Back Porch T_{btp}</td><td>3</td><td>43</td><td>43</td><td></td></tr><tr><td></td><td>Front Porch T_{fep}</td><td>2</td><td>8</td><td>75</td><td></td></tr><tr><td></td><td>Pulse Width T_{wp}</td><td>2</td><td>4</td><td>43</td><td></td></tr><tr><td>VSYNC</td><td>Period Time T_v</td><td>244</td><td>260</td><td>289</td><td></td></tr><tr><td></td><td>Display Period T_{vdis}</td><td></td><td>240</td><td></td><td></td></tr><tr><td></td><td>Back Porch T_{bvp}</td><td>2</td><td>12</td><td>12</td><td></td></tr><tr><td></td><td>Front Porch T_{fvp}</td><td>2</td><td>8</td><td>37</td><td></td></tr><tr><td></td><td>Pulse Width T_{vp}</td><td>2</td><td>4</td><td>12</td><td></td></tr><tr><td>Frame Rate</td><td>F</td><td></td><td>60</td><td>70</td><td>Hz</td></tr></table> <div>Note: DE mode only.</div>	Parameter	Symbol	Min.	Typ.	Max.	Unit	Clock frequency	$1/T_{Clock}$	5	6	8	MHz	Data	Setup Time T_{dsu}	12			ns		Hold Time T_{dhd}	12			ns	DE	Setup Time T_{esu}	12			ns		Period Time T_h	325	371	438		HSYNC	Display Period T_{hdsp}		320				Back Porch T_{btp}	3	43	43			Front Porch T_{fep}	2	8	75			Pulse Width T_{wp}	2	4	43		VSYNC	Period Time T_v	244	260	289			Display Period T_{vdis}		240				Back Porch T_{bvp}	2	12	12			Front Porch T_{fvp}	2	8	37			Pulse Width T_{vp}	2	4	12		Frame Rate	F		60	70	Hz	<div>6.5.1 Timing Characteristics</div> <table><tr><th>Parameter</th><th>Symbol</th><th>Min.</th><th>Typ.</th><th>Max.</th><th>Unit</th></tr><tr><td>Clock frequency</td><td>$1/T_{Clock}$</td><td>5</td><td>6</td><td>8</td><td>MHz</td></tr><tr><td>Data</td><td>Setup Time T_{dsu}</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td></td><td>Hold Time T_{dhd}</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td>DE</td><td>Setup Time T_{desu}</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td></td><td>Hold Time T_{dehd}</td><td>12</td><td></td><td></td><td>ns</td></tr><tr><td>HSYNC</td><td>Period Time T_h</td><td>325</td><td>371</td><td>438</td><td></td></tr><tr><td></td><td>Display Period T_{hdsp}</td><td></td><td>320</td><td></td><td></td></tr><tr><td></td><td>Back Porch T_{btp}</td><td>3</td><td>43</td><td>43</td><td></td></tr><tr><td></td><td>Front Porch T_{fep}</td><td>2</td><td>8</td><td>75</td><td></td></tr><tr><td></td><td>Pulse Width T_{wp}</td><td>2</td><td>4</td><td>43</td><td></td></tr><tr><td>VSYNC</td><td>Period Time T_v</td><td>244</td><td>260</td><td>289</td><td></td></tr><tr><td></td><td>Display Period T_{vdis}</td><td></td><td>240</td><td></td><td></td></tr><tr><td></td><td>Back Porch T_{bvp}</td><td>2</td><td>12</td><td>12</td><td></td></tr><tr><td></td><td>Front Porch T_{fvp}</td><td>2</td><td>8</td><td>37</td><td></td></tr><tr><td></td><td>Pulse Width T_{vp}</td><td>2</td><td>4</td><td>12</td><td></td></tr><tr><td>Frame Rate</td><td>F</td><td></td><td>60</td><td>70</td><td>Hz</td></tr></table> <div>Note: DE mode only.</div>	Parameter	Symbol	Min.	Typ.	Max.	Unit	Clock frequency	$1/T_{Clock}$	5	6	8	MHz	Data	Setup Time T_{dsu}	12			ns		Hold Time T_{dhd}	12			ns	DE	Setup Time T_{desu}	12			ns		Hold Time T_{dehd}	12			ns	HSYNC	Period Time T_h	325	371	438			Display Period T_{hdsp}		320				Back Porch T_{btp}	3	43	43			Front Porch T_{fep}	2	8	75			Pulse Width T_{wp}	2	4	43		VSYNC	Period Time T_v	244	260	289			Display Period T_{vdis}		240				Back Porch T_{bvp}	2	12	12			Front Porch T_{fvp}	2	8	37			Pulse Width T_{vp}	2	4	12		Frame Rate	F		60	70	Hz
Parameter	Symbol	Min.	Typ.	Max.	Unit																																																																																																																																																																																																				
Clock frequency	$1/T_{Clock}$	5	6	8	MHz																																																																																																																																																																																																				
Data	Setup Time T_{dsu}	12			ns																																																																																																																																																																																																				
	Hold Time T_{dhd}	12			ns																																																																																																																																																																																																				
DE	Setup Time T_{esu}	12			ns																																																																																																																																																																																																				
	Period Time T_h	325	371	438																																																																																																																																																																																																					
HSYNC	Display Period T_{hdsp}		320																																																																																																																																																																																																						
	Back Porch T_{btp}	3	43	43																																																																																																																																																																																																					
	Front Porch T_{fep}	2	8	75																																																																																																																																																																																																					
	Pulse Width T_{wp}	2	4	43																																																																																																																																																																																																					
VSYNC	Period Time T_v	244	260	289																																																																																																																																																																																																					
	Display Period T_{vdis}		240																																																																																																																																																																																																						
	Back Porch T_{bvp}	2	12	12																																																																																																																																																																																																					
	Front Porch T_{fvp}	2	8	37																																																																																																																																																																																																					
	Pulse Width T_{vp}	2	4	12																																																																																																																																																																																																					
Frame Rate	F		60	70	Hz																																																																																																																																																																																																				
Parameter	Symbol	Min.	Typ.	Max.	Unit																																																																																																																																																																																																				
Clock frequency	$1/T_{Clock}$	5	6	8	MHz																																																																																																																																																																																																				
Data	Setup Time T_{dsu}	12			ns																																																																																																																																																																																																				
	Hold Time T_{dhd}	12			ns																																																																																																																																																																																																				
DE	Setup Time T_{desu}	12			ns																																																																																																																																																																																																				
	Hold Time T_{dehd}	12			ns																																																																																																																																																																																																				
HSYNC	Period Time T_h	325	371	438																																																																																																																																																																																																					
	Display Period T_{hdsp}		320																																																																																																																																																																																																						
	Back Porch T_{btp}	3	43	43																																																																																																																																																																																																					
	Front Porch T_{fep}	2	8	75																																																																																																																																																																																																					
	Pulse Width T_{wp}	2	4	43																																																																																																																																																																																																					
VSYNC	Period Time T_v	244	260	289																																																																																																																																																																																																					
	Display Period T_{vdis}		240																																																																																																																																																																																																						
	Back Porch T_{bvp}	2	12	12																																																																																																																																																																																																					
	Front Porch T_{fvp}	2	8	37																																																																																																																																																																																																					
	Pulse Width T_{vp}	2	4	12																																																																																																																																																																																																					
Frame Rate	F		60	70	Hz																																																																																																																																																																																																				
1.3 2021/7/13	24	<div>6.5.1</div>	<div>6.5.1</div>																																																																																																																																																																																																						

1. Operating Precautions

- 1) Since front polarizer is easily damaged, please be cautious and not to scratch it.
- 2) Be sure to turn off power supply when inserting or disconnecting from input connector.
- 3) Wipe off water drop immediately. Long contact with water may cause discoloration or spots.
- 4) When the panel surface is soiled, wipe it with absorbent cotton or soft cloth.
- 5) Since the panel is made of glass, it may be broken or cracked if dropped or bumped on hard surface.
- 6) Since CMOS LSI is used in this module, take care of static electricity and insure human earth when handling.
- 7) Do not open nor modify the module assembly.
- 8) Do not press the reflector sheet at the back of the module to any direction.
- 9) In case if a module has to be put back into the packing container slot after it was taken out from the container, do not press the center of the LED Reflector edge. Instead, press at the far ends of the LED Reflector edge softly. Otherwise the TFT Module may be damaged.
- 10) At the insertion or removal of the Signal Interface Connector, be sure not to rotate nor tilt the Interface Connector of the TFT Module.
- 11) TFT-LCD Module is not allowed to be twisted & bent even force is added on module in a very short time. Please design your display product well to avoid external force applying to module by end-user directly.
- 12) Small amount of materials without flammability grade are used in the TFT-LCD module. The TFT-LCD module should be supplied by power complied with requirements of Limited Power Source (IEC60950-1 or UL60950-1), or be applied exemption.
- 13) Severe temperature condition may result in different luminance, response time.
- 14) Continuous operating TFT-LCD Module under high temperature environment may accelerate LED light bar exhaustion and reduce luminance dramatically.
- 15) The data on this specification sheet is applicable when TFT-LCD module is placed in landscape position.
- 16) Continuous displaying fixed pattern may induce image sticking. It's recommended to use screen saver or moving content periodically if fixed pattern is displayed on the screen.

2. General Description

G057QTN01.4 is a Color Active Matrix Liquid Crystal Display composed of a TFT-LCD display, a driver circuit, and a backlight system. The screen format is intended to support QVGA (320(H) x 240(V)) screen and 262K (RGB 6-bits). All input signals are CMOS interface compatible.

G057QTN01.4 is designed for industrial display applications.

2.1 Display Characteristics

The following items are characteristics summary on the table under 25 °C condition:

Items	Unit	Specifications
Screen Diagonal	[inch]	5.7
Active Area	[mm]	115.2(H) x 86.4(V)
Pixels H x V		320x3(RGB)x240
Pixel Pitch	[mm]	0.36 x 0.36
Pixel Arrangement		R.G.B. Vertical Stripe
Display Mode		TN, Normally White
Nominal Input Voltage VDD	[Volt]	3.3 typ.
Typical Power Consumption	[Watt]	1.816 W (LCD: 0.066 W/LED BLU: 1.75 W) @ All black pattern, Full Load and VLED=5V
Weight	[Grams]	150g (typ.), 165g (max.)
Physical Size	[mm]	144.0(H)x 104.6(V) x 8.8(D) (typ.)
Electrical Interface		CMOS 6-bit Parallel RGB
Surface Treatment		Anti-Glare, Hardness 3H
Support Color		262K colors
Temperature Range Operating Storage (Non-Operating)	[°C] [°C]	-30 to +85 (Panel surface temperature) -30 to +85
RoHS Compliance		RoHS Compliance

2.2 Optical Characteristics

The optical characteristics are measured under stable conditions at 25°C (Room Temperature):

Item	Unit	Conditions	Min.	Typ.	Max.	Note
White Luminance	[cd/m ²]	V _{LED} =5V, D _{PWM} =100% (center point)	400	500	-	1
Uniformity		5 Points			1.3	1, 2, 3
Contrast Ratio			500	700	-	4
Cross talk	%		-	1.2	1.5	5
Response Time	[msec]	Rising	-	15	20	6
	[msec]	Falling	-	10	15	
	[msec]	Raising + Falling	-	25	35	
Viewing Angle	[degree]	Horizontal (Right)	70	80	-	7
	[degree]	CR = 10 (Left)	70	80	-	
	[degree]	Vertical (Upper)	60	70	-	
	[degree]	CR = 10 (Lower)	60	70	-	
Color / Chromaticity Coordinates (CIE 1931)		White x	0.263	0.313	0.363	
		White y	0.279	0.329	0.379	
		Red x	0.491	0.541	0.591	
		Red y	0.253	0.303	0.353	
		Green x	0.279	0.329	0.379	
		Green y	0.559	0.609	0.659	
		Blue x	0.111	0.161	0.211	
		Blue y	0.064	0.114	0.164	
Color Gamut	%			50		


Note 1: Measurement method

Equipment Pattern Generator, Power Supply, Digital Voltmeter, Luminance meter (SR_3 or equivalent)


Aperture 1° with 50cm viewing distance

Test Point Center

Environment < 1 lux



Note 2: Definition of 9 points position (Display active area: 115.2(H) x 86.4(V))



Note 3: The luminance uniformity of 9 points is defined by dividing the minimum luminance values by the maximum test point luminance

$$\delta_{w9} = \frac{\text{Minimum Brightness of nine points}}{\text{Maximum Brightness of nine points}}$$

Note 4 : Definition of contrast ratio (CR):

$$\text{Contrast ratio (CR)} = \frac{\text{Brightness on the "White" state}}{\text{Brightness on the "Black" state}}$$


Note 5 : Definition of cross talk (CT)

$$CT = |YB - YA| / YA \times 100 (\%)$$

Where


YA = Luminance of measured location without gray level 0 pattern (cd/m2)

YB = Luminance of measured location with gray level 0 pattern (cd/m2)




Note 6: Definition of response time:

The output signals of photo detector are measured when the input signals are changed from “White” to “Black” (falling time) and from “Black” to “White” (rising time), respectively. The response time interval is between 10% and 90% of amplitudes. Please refer to the figure as below.




Note 7: Definition of viewing angle

Viewing angle is the measurement of contrast ratio ≥ 10 , at the screen center, over a 180° horizontal and 180° vertical range (off-normal viewing angles). The 180° viewing angle range is broken down as below: 90° (θ) horizontal left and right, and 90° (Φ) vertical high (up) and low (down). The measurement direction is typically perpendicular to the display surface with the screen rotated to its center to develop the desired measurement viewing angle.



3. Functional Block Diagram

The following diagram shows the functional block of the 5.7 inch color TFT/LCD module:



4. Absolute Maximum Ratings

4.1 Absolute Ratings of TFT LCD Module

Item	Symbol	Min	Max	Unit	Remark
Logic/LCD Drive Voltage	VDD	-0.3	+4.0	Volt	Ta= 25°C
LCD Input Signal Voltage	VIN	-0.3	+4.0	Volt	Ta= 25°C
LED BLU Drive Voltage	V _{LED}	-0.3	42	Volt	Ta= 25°C
LED Dimming Input Voltage High	V _{PWM}	-0.3	+6	Volt	Ta= 25°C
LED On/Off Input Voltage	V _{LED On/Off}	-0.3	+6	Volt	Ta= 25°C

4.2 Absolute Ratings of Environment

Item	Symbol	Min	Max	Unit	Remark
Operating Temperature	TOP	-30	+85	°C	Note 1, 2
Operation Humidity	HOP	5	90	%RH	Note 1, 2
Storage Temperature	TST	-30	+85	°C	Note 1
Storage Humidity	HST	5	90	%RH	Note 1

Note 1: Maximum Wet-Bulb should be 39°C and no condensation.

Note 2: Only operation is guaranteed. Optical performance should be evaluated at 25°C only.

5. Electrical Characteristics


5.1 TFT LCD Module

5.1.1 Power Specification

Symbol	Parameter	Min	Typ	Max	Units	Remark
VDD	Logic/LCD Drive Voltage	3.0	3.3	3.6	[Volt]	
IDD	VDD Current	-	20	24	[mA]	All Black Pattern (VDD=3.3V, at 60Hz)
Irush	LCD Inrush Current	-	-	280	[mA]	Note 1
PDD	VDD Power		66	88	[mW]	All Black Pattern (VDD=3.3V, at 60Hz)
VDDrp	Allowable Logic/LCD Drive Ripple Voltage	-	-	100	mVp-p	All Black Pattern (VDD=3.3V, at 60Hz)

Note 1: Measurement condition:

VDD



5.1.2 Signal Electrical Characteristics

Input signals shall be low or Hi-Z state when VDD is off.

Parameter		Symbol	Min.	Typ.	Max.	Unit	Remarks
Logic Input Voltage for Display Signals	High	VIH	0.7VDD	-	VDD	Volt	
	Low	VIL	0	-	0.3VDD	Volt	
Input Voltage for RL/UD	High	VIH	0.7VDD	-	VDD	Volt	
	Low	VIL	0	-	0.3VDD	Volt	

5.2 Backlight Unit

5.2.1 Parameter guideline for LED

Following characteristics are measured under stable condition using a LED driving board at 25°C (Room Temperature).

Symbol	Parameter	Min	Typ	Max	Units	Remark
V _{LED}	Input Voltage	4.5	5	5.5	Volt	
I _{LED}	Input Current	-	0.35	0.4	A	V _{LED} = 5V, D _{PWM} = 100%
P _{LED}	Power Consumption	-	1.5	2.2	W	V _{LED} = 5V, D _{PWM} = 100%
I _{rushLED}	Inrush Current	-		1.5	A	V _{LED} = 5V, D _{PWM} = 100% Note 5
V _{PWM DIM}	Backlight power control input voltage	1.2		5.5	V	ON
		-	-	0.4	V	OFF
F _{PWM}	Dimming Frequency	100	-	600	Hz	Note 1, 2
D _{PWM}	Dimming duty cycle	0.1		100	%	
V _{LED On/Off}	On Control Voltage	1.2		5.5	Volt	Note 3, 4
	Off Control Voltage	-	-	0.4	Volt	
LT	Operating life	75000	100000		Hrs	Note 3, 4

Note 1: PWM dimming function can be operated by PWM signal. PWM duty cycle can adjust white Luminance.

(PWM High: ON and PWM Low: OFF)


Note 2: PWM signal can not be floating and pull-down to ground when waiting.

Note 3: If G057QTN01.4 module is driven by high current or at high ambient temperature & humidity

condition. The operating life will be reduced.

Note 4: Operating life means brightness goes down to 50% initial brightness. Minimum operating life time is estimated data.


Note 5: Measurement condition:



6. Signal Characteristic

6.1 Pixel Format Image

Following figure shows the relationship between input signal and LCD pixel format.



6.2 Scanning Direction

The following figures show the image seen from the front view. The arrow indicates the direction of scan.



6.3 TFT- LCD Interface Signal Description

Pin#	Signal Name	Description
1	GND	Ground
2	DOTCLK	Dot clock
3	NC	No Connection
4	NC	No Connection
5	GND	Ground
6	R0	Red data(LSB)
7	R1	Red data
8	R2	Red data
9	R3	Red data
10	R4	Red data
11	R5	Red data(MSB)
12	GND	Ground
13	G0	Green data(LSB)
14	G1	Green data
15	G2	Green data
16	G3	Green data
17	G4	Green data
18	G5	Green data(MSB)
19	GND	Ground
20	B0	Blue data(LSB)
21	B1	Blue data
22	B2	Blue data
23	B3	Blue data
24	B4	Blue data
25	B5	Blue data(MSB)
26	GND	Ground
27	DE	Data enable signal
28	VDD	Power supply (3.3V Typ. Only)
29	VDD	Power supply (3.3V Typ. Only)
30	R/L	Horizontal reverse scan
31	U/D	Vertical reverse scan
32	NC	No Connection
33	GND	Ground

6.4 The Input Data Format

This product displays 262,144 colors in terms of the 64 grey levels on RGB respectively. The following table demonstrates the display of input data.


Display colors		Data signal (0 : Low level, 1: High level)																	
		R5	R4	R3	R2	R1	R0	G5	G4	G3	G2	G1	G0	B5	B4	B3	B2	B1	B0
Basic colors	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1
	Red	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
	Magenta	1	1	1	1	1	1	0	0	0	0	0	0	1	1	1	1	1	1
	Green	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
	Cyan	0	0	0	0	0	0	1	1	1	1	1	1	1	1	1	1	1	1
	Yellow	1	1	1	1	1	1	1	1	1	1	1	1	0	0	0	0	0	0
	White	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
Red grayscale	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Dark	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0
		0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	
	↑ ↓ bright																		
		1	1	1	1	0	1	0	0	0	0	0	0	0	0	0	0	0	0
	Red	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0
Green grayscale	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Dark	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0
		0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	
	↑ ↓ bright																		
		0	0	0	0	0	0	1	1	1	1	0	1	0	0	0	0	0	0
	Green	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
Blue grayscale	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Dark	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0
		0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	
	↑ ↓ bright																		
		0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	0	1
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1

6.5 Interface Timing

6.5.1 Timing Characteristics

Parameter		Symbol	Min.	Typ.	Max.	Unit
Clock frequency		1/ T _{Clock}	5	6	8	MHz
Data	Setup Time	T _{dsu}	12			ns
	Hold Time	T _{dhd}	12			ns
DE	Setup Time	T _{dest}	12			ns
	Hold Time	T _{dehd}	12			ns
HSYNC	Period Time	T _h	325	371	438	DCLK
	Display Period	T _{hdisp}		320		
	Back Porch	T _{hbp}	3	43	43	
	Front Porch	T _{hfp}	2	8	75	
	Pulse Width	T _{hw}	2	4	43	
VSYNC	Period Time	T _v	244	260	289	HSYNC
	Display Period	T _{vdisp}		240		
	Back Porch	T _{vbp}	2	12	12	
	Front Porch	T _{vfp}	2	8	37	
	Pulse Width	T _{vw}	2	4	12	
Frame Rate		F		60	70	Hz


Note: DE mode only.



6.6 LED Backlight Unit Interface Signal Description

Pin #	Symbol	Pin Description
1	V_{LED}	Backlight Power Supply Voltage
2	V_{LED}	Backlight Power Supply Voltage
3	GND	Ground
4	GND	Ground
5	V_{LED} On/Off	Backlight ON-OFF(ON:1.2V,OFF:0~0.4V)
6	PWM DIM	Light Dimming Control(PWM)input(High active)

6.7 Power ON/OFF Sequence



Power ON/OFF sequence timing

Parameter	Value			Units
	Min.	Typ.	Max.	
T1	0.5	-	10	[ms]
T2	30	40	50	[ms]
T3	200	-	-	[ms]
T4	0.5	-	10	[ms]
T5	10	-	-	[ms]
T6	10	-	-	[ms]
T7	0	-	-	[ms]
T8	10	-	-	[ms]
T9	-	-	10	[ms]
T10	110	-	-	[ms]
T11	0	16	50	[ms]
T12	-	-	10	[ms]
T13	1000	-	-	[ms]

The above on/off sequence should be applied to avoid abnormal function in the display. Please make sure to turn off the power when you plug the cable into the input connector or pull the cable out of the connector.

7. Connector & Pin Assignment

Physical interface is described as for the connector on module. These connectors are capable of accommodating the following signals and will be following components.

7.1 TFT- LCD Signal (CN1): LCD Connector


Manufacturer	Starconn
Connector Model Number	089H33-000100-G2-R, compatible with MS2406P33M

7.2 Backlight Power (CN2): LED Connector

Manufacturer	JAE
Backlight-side Connector Model Number	FI-S6P-HFE
Mating Connector Model Number	FI-S6S

7.3 Connector Illustration

7.3.1 PIN 1 definition of CN1 and CN2



Note:

- 1.Tolerance is $\pm 0.5\text{mm}$ unless noted.
- 2.CN1 is STARCONN_089H33-000100-G2-R And CN2 is JAE FI-S6P-HFE

(Rear side of TFT-LCD)

8. Reliability Test Criteria


Items	Required Condition	Note
Temperature Humidity Bias	40°C /90%,300 hours	Note 2
High Temperature Operation	85°C ,300 hours	Note 2
Low Temperature Operation	-30°C ,300 hours	Note 2
Hot Storage	85°C ,300 hours	Note 2
Cold Storage	-30°C ,300 hours	Note 2
Thermal Shock Test	-20°C/30 min ,60°C/30 min ,100cycles	Note 2
Hot Start Test	85°C /1 Hr (min.), power on/off per 5 minutes, repeat 5 times	Note 2
Cold Start Test	-30°C /1 Hr (min.), power on/off per 5 minutes, repeat 5 times	Note 2
Shock Test (Non-Operating)	50G,20ms,Half-sine wave,(±X, ±Y, ±Z)	Note 2
Vibration Test (Non-Operating)	1.5G, (10~200Hz, P-P) 30 mins/axis (X, Y, Z)	Note 2
On/off test	On/10 sec, Off/10 sec, 30,000 cycles	Note 1,2
ESD	Contact Discharge:±8KV,150pF(330Ω)1sec,8 points,25 times/ point Air Discharge: ±15KV, 150pF(330Ω)1sec, 8 points, 25 times/ point	Note 2

Note 1: According to EN61000-4-2, ESD class B: Some performance degradation allowed. No data lost
Self-recoverable. No hardware failures.

Note 2:


- Water condensation is not allowed for each test items.
- Each test is done by new TFT-LCD module. Don't use the same TFT-LCD module repeatedly for reliability test.
- The reliability test is performed only to examine the TFT-LCD module capability.
- To inspect TFT-LCD module after reliability test, please store it at room temperature and room humidity for 24 hours at least in advance.
- No function failure occurs.

9. Mechanical Characteristics




10. Label and Packaging

10.1 Shipping Label (on the rear side of TFT-LCD display)



10.2 Carton Package



11.1 Sharp Edge Requirements

There will be no sharp edges or corners on the display assembly that could cause injury.

11.2 Materials

11.2.1 Toxicity

There will be no carcinogenic materials used anywhere in the display module. If toxic materials are used, they will be reviewed and approved by the responsible AUO Display Plus toxicologist.

11.2.2 Flammability

All components including electrical components that do not meet the flammability grade UL94-V1 in the module will complete the flammability rating exception approval process. The printed circuit board will be made from material rated 94-V1 or better. The actual UL flammability rating will be printed on the printed circuit board.

11.3 Capacitors

If any polarized capacitors are used in the display assembly, provisions will be made to keep them from being inserted backwards.

11.4 National Test Lab Requirement

The display module will satisfy all requirements for compliance to:

UL 60950-1, Second Edition

U.S.A. Information Technology Equipment